

# Eaton 170M6760

Catalog Number: 170M6760

Fuse-link, high speed, 630 A, AC 690 V, size 3, 76 x 92 x 139 mm, aR, IEC, UL, single indicator

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series high speed square body fuse	170M6760
	<b>UPC</b>
	051712792752
<b>EAN</b>	<b>Product Length/Depth</b>
5996516020661	168 mm
<b>Product Height</b>	<b>Product Width</b>
76 mm	95 mm
<b>Product Weight</b>	<b>Warranty</b>
959 g	Not Applicable
<b>Compliances</b>	<b>Certifications</b>
CE Marked	IEC Rated
RoHS Compliant	UL Recognized

## defaultTaxonomyAttributeLabel

### Type

Fuse

### Application

semiconductor protection

### Amperage Rating

630 A

### Breaking capacity

200 kA

### Fuse indicator

Centre fuse status indicator

### Insulated metal gripping lugs (IMGL)

No

### Utilization category

aR (accompanied semiconductor protection)

### Voltage type

AC

### Fuse size

3

### Rated voltage AC

690 V

### Center-to-center distance of connections

114 mm

### Current type

AC

### Mounting dimension

Other

### Class

Class aR

### Clearing (I2T)

210000 at 660 V

### Watt losses

105 W

### Fuse shape

Square body, center bolted tags

### Pre arc (I2T)

## Resources

### Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[Bussmann series complete full line catalog no. 1007](#)

[170M6760~Eaton Bussmann series high speed square body fuse](#)

31000

Color

None

Interrupt rating

200 kAIC

Fitted with:

Type K Indicator for micro

Connection

Blade end x blade end

Construction size

3

Packaging type

Standard

Voltage rating

690 V

Fuse type

US Style

FKE/115 Type K indicator for micro

Bolted tag

Fuse system (according to IEC 60269)

Other



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)