



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



500SR 500 Al/Cu Mechanical Butt Splice

Nsi Industries

Catalog Number	500SR
Manufacturer	Nsi Industries
Description	Aluminum Splicer Reducer 500 MCM - 3/0 Awg Aluminum Splicer Reducers Are Used For Splicing Two Copper or Aluminum Wires Of Equal or Different Sizes. Made Of 6061T-6 Aluminum Alloy. Tin Plated For Low Contact Resistance. Suitable For Use With Both Copper and Aluminum Conductors. Rated 600 Volts.
Weight per unit	0.7500 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Material	Aluminum
Poles	1
Voltage Rating	600
Warranty	1 YEAR

Material, Color, and Finish

Color	Silver
Finish	Aluminum

Descriptions

Description	500 AL/CU MECHANICAL BUTT SPLICE
extra long description	NSI 500SR Splicer Reducer 500 MCM-#
Features	Aluminum Splicer Reducer 500 MCM - 3/0 AWG Aluminum Splicer Reducers are used for splicing two copper or aluminum wires of equal or different sizes. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts.
Long Description	Aluminum Splicer Reducer 500 MCM - 3/0 AWG Aluminum Splicer Reducers are used for splicing two copper or aluminum wires of equal or different sizes. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts.
Product Type	Splicer Reducer 500 MCM-#4

Manufacturer Information

Brand	NSi
GTIN	00662381002358
Manufacturers Part Number	500SR
sub brand	Mechanical Connector
UPC	662381002358



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
----------------------	-------------

Packaging

Carton	3
--------	---

Weight Per each	0.75
-----------------	------

Uses, Certifications, and Standards

environmental conditions	90 C
--------------------------	------

Temperature Rating	90 C
--------------------	------