



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2097HGI Self Test GfcI Recp HG 20A 12 Iv

*Pass & Seymour/Legrand*

Catalog Number	2097HGI
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 20 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Ivory, 0.025 Sec Trip Time, Impact Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
media	Yes
Number of Wires	3
Outlet Type	Hospital Grade, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Length	1.03
Width	1.73

### Descriptions

Description	SELF TEST GFCI RECP HG 20A 12 IV
extra long description	P&S 2097HGI SELF-TEST GFCI HOS GRD

### Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007035933
UPC	785007035933



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	CULUS, cULus, UL Listed, FSUL