



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



20AC1I 20A 120/277VAC B+S Wire SP SW Iv

Pass & Seymour/Legrand

Catalog Number	20AC1I
Manufacturer	Pass & Seymour/Legrand
Description	1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Switches

Features

action	Single pole
actuator	Toggle
amperage rating	20
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	Halogen, Universal, CFL, Fluorescent, Incandescent, Xenon, LED
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	20A 120/277VAC B+S WIRE SP SW I
extra long description	P&S PS20AC1I 20A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V
Product Type	20A 120/277VAC B+S Wire SP SW I
Special Features	Back & side wire, locking support, heavy duty toggle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007196627
Manufacturers Part Number	PS20AC1I
UPC	785007196627

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Industrial Spec Grade
Enclosure	Nylon
Mounting standard	WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC