

# Scotch™ 2242 Linerless Electrical Rubber Tape

## **Product Description**

Scotch<sup>™</sup> 2242 Electrical Tape is an economical, general purpose, rubber tape. The tape is a highly conformable, linerless EPR (Ethylene Propylene Rubber) based electrical insulating tape. The tape is designed for use in splicing and terminating wires and cables rated up to 90°C. The tape will meet industry specifications for flame retardance and has the necessary physical and electrical properties to provide immediate moisture seals and void–free buildup.

### **Tape Features:**

- •Linerless, self–bonding, insulating tape
- •Ethylene propylene base
- •Flame retardant
- •Physical and electrical properties unaffected by degree of stretch
- •Uniform tape unwind from roll
- •Small roll size (OD)
- •Five year shelf life
- •Stable over wide application temperature range
- •Weather Resistant

## **Applications**

- •Primary insulation for cable splices and terminations
- •Moisture–sealing and insulating electrical connections
- •Bus bar insulation

**Physical Properties** 

ASTM D-4388

- •Moisture-sealing of cable ends
- •Motor leads
- •Wire and cable jacket repair

## Data: Physical and Electrical Properties

i nysicui i roper des	
Color	Black
Thickness	30 mils
ASTM D-4325	(0.762 mm)
Tensile Strength	250 psi
ASTM D-4325	(1.72 MPa)
Ultimate Elongation ASTM D-4325	1000 %
Operating Temperature	90°C
ASTM D-4388	(194°F)
Emergency Overload	130°C
ASTM D-4388	(266°F)
Thermal Resistivity	300°C
3M Transient	cm/watt
Ozone Resistance	Passes

Heat Resistance ASTM D–4388	Passes	
UV Resistance ASTM D–4388	Passes	
Flame Resistance IEEE Std 27–1974 A C37.20C 74	Passes	
<b>Electrical Properties</b>		
Dielectric Strength ASTM D–4325 Original	750 V/mil (29.5 KV/mm)	
ASTM D-4325 24 hrs in H <sub>2</sub> O	750 V/mil (29.5 KV/mm)	
ASTM D-4325 96 hrs @ 23°C 96% RH	730 V/mil (28.7 KV/mm)	
Volume Resistivity ASTM D–4325 Original Aged 96 hrs @ 23°C 96% RH	$>10^{15}$ ohm-cm $>10^{14}$ ohm-cm	
Dielctric Constant ASTM D–4325 1200 V @ 60 Hz 23	°C	
Dissipation Factor ASTM D–4325 1200 V @ 60 Hz 23	0.70% °C	
*This data is not to be used for specifications. Values listed are for typical properties and should not be considered minimum or maximum.		

## **Specifications**

#### Product

The high-voltage corona resistant tape must be supplied without a liner and based on ethylene propylene rubber and be capable of emergency operating cable temperature of 130°C. The tape must be capable of being applied in either stretched or unstretched conditions without resulting in loss in either physical or electrical properties. The tape must not split, crack, slip or flag when exposed to various environments (indoors or outdoor). The tape must be compatible with all synthetic cable insulations and have a shelf life of five years. The tape must be flame retardant.

#### **Engineering/Architectural**

Splicing and terminating solid dielectric cables shall be done in accordance with drawings engineered by the splice material manufacturer such as the 2047 Series available from the 3M company.

## **Installation Techniques**

Scotch<sup>™</sup> 2242 Electrical Tape should be applied in successive half-lapped level wound layers until desired buildup is reached.

This tape should be applied like any rubber tape: that is, the side of the tape wrapped inside the roll should be applied ouside on the splice. (Tacky side up.) This will help prevent the roll from getting progressively further away from the work area.

To eliminate voids in critical areas, highly elongate 2242 Tape. Stretch tape in these critical areas just short of the breaking point; doing so will not alter its physical or electrical properties. In less critical areas, less elongation may be used. Normally 2242 Tape is stretched 3/4 of its original width in these critical areas. Always attempt to half-lap to produce a uniform buildup.

## Shelf Life

Scotch<sup>™</sup> 2242 Electrical Tape has a 5-year shelf life (from date of manufacture) when stored under the following recommended storage conditions. Store behind present stock in a clean dry place at a temperature of 70°F and 40 to 50% relative humidity. Good stock rotation is also recommended.

## **Availability**

Scotch<sup>™</sup> 2242 Electrical Tape is available in 3/4 in. by 15 ft, and 1-1/2in. by 15 ft rolls from your electrical distributor.

#### IMPORTANT NOTICE TO PURCHASER: All statements, technical information and recommendations related to the Seller's products are based on information believed to be reliable, but the accuracy or completeness thereof is is not guaranteed. Before utilizing the product, the user should determine the suitability of the product for its liability whatsoever in connection with such

use. 80-6104-3993-9

#### **3M Electrical Products Division**

6801 River Place Blvd. Austin, TX 78726-9000

All statements or recommendations of the seller which are not contained in the Seller's current publications shall have no force or effect unless contained in an agreement signed by an authorized officer of the Seller. The statements contained herein are made in lieu of all warranties express or implied, including but not limited to the implied intended use. The user assumes all risks and warranties of merchantability and fitness for a particular purpose which warranties are hereby expressly disclaimed. (c)1991 3M

SELLER SHALL NOT BE LIABLE TO THE USER OR ANY OTHER PERSON UNDER ANY LEGAL THEORY, INCLUDING BUT NOT LIMITED TO NEGLIGENCE OR STRICT LIABILITY, FOR ANY INJURY OR FOR ANY DIRECT OR CONSEQUENTIAL DAMAGES SUSTAINED OR INCURRED BY REASON OF THE USE OF ANY OF THE SELLER'S PRODUCTS.

Litho in U.S.A

