



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



567 Scotchlok Electrical Idc 567-Pouch, BR *Minnesota Mining (3M)*

Catalog Number	567
Manufacturer	Minnesota Mining (3M)
Description	3M™ Scotchlok™ Insulation Displacement Connector 567 Electrically Connects A Tap Wire to A Run (Through) Wire While Insulating The Connection. This Connector Is Suitable For Control Circuit Wiring, Fixture Wiring, Appliance Wiring, Signal and Pa Systems and Automotive/Boat/RV Wiring. Polypropylene Insulated and Self Stripping.
Weight per unit	0.0008 (lbs/each)
Product Category	Small Terminals & Connectors

Descriptions

Description	SCOTCHLOK ELECTRICAL IDC 567-POUCH, BR
extra long description	3M 7100167058 3M™ Scotchlok™ IDC C
Features	3M™ Scotchlok™ Insulation Displacement Connector 567 is 600V rated for building wire and 1000V rated for signs, fixtures and luminaires. The connector withstands temperatures of 221 degrees F (105 degrees C). UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.
Long Description	3M™ Scotchlok™ Insulation Displacement Connector 567 electrically connects a tap wire to a run (through) wire while insulating the connection. This connector is suitable for control circuit wiring, fixture wiring, appliance wiring, signal and PA systems and automotive/boat/RV wiring. Polypropylene insulated and self stripping.
Product Type	3M™ Scotchlok™ Idc Connector 567
Special Features	Flame Retardant

Manufacturer Information

Brand	Scotchlok
GTIN	00054007148876
Manufacturers Part Number	567-POUCH
sub brand	Scotchlok
UPC	054007148876

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Insulation Displacement

Availability

minimum qty	100
-------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1000

Weight Per each 0.0008

Uses, Certifications, and Standards

standard UL and CSA