25W47 WATERTIGHT NEMA 4X/6P LOCKING CONNECTOR

25W47 | Pass & Seymour

FEATURES & BENEFITS

Locking Watertight Connector, 15amp 125volt, NEMA Configuration L5-15, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Type: Connector
Features: Watertight
Number Of Poles: 2
Number Of Wires: 3
Special Features: Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M
CSA Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121403

CONSTRUCTION INFORMATION

Material 1: Rubber

DIMENSIONS

Diameter (US): 1.81"

Length (US): 4.01"

TECHNICAL INFORMATION

Amps: 15A
Material: Rubber
NEMA Configuration Number: L5-15
NEMA Rating: 4X/6P
Volts: 125V
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

25W47 WATERTIGHT NEMA 4X/6P LOCKING CONNECTOR

25W47 | Pass & Seymour

FEATURES & BENEFITS

Locking Watertight Connector, 15amp 125volt, NEMA Configuration L5-15, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow
Type: Connector
Features: Watertight
Number Of Poles: 2
Number Of Wires: 3
Special Features: Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M
CSA Standard: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121403

CONSTRUCTION INFORMATION

Material 1: Rubber

DIMENSIONS

Diameter (US): 1.81"

Length (US): 4.01"

TECHNICAL INFORMATION

Amps: 15A
Material: Rubber
NEMA Configuration Number: L5-15
NEMA Rating: 4X/6P
Volts: 125V
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant