



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

5P1000R 7151 Eaton Us 1000VA 120/120VAC Rack *Eaton Power Quality*

Catalog Number	5P1000R
Manufacturer	Eaton Power Quality
Description	Eaton 5P Ups, 1U, 1000 Va, 770 W, 5-15P Input, Outputs: (5) 5-15R, 120V
Weight per unit	45.6 (lbs/each)
Product Category	Uninterruptible Power Supplies

Features

accessories	Quick Start Guide
battery	Sealed, lead-acid
Battery Type	VRLA
dimensions	20.0000 IN X 17.4000 IN X 1.7000 IN
Output Voltage	120V default
Phase	1 PH
Voltage Rating	151/153 V
Wattage	770 W

Dimensions and Weight

Height	1.7 W
Length	20 A
Width	275 LUMEN

Descriptions

Description	7151 EATON US 1000VA 120/120VAC RACK
extra long description	ETN 5P1000R EATON 5P RACKMOUNT 1U U
Features	The Eaton 5P UPS delivers reliable backup power in tower and various rackmount form factors for enterprise and distributed IT applications. As the first in the UPS industry to comply with the UL 2900-2-2 cybersecurity standard, Eaton's optional gigabit network card (NETWORK-M2) provides remote monitoring and management for the 5P family of products. When paired with Eaton Intelligent Power Manager (IPM) software, IT professionals can seamlessly manage their connected equipment install base, even in virtual
Long Description	Eaton 5P UPS, 1U, 1000 VA, 770 W, 5-15P input, Outputs: (5) 5-15R, 120V
Product Type	Eaton 5P Rackmount 1U Ups
Special Features	ROO/RPO: Rear terminal block connector for remote on/off and power off



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00743172043054
Manufacturers Part Number	5P1000R
UPC	743172043054

Taxonomies, Classifications, and Categories

Category Description	SURGE SUPPRESSION PRODUCTS
igcc	4149
Type	UPS
unspsc code	39121011

Packaging

Carton	1
Weight Per each	45.63

Uses, Certifications, and Standards

Application	Backup Power and Electronic Power Conversion
Frequency Rating	40/50/60
standard	UL 1778;UL 497A;cULus Listed;IEC 62040-2 C1-C2 / EN 55024 / CISPR22 Class B / FCC part 15 Class B;CE Marked