



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 6203002 2-1/2" SCH40 Long Line PVC Coupling

*Cantex, Inc*

Catalog Number	6203002
Manufacturer	Cantex, Inc
Description	Cantex 6203002 Is A 2-1/2 In. Schedule 40 Long Line Coupling With No Center Stop Used to Repair or Join Lengths Of Conduit Pipe Together With Two Solvent Weld Socket Ends
Weight per unit	0.4650 (lbs/each)
Product Category	PVC Conduit Fittings & Accy

### Features

outside diameter	2.875
Schedule	40

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Length	6
Size	2-1/2 in. Schedule 40 Long Line Coupling with No Center Stop

### Descriptions

Description	2-1/2" SCH40 LONG LINE PVC COUPLING
extra long description	CTX 6203002 2 1/2 TC40 L/LONG CPLG
Features	CANTEX 6203002 is a 2-1/2 in. Schedule 40 Long Line Coupling with No Center Stop used to repair or join lengths of conduit pipe together with two solvent weld socket ends
Long Description	CANTEX 6203002 is a 2-1/2 in. Schedule 40 Long Line Coupling with No Center Stop used to repair or join lengths of conduit pipe together with two solvent weld socket ends
Product Type	2 1/2 TC40 L/Long CPLG NS
Special Features	For use with Schedule 40 and Schedule 80 conduit

### Manufacturer Information

Brand	PVC & Accessories
GTIN	00088700023413
Manufacturers Part Number	6203002
UPC	088700023413

### Taxonomies, Classifications, and Categories

Type	2-1/2 in. Schedule 40 Long Line Coupling with No Center Stop;Schedule 40 Long Line Coupling with no Center Stop
------	---

### Trade Size

Trade Size	2 1/2
------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Weight Per each	0.465

## Uses, Certifications, and Standards

Application	Schedule 40 Long Line Coupling with no Center Stop
standard	Meets NEMA TC-3 Standards