


280-DCX EMT to AC/MC/FMC/NM Transition Fitting

Transition fitting for use between 1/2" EMT to 3/8" FMC, metal clad and armored cable assemblies with O.D. of .43-.61 (14/2 to 10/3 within the specified ranges), as well as 14/2 to 10/3 NM Cables and (2) 14/2 or (2) 12/2 NM Cables stacked. AC/MC should be prepared to the desired length and fed through the fitting. AC/MC/MCIA and FMC should be inserted until the armor engages with the endstop at the center of the fitting. Use of Antishort bushings is required on AC/MC cables. For dry locations only. Max wire fill is 60% or 0.137 sq. inches.

[Download Photo](#)[Download Drawing](#)[Download Drawing](#)

Product details

Catalog Number:	280-DCX
UPC Number:	78174709279
Trade Size:	1/2"
Unit Quantity:	25
Standard Package Quantity:	100

Dimensions

Trade Size:	1/2"
Dimensions A:	1.13
Dimensions B:	0.38
Dimensions C:	0.93

Certifications & Codes

Federal Specification Number: C22.2 no. 18 3-04

UL File Number: E9391

UNSPSC: 39131707

Nema Standard: FB-1

UL Standard: UL-514B