



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1820 N Main St.  
76033-0000, TX Cleburne  
Phone: 817-202-8933  
Fax: 817-202-8998

## 63502 14" 9W Led Undercab 3K/4K/5K White *Satco*

Catalog Number	63502
Manufacturer	Satco
Description	9 Watt 14-Inch Led White Under Cabinet Light - CCT Selectable - 40000 Hours
Weight per unit	0.8700 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.075
Lamp Included	Integrated
Lamp Type	LED
Material	Aluminum
Reflector Type	Frosted White
Socket Type	Integrated
Voltage Rating	120
Warranty	5 Year Limited - Fixtures
Wattage	9

### Material, Color, and Finish

Color	White
Finish	white
Style	Utility

### Dimensions and Weight

Height	1
Length	14
Width	3.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1820 N Main St.  
76033-0000, TX Cleburne  
Phone: 817-202-8933  
Fax: 817-202-8998

## Descriptions

Description	14" 9W LED UNDERCAB 3K/4K/5K WHITE
extra long description	SATCO 63/502 UNDER CAB LED SCCT 14"
Long Description	9 Watt 14-Inch LED White Under Cabinet Light - CCT Selectable - 40000 Hours
Product Type	Under Cab Led SCCT 14" - WH
Special Features	Warranty: 5-Years ; Location Rating: Dry ; NSF Approved: No ; Style: Utility ; JA8 Compliant: True ; Amps: 0.075A ; Incandescent Equivalent: 50W ; Operating Frequency: 50/60Hz ; Power Factor: >0.9 ; Wattage Selectable: False ; Bulb Included: Integrated ; Beam Angle (degree): 105 ; Cct Selectable: True ; Indoor Outdoor: Indoor ; IP Rating: IP20 ; Lens Finish: Frosted White ; Lens Material: Polycarbonate (PC) ; Mounting Procedure: Under Cabinet: Screws ; Operating Temp: -20C (-4F) to +40C (+104F) ; Replaceab

## Manufacturer Information

Brand	Nuvo
GTIN	00045923656484
Manufacturers Part Number	63/502
UPC	045923656484

## Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Functional Lighting

## Packaging

Carton	1
Weight	0.87
Weight Per each	0.87

## Uses, Certifications, and Standards

Application	Under Cabinet & Cove
Frequency Rating	50/60
Mounting	Under Cabinet: Screws
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
standard	cETLus - Listed