



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 670030609 18/4 Oa Foil SHLD

*Coleman Cable*

Catalog Number	670030609
Manufacturer	Coleman Cable
Description	Bare Copper Wire, 4 Conductors, #18 Awg Conductor Size, 300 V, 7/0.0152 MM Core Strands, PVC Jacket Material, PVC Insulation Material, Copper Conductor Material, Black;Red;White;Green, 1000 FT Overall Length, 0.193 In Outside Diameter, +60 °C Operating Temperature, 0.04 LB/MFT
Weight per unit	0.0400 (lbs/ft)
Product Category	Soft Drawn-STR (Stranded)

### Features

Drain Wire Size	24 AWG
Shielding Type	ALUMINUM MYLAR

### Material, Color, and Finish

Color Code	BLACK, RED, WHITE, GREEN
Drain Wire Material	TINNED COPPER
Jacket Color	Gray 0

### Dimensions and Weight

Length	1000 FT
Outer Diameter	0.193 Inch

### Descriptions

Additional Information	STRANDING 7/0.0152
Commodity Description	COPPER WIRE-BARE-SOFT DRAWN-STR
Description	18/4 OA FOIL SHLD

### Manufacturer Information

Brand	Cables & Cords
GTIN	00029892369156
Model	67003
UPC	029892369156

### Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC CABLE
Type	CMR/CL3R (UL)

### Availability

minimum qty	500
-------------	-----

### Packaging

Carton	1000
Weight Per foot	0.04



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Approval .....	UL, CUL .....
Temperature Rating .....	60 DEG C .....



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192

**PART NUMBER:** 67003  
**DESCRIPTION:** 18/4 STRANDED SHIELDED CMR/CL3R/FPLR  
**CONSTRUCTION:** This cable consists of four bare copper insulated conductors with an overall shield with a drain. The overall assembly has an overall jacket.  
**APPROVALS:** UL Standard 13 and 444, NEC Articles 725 and 800.  
**APPLICATION:** Class 3 Power Limited Circuit Cable and Communications Cable for Riser Applications

## Construction Parameters:

Conductor 18 AWG Bare Copper  
Stranding 7/.0152"  
Insulation Material PVC  
Insulation Thickness 0.008" Nom.  
Insulated Conductor Diameter 0.062" Nom.  
Number of Conductors 4  
Lay Length 4.00" Nom.  
Shield Alum/Mylar  
Drain 24 AWG Stranded Tinned Copper  
Jacket Material PVC  
Jacket Thickness 0.017" Nom.  
Overall Cable Diameter 0.196" Nom.  
Approximate Cable Weight 33.6 Lbs/1M' Nom.  
Flame Rating UL 1666 Riser Flame Test

## Cable Cross-Section



## Electrical & Environmental Properties:

Temperature Rating -20°C to 60°C  
Operating Voltage 300 V RMS Max.  
Capacitance Between Conductors @ 1 KHz 59 pF/ft Nom.  
Capacitance Between Conductors to Shield @ 1 KHz 109 pF/ft Nom.  
DC Resistance per Conductor @ 20°C 6.29 Ohms/1M' Nom.

Insulation Colors Black Red White Green  
Jacket Color Gray (Other colors available for minimum order)

Legend (Surface Ink Print) COLEMAN CABLE 67003 \* 18 AWG 4/C C(ETL)US (ETL CODE) TYPE CMR/CL3R/FPLR SUN RES -- CMX OUTDOOR - TYPE CMG FT4

This product complies with European Directive 2002/95/EC (RoHS)  
On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.  
Cable has a rip cord for easy jacket removal. The jacket is sequentially footmarked.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_ Date Signed \_\_\_\_\_  
Customer Approval \_\_\_\_\_

Specification Issue Date: June 18, 2007

# Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

\* Not all options are available for each product



## Coleman Cable Part Legend



Put-ups	Code
Reel, 250 ft	04
Reel, 500 ft	05
Reel, 1,000 ft	06
Reel-in-box, 1,000 ft	16
RabbitPull™ Pull-Box, 500 ft	45
RabbitPull™ Pull-Box, 1,000 ft	46
SignaCoil™ 500 ft	55
SignaCoil™ 1,000 ft	56

Colors	Code		Code
White	01	Pink	11
Yellow	02	Purple	13
Orange	03	Clear	18
Red	04	Fluorescent	
Green	05	Pink	21
Blue	06	Ivory	22
Brown	07	Natural	23
Black	08	Beige	33
Gray	09	Red Striped	
		CorraClad™	44

