



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



690LA Combo 2SW 1P 15A 120/277V W/GRD La

Pass & Seymour/Legrand

Catalog Number	690LA
Manufacturer	Pass & Seymour/Legrand
Description	<P>Single Pole, Double Combination Switch, 15 Amps, 120/277 Volts, With Ground. Light Almond. </P> <P>?</P>
Weight per unit	0.2100 (lbs/each)
Product Category	Combination Devices

Features

amperage rating	15
connection	Side wire
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
Load Rating	15 A @ 120/277 VAC
Load Type	Xenon, Incandescent, Halogen, CFL, Fluorescent, Universal, LED
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	2.0
Number of Wires	3
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	277 VAC, 120 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	4

Material, Color, and Finish

Color	Light Almond
Finish	SATIN

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	COMBO 2SW 1P 15A 120/277V W/GRD LA
extra long description	P&S 690LAG COMBO 2SW 1P 15A 120/277
Features	Combination
Long Description	<p>Single Pole, Double Combination Switch, 15 amps, 120/277 volts, With Ground. Light Almond. </p> <p>?</p>
Product Type	Combo 2SW 1P 15A 120/277V W/GRD La
Special Features	Two devices fits in one space, side wire



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007691078
Manufacturers Part Number	690LAG
UPC	785007691078

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Combination, Tamper-Resistant, Switch

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Weight Per each	0.21

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498