



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell  
88101-0000, NM Clovis  
Phone: 575-742-2504  
Fax: 575-742-2508



## 31355 Yellow 77, 5-Gallon Bucket

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 31355   |
| Manufacturer     | Ideal   |
| Description      | Yellow 77 Lubricant, Size: 5 Gal, Container: Bucket, Specific Gravity: 0.98, Plastic Safe: Yes, Slight Perfume Odor, Voc: 2.7 GPL (As Packaged, Minus Water), Working Temperature: 40 - 100 Deg F, Boiling Point: 212 Deg F (100 Deg C), Percent Volatile By Volume: Less Than 90 PCT, Percent Solid By Weight: Approximately 20 PCT, Yellow Paste, 7 - 8.5 PH, Solubility In Water: Moderate, Storage Temperature: 32 - 130 Deg F, UI Listed, For Wire Pulling |
| Weight per unit  | 43.0 (lbs/each)   |
| Product Category | Paint, Chemicals, Etc.  |

### Features

|                  |                |
|------------------|----------------|
| odor             | Slight Perfume |
| specific gravity | 0.98           |

### Dimensions and Weight

|      |   |
|------|---|
| Size | 5 |
|------|---|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell  
88101-0000, NM Clovis  
Phone: 575-742-2504  
Fax: 575-742-2508

## Descriptions

|                        |   |
|------------------------|---|
| Description            | YELLOW 77, 5-GALLON BUCKET  |
| extra long description | IDEAL 31-355 Yellow Lubricant,Ideal   |
| Features               | IDEAL Yellow 77 Wire pulling lubricant is a wax-based formula, and is the perfect general purpose lube. It is safe to use with most cable types except low-density polyethylene and semi-conducting jackets. It won't break down/separate after repeated exposure to freezing temperatures and dries to a thin, non-conductive film that won't clog conduit. Yellow 77 has a creamy texture and clings to cable throughout long pulls. Apply conveniently and uniformly by hand or brush. It is a homogeneous blend that requir |
| Long Description       | Yellow 77 Lubricant, Size: 5 GAL, Container: Bucket, Specific Gravity: 0.98, Plastic Safe: Yes, Slight Perfume Odor, Voc: 2.7 GPL (As Packaged, Minus Water), Working Temperature: 40 - 100 DEG F, Boiling Point: 212 DEG F (100 DEG C), Percent Volatile By Volume: Less Than 90 PCT, Percent Solid By Weight: Approximately 20 PCT, Yellow Paste, 7 - 8.5 pH, Solubility In Water: Moderate, Storage Temperature: 32 - 130 DEG F, UI Listed, For Wire Pulling   |
| Product Type           | Yellow Lubricant, Ideal, 5 Gal Bucket Capacity, For 77 Wire Pul   |
| Special Features       | The #1 brand of wire pulling lubricant since 1959 - the perfect general purpose lube; Wax-based formula provides superior lubricity; Safe to use with most cable types except low-density polyethylene and semi-conducting jackets; Won't break down or separate after repeated exposure to freezing temperatures; Dries to a thin, non-conductive film that won't clog conduit; Clings to cable throughout long pulls; Easy to apply by hand or with pump; Creamy texture applies easily and uniformly; Homogeneous blend requ |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250313556 |
| Manufacturers Part Number | 31-355         |
| UPC                       | 783250313556   |

## Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
| Type                 | Lubricant                  |

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 43 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3205 Axtell  
88101-0000, NM Clovis  
Phone: 575-742-2504  
Fax: 575-742-2508

---

## Uses, Certifications, and Standards

|                   |                        |
|-------------------|------------------------|
| Application ..... | For Wire Pulling ..... |
| standard .....    | UL Listed .....        |