



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196



696IG Combo 2SW 1P+3W 15A 120/277V Iv

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 696IG |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Single-Pole, 3-Way Double Combination Switch, 15A 120/277V, Ivory. |
| Weight per unit | 0.2400 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------------|--|
| action | (1) SP & (1) 3W |
| actuator | Toggle |
| amperage rating | 15 |
| connection | Side wire |
| Contact Configuration | N-O |
| Contact Rating | 15amp, 120/277vac |
| indoor/outdoor | Indoor |
| Load Rating | 15 A @ 120/277 VAC |
| Load Type | Universal, Halogen, Xenon, Incandescent, LED, CFL, Fluorescent |
| Material | Thermoplastic |
| Mounting Type | Wall Box |
| Number of Gangs | 1 |
| Number of Switches | 2.0 |
| operating cycles | 30k.0 |
| Poles | 3-Way, 1 |
| Switch Type | Toggle |
| throw type | Single Throw |
| Voltage | 120 VAC, 277 VAC |
| Voltage Rating | 0.433212996389892 |
| Wall Plate Included | NO |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | SATIN |
|--------|-------|

Dimensions and Weight

| | |
|------|--------------------------|
| Size | 1.32 L x 0.94 W x 4.06 H |
|------|--------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196

Descriptions

| | |
|------------------------|---|
| Description | COMBO 2SW 1P+3W 15A 120/277V IV |
| extra long description | P&S 696IG COMBO 2SW 1P+3W 15A 120/2 |
| Features | Combination |
| Long Description | Single-Pole, 3-way Double Combination Switch, 15A 120/277V, Ivory. |
| Product Type | Combo 2SW 1P+3W 15A 120/277V I |
| Special Features | Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements. |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007006216 |
| Manufacturers Part Number | 696-IG |
| UPC | 785007006216 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------------------|
| Category Description | Residential Switches |
| Type | Combination, Switch, Tamper-Resistant |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.24 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential/Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| Operating Temperature | Maximum continuous +60°C, minimum -30°C |
| standard | CULUS, UL20 |