






PART	WIRE RANGE	HEX SIZE	L	H	W	A	B	C	D	MOUNT HOLE
3-250L2/L4	250KCMIL - 6 AWG	5/16	3.88	1.02	2.50	.56	3.01	.22	.38	9/16
3-350L2/L4	350KCMIL - 6 AWG	5/16	4.25	1.13	2.92	.63	3.25	.25	.59	9/16
3-600L2/L4	600KCMIL - 2 AWG	3/8	4.65	1.51	3.93	.63	3.40	.38	1.09	9/16
3-800L2/L4	800 - 300KCMIL	1/2	4.75	1.69	4.06	.63	3.38	.44	1.16	9/16
3-1000L2/L4	1000 - 500KCMIL	9/16	4.94	1.88	4.69	.63	3.44	.44	1.47	9/16



CONTACT NSI FOR SALES @ 800.321.5847

NOTES:

1. TIN PLATED 6061-T6511 ALUMINUM ALLOY.
2. UL LISTED 90° C FOR COPPER AND ALUMINIUM CONDUCTOR.

		POLARIS SALES CO. INC	
PROPRIETARY AND CONFIDENTIAL		11625 PROSPEROUS DRIVE ODESSA, FL 33556	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.		TITLE: NSI 3 PORT LUGS 2/4 NEMA MOUNT SERIES	
DRAWN BY: S.PARRY		DATE: 9/18/2012	
MATERIAL: SEE NOTE		DWG. NO.: 3-_L2/L4-SERIES	
SCALE: 1:2		SHEET: 1 OF 1	