



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35078 Powerblade Drill Powered Cable Cutter

Ideal

Catalog Number	35078
Manufacturer	Ideal
Description	Powerblade Cable Cutter, Voltage Rating: 12 V Minimum, Capacity: Up to 750 MCM Hard-Drawn Copper, Up to 1000 MCM Aluminum, Rugged Metal Housing
Weight per unit	1.0 (lbs/each)
Product Category	Wire & Cable Cutters

Features

housing	Rugged Metal
Voltage Rating	12 V Minimum

Descriptions

Description	POWERBLADE DRILL POWERED CABLE CUTTER
extra long description	IDEAL 35-078 DRILL POWERED CABLE CU
Features	PowerBlade Cable cutter cuts copper cable up to 750 MCM and aluminum cable up to 1000 MCM. It features heavy-duty gears and hardened rounded blades of professional quality that minimizes cable distortion. Cutter requires minimum voltage rating of 12 Volts for drilling that accepts 3/8 in. of drive shaft. It offers low speed RPM setting.
Long Description	PowerBlade Cable Cutter, Voltage Rating: 12 V Minimum, Capacity: Up To 750 MCM Hard-Drawn Copper, Up To 1000 MCM Aluminum, Rugged Metal Housing
Product Type	Drill Powered Cable Cutter
Special Features	Extremely versatile: fits almost any drill (12 V minimum); Cuts up to 750 MCM hard-drawn copper, 1000 MCM aluminum; Heavy-duty gears and specially hardened blades for professional quality; Rounded blade design minimizes cable distortion during cutting; No need to mess with battery packs or special chargers, this tool works with the drill you already carry; Drill not included

Manufacturer Information

Brand	Ideal
GTIN	00783250601752
Manufacturers Part Number	35-078
sub brand	PowerBlade
UPC	783250601752

Taxonomies, Classifications, and Categories

Type	Cable Cutter
------	--------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Capacity	Up To 750 MCM Hard-Drawn Copper, Up To 1000 MCM Aluminum
----------	--