

# ETP Steel EMT Compression Connectors

## 7000S Series Connectors

### Application

- To ground and secure EMT raceways to boxes and enclosures.

### Features

- Male hub threads — NPS.
- Available with insulated throat.
- Concretetight.
- Insulated throat connector rated 90 °C.

### Material/Finish

- Body and nut: steel
- Steel/zinc plated

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14815, E14814
- cUL Listed: E14815
- CSA Standard: C22.2 No. 18.3
- NEMA: FB-1



7050S – 7400S

Trade Size (Inches)	Catalog Number	Insulated Throat Catalog Number	Dimensions in Inches/Millimeters			Weight Lbs./Kgs. Per 100
			Body Length	Maximum Diameter	Thread Length	
1/2	7050S	7050ST	1.13/28.7	1.06/26.9	0.38/9.7	15.00/6.80
3/4	7075S	7075ST	1.03/26.2	1.25/31.8	0.44/11.2	21.00/9.53
1	7100S	7100ST	1.25/31.8	1.56/39.6	0.44/11.2	32.00/14.51
1-1/4	7125S	7125ST	1.81/46.0	2.00/50.8	0.56/14.2	72.00/32.66
1-1/2	7150S	7150ST	2.00/50.8	2.19/55.6	0.56/14.2	85.00/38.56
2	7200S	7200ST	2.25/57.2	2.69/68.3	0.69/17.5	124.00/56.25
2-1/2 *	7250S	7250ST	2.38/60.5	3.34/84.8	0.88/22.4	160.00/72.57
3 *	7300S	7300ST	2.88/73.2	4.00/101.6	0.88/22.4	265.00/120.20
3-1/2 *	7350S	7350ST	3.00/76.2	4.50/114.3	1.00/25.4	425.00/192.78
4 *	7400S	7400ST	3.19/81.0	5.06/128.5	1.00/25.4	600.00/272.16

\* Rated for steel EMT, aluminum and steel RMC, and steel IMC.

# ETP Steel EMT Compression Connectors

## 7000S Series Connectors

### Application

- To ground and secure EMT raceways to boxes and enclosures.

### Features

- Male hub threads — NPS.
- Available with insulated throat.
- Concretetight.
- Insulated throat connector rated 90 °C.

### Material/Finish

- Body and nut: steel
- Steel/zinc plated

### Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14815, E14814
- cUL Listed: E14815
- CSA Standard: C22.2 No. 18.3
- NEMA: FB-1



7050S – 7400S

Trade Size (Inches)	Catalog Number	Insulated Throat Catalog Number	Dimensions in Inches/Millimeters			Weight Lbs./Kgs. Per 100
			Body Length	Maximum Diameter	Thread Length	
1/2	7050S	7050ST	1.13/28.7	1.06/26.9	0.38/9.7	15.00/6.80
3/4	7075S	7075ST	1.03/26.2	1.25/31.8	0.44/11.2	21.00/9.53
1	7100S	7100ST	1.25/31.8	1.56/39.6	0.44/11.2	32.00/14.51
1-1/4	7125S	7125ST	1.81/46.0	2.00/50.8	0.56/14.2	72.00/32.66
1-1/2	7150S	7150ST	2.00/50.8	2.19/55.6	0.56/14.2	85.00/38.56
2	7200S	7200ST	2.25/57.2	2.69/68.3	0.69/17.5	124.00/56.25
2-1/2 *	7250S	7250ST	2.38/60.5	3.34/84.8	0.88/22.4	160.00/72.57
3 *	7300S	7300ST	2.88/73.2	4.00/101.6	0.88/22.4	265.00/120.20
3-1/2 *	7350S	7350ST	3.00/76.2	4.50/114.3	1.00/25.4	425.00/192.78
4 *	7400S	7400ST	3.19/81.0	5.06/128.5	1.00/25.4	600.00/272.16

\* Rated for steel EMT, aluminum and steel RMC, and steel IMC.