

# Eaton 3BR3030N100

Catalog Number: 3BR3030N100

Eaton BR convertible loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Convertible main, 100 A, D1, Aluminum, Cover included, NEMA1, Metallic, 10 kAIC, BR, Combination, 30 Circuits, 30 Spaces, Four-wire, Three-phase, 208 Y/120, 240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR convertible loadcenter	3BR3030N100
<b>UPC</b>	<b>Product Length/Depth</b>
786676442909	3.88 in
<b>Product Height</b>	<b>Product Width</b>
29.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
20 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	The maximum rating of the panel is the main breaker rating when used as service entrance equipment. Has notch for brhdk125 hold-down kit.

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs, includes BREQS125 hold-down screw

### Type

Convertible main

### Amperage Rating

100 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

30

### Number of spaces

30

### Phase

Three-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

208Y/120, 240V

### Wire size

Determined by circuit breaker installed

### Box size

D1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, BR CONVERTIBLE, INDOOR  
NEMA 1, 120/240 VAC, 3 PHASE

### Specifications and datasheets

Eaton Specification Sheet - 3BR3030N100

3-Phase Loadcenter Program

Number of wires

4



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)