

## T12 Plastic-Coated, Shatterproof Fluorescent Lamps

### Instant Start Slimline T12 Fluorescent Lamps Single Pin

Nominal Lamp Watts	UPC/Catalog Order#	Ordering Description	Std. Pkg. Qty.	Lamp Description	Nominal Length (Inches)	Avg. Life (Hours)	Mean Lumens
20	25010	F24T12/CW	24	COOL WHITE	24	7,500	960
30	29010	F36T12/CW	24	COOL WHITE	36	7,500	1,800
35	33019	F42T12/CW	24	COOL WHITE	42	7,500	1,920
39	34018	F48T12/CW/ALTO	30	COOL WHITE	48	9,000	2,680
	34028	F48T12/D/ALTO	30	DAYLIGHT	48	9,000	2,600
	34038	F48T12/WW/ALTO	30	WARM WHITE	48	9,000	2,650
	34260	F48T12/SPEC35	30	3500K, SPEC	48	9,000	2,800
	34230	F48T12/41U	30	4100K, ULTRALUME	48	9,000	2,950
50	35010	F60T12/CW	15	COOL WHITE	60	12,000	3,050
	35020	F60T12/D	15	DAYLIGHT	60	12,000	2,850
51	38010	F64T12/CW	15	COOL WHITE	64	12,000	3,540
	38020	F64T12/D	15	DAYLIGHT	64	12,000	2,800
56	40018	F72T12/CW/ALTO	15	COOL WHITE	72	12,000	4,140
	40028	F72T12/D/ALTO	15	DAYLIGHT	72	12,000	3,350
	40038	F72T12/WW/ALTO	15	WARM WHITE	72	12,000	4,000
	40260	F72T12/SPEC35	15	3500K, SPEC	72	12,000	4,400
	40218	F72T12/30U/ALTO	15	3000K, ULTRALUME	72	12,000	4,400
	40228	F72T12/35U/ALTO	15	3500K, ULTRALUME	72	12,000	4,550
	40238	F72T12/41U/ALTO	15	4100K, ULTRALUME	72	12,000	4,510
75	44010	F96T12/CW	15	COOL WHITE	96	12,000	5,660
	44020	F96T12/D	15	DAYLIGHT	96	12,000	3,950
	44040	F96T12/CWX	15	COOL WHITE DELUXE	96	12,000	3,950
	44080	F96T12/N	15	NATURAL	96	12,000	3,850
	44150	F96T12/C50	15	COLORTONE 50	96	12,000	4,200
	44258	F96T12/SPEC30/ALTO	15	3000K, SPEC	96	12,000	6,050
	44268	F96T12/SPEC35/ALTO	15	3500K, SPEC	96	12,000	6,050
	44278	F96T12/SPEC41/ALTO	15	4100K, SPEC	96	12,000	6,050
	44218	F96T12/30U/ALTO	15	3000K, ULTRALUME	96	12,000	6,225
	44228	F96T12/35U/ALTO	15	3500K, ULTRALUME	96	12,000	6,225
	44238	F96T12/41U/ALTO	15	4100K, ULTRALUME	96	12,000	6,225
	44248	F96T12/50U/ALTO	15	5000K, ULTRALUME	96	12,000	6,125

### Energy-Saving Instant Start Slimline T12 Fluorescent Lamps Single Pin

Nominal Lamp Watts	UPC/Catalog Order#	Ordering Description	Std. Pkg. Qty.	Lamp Description	Nominal Length (Inches)	Avg. Life (Hours)	Mean Lumens
30	\$ 34016	F48T12/CW/ES/ALTO	30	COOL WHITE	48	9,000	2,150
	\$ 34266	F48T12/SPEC35/ES/ALTO	30	3500K, SPEC	48	9,000	2,350
	\$ 34276	F48T12/SPEC41/ES/ALTO	30	4100K, SPEC	48	9,000	2,350
60	\$ 44011	F96T12/CW/ES	15	COOL WHITE	96	12,000	4,750
	ⓔ \$ 44016	F96T12/CW/ES/ALTO	15	COOL WHITE	96	12,000	4,750
	\$ 44028	F96T12/DX/ES/ALTO	15	DAYLIGHT DELUXE	96	12,000	3,675
	ⓔ \$ 44036	F96T12/WW/ES/ALTO	15	WARM WHITE	96	12,000	4,850
	\$ 44151	F96T12/C50/ES	15	COLORTONE 50	96	12,000	3,700
	ⓔ \$ 44251	F96T12/SPEC30/ES/ALTO	15	3000K, SPEC	96	12,000	5,400
	ⓔ \$ 44266	F96T12/SPEC35/ES/ALTO	15	3500K, SPEC	96	12,000	5,400
	ⓔ \$ 44276	F96T12/SPEC41/ES/ALTO	15	4100K, SPEC	96	12,000	5,400
	ⓔ \$ 44216	F96T12/30U/ES/ALTO	15	3000K, ULTRALUME	96	12,000	5,550
	ⓔ \$ 44226	F96T12/35U/ES/ALTO	15	3500K, ULTRALUME	96	12,000	5,550
	ⓔ \$ 44236	F96T12/41U/ES/ALTO	15	4100K, ULTRALUME	96	12,000	5,550
	ⓔ \$ 44246	F96T12/50U/ES/ALTO	15	5000K, ULTRALUME	96	12,000	5,500

\$ – Energy-Saving Product

ⓔ – This bulb meets U.S. Federal minimum efficiency standards.

ALTO® – Reduced Mercury Lamps

■ – Features ALTO® Lamp Technology

Footnotes located on page 28

**NOTE** – Energy-Saving lamps are not intended for use in ambient temperatures below 60°F, in drafty locations, on low power factor ballasts, reduced current and light output ballasts, dimming ballasts, or on inventor powered emergency lighting systems. (3)