



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 442G 12" Tongue & Groove V Jaw

*Channellock, Inc.*

Catalog Number	442G
Manufacturer	Channellock, Inc.
Description	Tongue and Groove Pliers, Grooved, Tongue Type; C1080 High Carbon Steel Material; 12 Inch Overall Length; 1.5 Inch Jaw Length; 0.5 Inch Jaw Width; Cutting Application; Heat Treated Process; 2.25 Inch Capacity; Plastic Grip Handle Material
Weight per unit	1.3 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Jaw Length	1.5 Inch
Jaw Type	V
Jaw Width	0.5 Inch
Material	C1080 High Carbon Steel
Process	HEAT TREATED

### Material, Color, and Finish

Handle Color	CHANNELLOCK BLUE[R]
Handle Material	PLASTIC GRIP

### Dimensions and Weight

Overall Length	12 INCH
----------------	---------

### Descriptions

Additional Information	ITEMS/FEATURES (7) STEPS ADJUSTMENTS, PERMALOCK[R] FASTENER, RIGHT ANGLE TEETH, REINFORCED EDGE
Commodity Description	PLRS,WRNCH,DRV,SAW,POUCH,TOOL BOX
Description	12" TONGUE & GROOVE V JAW
Long Description	TONGUE AND GROOVE PLIERS, GROOVED, TONGUE TYPE; C1080 HIGH CARBON STEEL MATERIAL; 12 INCH OVERALL LENGTH; 1.5 INCH JAW LENGTH; 0.5 INCH JAW WIDTH; CUTTING APPLICATION; HEAT TREATED PROCESS; 2.25 INCH CAPACITY; PLASTIC GRIP HANDLE MATERIAL
Product Type	Tongue and Groove Pliers

### Manufacturer Information

Brand	Channellock, Inc.
GTIN	00025582301871
UPC	025582301871

### Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	GROOVE JOINT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	20
Weight Per each	1.2999

## Uses, Certifications, and Standards

Application	CUTTING
Capacity	2.25 Inch


# CHANNEL LOCK

WORK HARD. SWEAT BLUE.®

## SMOOTH JAW


### Features

- Smooth jaws for non-marring surfaces (PVC pipe, chromes, etc.).
- Mâchoires lisses pour surfaces non rayables (tuyaux PVC, chromes, etc.)
- Mordazas lisas que no dañan las superficies (para tuberías de PVC, cromos, etc.).




PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		H HANDLE SPAN		WEIGHT		NUMBER OF ADJUSTMENTS	JAW CAPACITY	
	in	mm	in	mm	in	mm	in	mm	pounds	grams		in	mm
415	10.00	254.00	1.38	35.05	0.44	11.18	2.13	54.10	0.98	444.52	7	2.00	50.80

## V-JAW




### Features

- V-Jaws give you more points of contact on round stock and tubing.
- Les mâchoires en V augmentent le nombre de points de contact sur les pièces arrondies et sur les tuyaux.
- Las mordazas en V le ofrecen más puntos de contacto para materiales y tubos redondos.



PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		H HANDLE SPAN		WEIGHT		NUMBER OF ADJUSTMENTS	JAW CAPACITY	
	in	mm	in	mm	in	mm	in	mm	pounds	grams		in	mm
483	20.25	514.35	3.19	81.03	0.54	13.72	2.94	74.68	3.74	1696.44	12	5.50	139.70
463	16.50	419.10	1.08	27.43	0.48	12.19	1.93	49.02	2.71	1229.23	8	4.25	107.95




PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		H HANDLE SPAN		WEIGHT		NUMBER OF ADJUSTMENTS	JAW CAPACITY	
	in	mm	in	mm	in	mm	in	mm	pounds	grams		in	mm
442	12.00	304.80	1.50	38.10	0.50	12.70	1.69	42.93	1.78	807.39	7	2.25	57.15
432	10.00	254.00	1.37	34.80	0.43	10.92	2.20	55.88	0.95	430.91	7	2.00	50.80
422	9.50	241.30	1.12	28.45	0.47	11.94	1.57	39.88	0.84	381.02	5	1.50	38.10

## NARROW NOSE

### Features

- Air brake tool
- Easy brake clearance check for automatic or manual slack adjusters.
- Outil à frein pneumatique
- Vérification de jeu pour rattrapeurs d'usure automatiques ou manuels.
- Herramienta para ajustar los frenos de aire
- Perfil delgado para los ajustadores de freno automático y manual.



PLIER	A OVERALL LENGTH		B JAW LENGTH		C JOINT THICKNESS		H HANDLE SPAN		WEIGHT		NUMBER OF ADJUSTMENTS	JAW CAPACITY	
	in	mm	in	mm	in	mm	in	mm	pounds	grams		in	mm
444	12.00	304.80	1.50	38.10	0.34	8.64	1.81	45.97	1.64	743.89	7	2.25	57.15

Patent Pending

