Effective January 2014

ARROW/HART

Industrial grade 20A Non-NEMA locking devices

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Туре:



9965C



7314C



7310B



7328N

Description

Non-NEMA 20A, 125/250V/AC, 3P-3W



Receptacle Plug

Design features for plug & connector

- All nylon construction
- EPDM gasket seals cord hole from dust and debris
- Back wire terminal clamps for easy secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires
- Clear cover over wiring compartments allows easy inspection of wiring terminations
- Rating printed on side of device
- · Largest-in-class grommet size allows for entire cord size range

Design features for receptacle

- Rugged glass filled nylon body
- Clearly marked rating, NEMA configuration and approval listings on receptacle face
- One piece brass contacts offer superior performance and minimum heat rise
- · Back and side wiring terminal clamps for easy, secure wiring

Design features for flanged inlet & outlet

- All nylon construction
- Mounting holes interchangeable with competitive units
- · Back wire terminal clamps for easy, secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires

Table 1. Non-NEMA 20A Industrial Grade Locking Devices

Catalog No.	Description	Amps	Volts	Color
□ 9965C	Safety grip plug	20	125/250	Gray
□7314C	Safety grip connector	20	125/250	Gray
□ 7310B	Single receptacle	20	125/250	Black
□ 7328N	Flanged outlet	20	125/250	Gray
🗆 7327N	Flanged inlet	20	125/250	Gray

Compliances, specifications and availability are subject to change without notice.



Project Name:		Prepared By:
	Project Number:	Date:
	Catalog Number:	Туре:

Plug & Connector

Non-NEMA 20A, 125/250V/AC, 3P-3W

Table 2. Specifications

Catalog No.	Non-NEMA 20A Plug & Connector	
NEMA Config	Non-NEMA 20A	
Wiring Type	Back wire	
Environmental Specifications	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C to 60°C (-40°F to 140°F)	
Electrical Specifications Dielectric Voltage: Twice the device rating + 1000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated curre		
Mechanical Specifications	Terminal Accommodation: #16 - #8 AWG Voltage Ratings: Permanently marked on device	

Table 3. Materials

Catalog No.	Non-NEMA 20A Plug & Connector
NEMA Config	Non-NEMA 20A
Outer Shell	Nylon
Interior Body	Nylon
Terminal Retainer	Polycarbonate
Blades	Brass
Line Contacts	Brass, connectors: tin plated
Terminal Clamps	Steel
Terminal Screws	#8-32 brass, zinc plated (neutral screw)
Ground Screw	#8-32 brass plated (green)
Assembly Screws	Steel, nickel plated
Gasket/Dust Shield	EPDM
Cord Clamp Screws	Steel, nickel plated
Cord Clamp	Nylon

Product Dimensions




Figure 1. 9965C

Figure 2. 7314C

Compliances, specifications and availability are subject to change without notice.

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Single Receptacle

Non-NEMA 20A, 125/250V/AC, 3P-3W

Table 4. Specifications

Catalog No.	Non-NEMA 20A Single Receptacle	
NEMA Config	Non-NEMA 20A	
Wiring Type	Back & side wire	
Environmental Specifications	Flammability: Meets UL94 requirements; V0 rated Temperature Rating: -40°C to 60°C (-40°F to 140°F)	
Electrical Specifications	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	
Mechanical Specifications	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	

Table 5. Materials

Catalog No.	Non-NEMA 20A Single Receptacle
NEMA Config	Non-NEMA 20A
Face	Glass-filled nylon
Base	Glass-filled nylon
Mounting Strap	0.050" thick steel, zinc plated
Line Contacts	0.031" thick brass
Terminal Screws	#8-32 brass, nickel plated (neutral screw)
Ground Screw	#8-32 brass (green)
Terminal Clamps/Plates	0.070" thick steel
Ground Contacts	0.041" thick brass
Back Plate	0.041" thick brass, nickel plated
Mounting Screws	Steel, zinc plated

Product Dimensions




Figure 3. 7310B

Compliances, specifications and availability are subject to change without notice.

Project Name:		Prepared By:
Project Number:		Date:
	Catalog Number:	Туре:

Flanged Outlet & Inlet

Non-NEMA 20A, 125/250V/AC, 3P-3W

Table 6. Specifications

Catalog No.	Non-NEMA 20A Flanged Outlet	Non-NEMA 20A Flanged Inlet
NEMA Config	Non-NEMA 20A	Non-NEMA 20A
Wiring Type	Back wire	Back wire
Environmental Specifications	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C to 60°C (-40°F to 140°F)
Electrical Specifications	Dielectric Voltage: <300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) @ maximum rated current (DC)
Mechanical Specifications	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device

Table 7. Materials

Catalog No.	Non-NEMA 20A Flanged Outlet	Non-NEMA 20A Flanged Inlet	
NEMA Config	Non-NEMA 20A	Non-NEMA 20A	
Outer Shell	Nylon	Nylon	
Interior Body	Nylon	Nylon	
Terminal Retainer	Polycarbonate	Polycarbonate	
Blades	N/A	0.062" thick brass	
Line Contacts	0.031" thick brass	N/A	
Terminal Clamps	Steel	Steel	
Terminal Screws	#8-32 brass, nickel plated (neutral screw)	#8-32 brass, nickel plated (neutral screw)	
Ground Screw	#8-32 brass (green)	#8-32 brass (green)	
Assembly Screws	Steel, zinc plated	Steel, zinc plated	
Mounting Screws	Steel, zinc plated	Steel, zinc plated	

Product Dimensions




Figure 4. 7328N

Figure 5. 7327N



Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Туре:

Certifications & Compliances

Catalog No.		c (UL) us	(h)	9	
9965C		•		•	•
7314C		•		•	•
7310B			٠		٠
7328N			٠		٠
7327N		•		•	•
KEY:	c (UL) us	cULus		(III)	UL

@ Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Compliances, specifications and availability are subject to change without notice.

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Arrowhart.com Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Arrowhart.com Electrical Sector Mexico Operations Carr. Tlalnepantla -Cuautitlan Km 17.8 s/n Col. Villa Jardin esq. Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800 Mexico Eaton.mx Arrowhart.com

Eaton

1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

© 2014 Eaton All Rights Reserved Printed in USA Publication No. 125-0089-13 January 2014

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

