



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 461DC 3/4" Emt Set Screw ZN PLT CPLG *Crouse-Hinds*

Catalog Number	461DC
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Emt Set Screw Type Coupling, Emt, Zinc Die Cast, 3/4"
Weight per unit	0.0700 (lbs/each)
Product Category	Die Cast Straight Set Screw Em

### Features

dimensions	4.9500 IN X 3.4300 IN X 1.9400 IN
------------	-----------------------------------

### Descriptions

Description	3/4" EMT SET SCREW ZN PLT CPLG
extra long description	MIDWEST 461DC 3/4 EMT SS CPL DC
Features	Crouse-Hinds series EMT connectors and couplings are used to join EMT conduit to a box or enclosure, or to couple two ends of EMT conduit. Our EMT fittings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in steel and zinc die cast. Crouse-Hinds series EMT connectors and couplings are also available painted in seven different colors to better match architectural specifications and preferences.
Long Description	Eaton Crouse-Hinds series EMT set screw type coupling, EMT, Zinc die cast, 3/4"
Product Type	3/4 Emt SS CPL DC
Special Features	Concrete Tight

### Manufacturer Information

Brand	Crouse-Hinds
GTIN	00784564003973
Manufacturers Part Number	461DC
UPC	784564003973

### Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	Set screw type coupling

### Trade Size

Trade Size	3/4 in
------------	--------

### Packaging

Carton	25
Weight Per each	0.07



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

standard

UL, cUL