



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49109112 Open-Lok 6PC Multi-Tool Blade Kit

Milwaukee Electric Tool

Catalog Number	49109112
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Universal Fit Open-Lok 6-Piece Oscillating Multi-Tool General Purpose Blade Kit Provides An Assortment For Cuts In Hardwood, Wood & Nails, Wood, PVC, and Drywall. The Included Titanium Enhanced Bi-Metal Blades Use Premium High-Speed Steel and Last Up to 15X Longer Than Standard High Carbon Steel (HCS) Blades. The Bi-Metal Blade Is Ideal For Smooth Cuts In Wood With Nails, PVC, and Drywall. The Triple Ground Japanese Tooth Blades Deliver Up to 2X Faster Cuts Than The Previous Milwaukee HCS B
Weight per unit	0.7300 (lbs/each)
Product Category	Tools & Testers

Descriptions

Description	OPEN-LOK 6PC MULTI-TOOL BLADE KIT
Features	Milwaukee® OPEN-LOK 6PC MULTI-TOOL BLADE KIT
Long Description	The MILWAUKEE® Universal Fit OPEN-LOK 6-Piece Oscillating Multi-Tool General Purpose Blade Kit provides an assortment for cuts in hardwood, wood & nails, wood, PVC, and drywall. The included Titanium Enhanced Bi-Metal Blades use premium high-speed steel and last up to 15X longer than standard high carbon steel (HCS) blades. The bi-metal blade is ideal for smooth cuts in wood with nails, PVC, and drywall. The Triple Ground Japanese Tooth Blades deliver up to 2X faster cuts than the previous Milwaukee HCS b
Product Type	6PC Multi-Tool Blade Kit

Manufacturer Information

Brand	milwaukee
GTIN	00045242586479
Manufacturers Part Number	49-10-9112
sub brand	OPEN-LOK? ?
UPC	045242586479

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Multi-Tool Blades

Packaging

Carton	1
Weight Per each	0.73



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

All-Purpose