



**Product Number:** 58327

**Order Abbreviation:** 50MR16/FL35/C(EXN) 12V

**General Description:** Tungsten Halogen Tru-Aim MR16 STANDARD Axial Filament UV-Filter Dichroic Reflector Cover Glass GU5.3 Bi-Pin Base 50Watt 12Volt Flood Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	50MR16FL35CEXN 12V 20/CS 1/SKU
ANSI Code	EXN
Average Rated Life (hr)	2000
Base	GU5.3 Bipin
Beam Angle (deg)	36
Beam Type	WFL
Bulb	MR16
Centerbeam Candlepower (cp)	1450
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2950
Diameter (in)	2.008
Diameter (mm)	51.00
Ecologic	YES
Family Brand Name	TRU-AIM Standard
Filament	AXIAL
Horizontal Beam Angle (deg)	35
Lamp Finish	Covered
Maximum Overall Length - MOL (in)	1.750
Maximum Overall Length - MOL (mm)	45.0
Nominal Voltage (V)	12.00
Nominal Wattage (W)	50.00
Vertical Beam Angle (deg)	35



#### Footnotes

- UV Filter capsul with axial filament in covered dichroic reflector.
- Max. seal temperature 370 C (662F)
- Max pin temperature 250 C.
- Max temperature at lens reflector joint 240 C.
- Suitable for use in unshielded fixtures. Consult most recent luminaire standards for your area to determine luminaire requirements.



**Product Number:** 58327

**Order Abbreviation:** 50MR16/FL35/C(EXN) 12V

**General Description:** Tungsten Halogen Tru-Aim MR16 STANDARD Axial Filament UV-Filter Dichroic Reflector Cover Glass GU5.3 Bi-Pin Base 50Watt 12Volt Flood Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	50MR16FL35CEXN 12V 20/CS 1/SKU
ANSI Code	EXN
Average Rated Life (hr)	2000
Base	GU5.3 Bipin
Beam Angle (deg)	36
Beam Type	WFL
Bulb	MR16
Centerbeam Candlepower (cp)	1450
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2950
Diameter (in)	2.008
Diameter (mm)	51.00
Ecologic	YES
Family Brand Name	TRU-AIM Standard
Filament	AXIAL
Horizontal Beam Angle (deg)	35
Lamp Finish	Covered
Maximum Overall Length - MOL (in)	1.750
Maximum Overall Length - MOL (mm)	45.0
Nominal Voltage (V)	12.00
Nominal Wattage (W)	50.00
Vertical Beam Angle (deg)	35



#### Footnotes

- UV Filter capsul with axial filament in covered dichroic reflector.
- Max. seal temperature 370 C (662F)
- Max pin temperature 250 C.
- Max temperature at lens reflector joint 240 C.
- Suitable for use in unshielded fixtures. Consult most recent luminaire standards for your area to determine luminaire requirements.