

## Miniature Lamps (Alphanumeric)

Item	Order Code	Amps	Volts	Base	Filament	MOL in/mm	MOD in/mm	Life
<b>577</b>	42082	1.4	12.8	Double End Cap	C-8	1.72/43.7	0.62/15.8	1,000
<b>577-BP</b>	42080	1.4	12.8	Double End Cap	C-8	1.72/43.7	0.62/15.8	1,000
<b>578</b>	06699	0.78	12.8	Double End Cap	C-8	1.72/43.7	0.38/9.6	1,000
<b>578-BP</b>	06700	0.97	12.8	Double End Cap	C-8	1.72/43.7	0.38/9.6	1,000
<b>579</b>	06702	0.80	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	200
<b>579-BP</b>	06703	0.80	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	200
<b>585</b>	40759	0.04	28	W2.1x9.5d	C-2F	1.06/26.9	0.40/10.2	7,000
<b>605</b>	40826	0.5	6.15	E10	C-2R	1.07/27.2	0.59/15.0	15
<b>623</b>	40828	0.37	28	BA15s	2C-6	1.44/36.6	0.75/19.1	1,000
<b>624</b>	40829	0.37	28	BA15d	2C-6	1.44/36.6	0.75/19.1	1,000
<b>631</b>	40832	0.63	14	BA15s	C-6/C-6	1.44/36.6	0.75/19.1	1,000
<b>631-BP</b>	40833	0.63	14	BA15s	C-6/C-6	1.44/36.6	0.75/19.1	1,000
<b>655</b>	49620	0.20	28	W2.1x9.5d	C-2F	1.06/26.9	0.40/10.2	7,000
<b>656</b>	40836	0.06	28	W2.1x9.5d	C-2F	1.06/26.9	0.40/10.2	2,500
<b>657</b>	40837	0.08	28	W2.1x9.5d	C-2F	1.06/26.9	0.40/10.2	15,000
<b>658</b>	42272	0.08	14	W2.1x9.5d	C-2F	1.06/26.9	0.40/10.2	15,000
<b>658-BP</b>	42086	0.08	14	W2.1x9.5d	C-2F	1.06/26.9	0.40/10.2	15,000
<b>680</b>	40852	0.06	5	WL	C-2R	0.25/6.4	0.13/3.2	60,000
<b>683</b>	40856	0.06	5	WL	C-2R	0.25/6.4	0.13/3.2	25,000
<b>685</b>	40872	0.06	5	SX4s	C-2R	0.38/9.7	0.13/3.2	25,000
<b>715</b>	40884	0.115	5	WL	C-2R	0.25/6.4	0.13/3.2	40,000
<b>718</b>	81173	0.115	5	SX4s	C-2R	0.38/9.7	0.13/3.2	40,000
<b>755</b>	40932	0.15	6.3	BA9s	C-2R	1.19/30.2	0.43/11.0	20,000
<b>755-BP</b>	16052	0.15	6.3	BA9s	C-2R	1.19/30.2	0.43/11.0	20,000
<b>756</b>	40934	0.08	14	BA9s	C-2F	1.19/30.2	0.43/11.0	15,000
<b>757</b>	40936	0.08	28	BA9s	C-2F	1.19/30.2	0.40/10.2	15,000
<b>757-BP</b>	42362	0.08	28	BA9s	C-2F	1.19/30.2	0.40/10.2	15,000
<b>778</b>	41400	3.33	6	G4	C-6	1.05/26.7	0.38/9.6	100
<b>787</b>	41402	1.67	6	G4	C-6	1.00/25.4	0.30/7.6	100
<b>788</b>	41404	3.33	6	G4	C-6	1.00/25.4	0.30/7.6	100
<b>789</b>	41406	1.17	12	G4	C-6	1.05/26.7	0.38/9.6	200
<b>795</b>	44019	3.91	12.8	BA15s	C-6	2.50/63.5	0.48/12.2	200
<b>795X</b>	44021	3.91	12.8	BA15s	C-8	2.50/63.5	0.48/12.2	200
<b>796</b>	44023	2.73	12.8	BA15s	C-6	2.50/63.5	0.48/12.2	300
<b>797</b>	00447	3.91	12.8	G7.1	C-6	1.9/48.3	0.5/13	200
<b>882</b>	42100	0.35	12.8	B10d	C-6	1.18/30.0	0.72/18.3	2,000
<b>891</b>	42116	0.625	12.8	G4	C-6	1.20/30.5	0.32/8.1	800
<b>895</b>	41004	0.53	40	BA15d	CC-6	2.00/50.8	1.04/26.4	3,800
<b>901</b>	42141	0.31	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	500
<b>901A</b>	43201	0.31	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	500
<b>901B</b>	43204	0.31	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	500
<b>901-BP</b>	42143	0.31	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	500
<b>901G</b>	43207	0.31	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	500
<b>901R</b>	43210	0.31	12.8	W2.1x9.5d	C-2R	1.49/37.9	0.62/15.8	500
<b>904</b>	41010	0.69	13.5	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	5,000
<b>904-BP</b>	42206	0.69	13.5	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	5,000
<b>906</b>	41012	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000
<b>906A</b>	01814	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000
<b>906B</b>	00358	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000
<b>906-BP</b>	42142	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000
<b>906G</b>	00356	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000
<b>906P</b>	06011	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000
<b>906R</b>	00357	0.69	13	W2.1x9.5d	C-2F	1.49/37.9	0.62/15.8	1,000