



Industrial Specification Grade Straight Blade Plugs & Connectors

2-Pole, 3-Wire Grounding
15A, 125V/AC
NEMA 5-15




6266



5269N



5969BLK



14W47



1547

Industrial Grade Dimensional Information: B-18

Specification Information:

Safety Grip Industrial Plugs & Connectors: B-26

AutoGrip Industrial Plugs & Connectors: B-26

Corrosion Resistant AutoGrip Industrial Plugs & Connectors: B-29

QuickGrip Plugs & Connectors: B-26

Watertight Industrial Plugs & Connectors: B-28

Severe Duty Industrial Plugs & Connectors: B-29

Industrial Grade Plugs & Connectors

Safety Grip™ NEMA 5-15



Rating	A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
15	125		Straight Body 0.33-0.66" (6.4-16.7mm)	Black & White	<input type="checkbox"/> 6266	<input checked="" type="checkbox"/> 6269	<input checked="" type="checkbox"/> 6269
			Straight Body 0.33-0.66" (6.4-16.7mm)	Black	<input type="checkbox"/> 6266BLK	<input checked="" type="checkbox"/> 6269BLK	<input checked="" type="checkbox"/> 6269BLK
			Angled Body 0.33-0.66" (7.6-16.7mm)	Black & White	<input type="checkbox"/> 6265	<input checked="" type="checkbox"/>	<input type="checkbox"/>

AutoGrip™ NEMA 5-15



Rating	A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
15	125		Straight Body 0.33-0.66" (6.4-16.7mm)	Black & White	<input type="checkbox"/> 5266N	<input checked="" type="checkbox"/> 5269N	<input checked="" type="checkbox"/> 5269N
			Corrosion Resistant, Straight Body 0.33-0.66" (6.4-16.7mm)	Yellow	<input type="checkbox"/> 5266NCR	<input checked="" type="checkbox"/> 5269NCR	<input checked="" type="checkbox"/> 5269NCR

QuickGrip™ NEMA 5-15



Rating	A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
15	125		Straight Body 0.23-0.72" (5.8-18.3mm)	Black	<input type="checkbox"/> 5965BLK	<input checked="" type="checkbox"/> 5969BLK	<input checked="" type="checkbox"/> 5969BLK

Watertight NEMA 5-15



Rating	A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
15	125		Straight Body 0.30-0.65" (7.6-16.5mm)	Yellow	<input type="checkbox"/> 14W47	<input checked="" type="checkbox"/> 15W47	<input checked="" type="checkbox"/> 15W47
			Straight Body 0.30-0.65" (7.6-16.5mm)	Black	<input type="checkbox"/> 14W47BK	<input checked="" type="checkbox"/> 15W47BK	<input checked="" type="checkbox"/> 15W47BK

Severe Duty NEMA 5-15



Rating	A	V/AC	Product Type & Cord Diameter	Color	Plug	Catalog No.	Connector
15	125		Straight Body 0.38-1.00" (19.1-25.4mm)	Yellow & Black	<input type="checkbox"/> 1447	<input checked="" type="checkbox"/> 1547	<input checked="" type="checkbox"/> 1547

Icon Key

NAFTA Compliant - see page O-30

Accessories for Industrial Grade NEMA 5-15 Plugs & Connectors

Description	Catalog No.
Watertight plug closure cap for 15A plug	<input type="checkbox"/> 14W <input checked="" type="checkbox"/>
Replacement watertight connector closure cap for 15A connector	<input type="checkbox"/> 15W <input checked="" type="checkbox"/>
Wire mesh grip for 15A watertight plugs & connectors, 0.30-0.50" (7.6-12.7mm) cord dia.	<input type="checkbox"/> WM115 <input checked="" type="checkbox"/>
Wire mesh grip for 15A watertight plugs & connectors, 0.50-0.62" (12.7-15.8mm) cord dia.	<input type="checkbox"/> WM116 <input checked="" type="checkbox"/>



14W



15W



WM115



WM116

**Industrial Specification Grade
 Plugs & Connectors**

2-Pole, 3-Wire Grounding
 3-Pole, 3-Wire Non-Grounding
 4-Pole, 4-Wire Non-Grounding

	Device Type	Industrial Grade Safety Grip™ Plugs & Connectors, Straight Blade	Industrial Grade AutoGrip™ Plugs & Connectors, Straight Blade	Industrial Grade QuickGrip™ Plugs & Connectors, Straight Blade	
	Wiring Type	Back wire	Back wire	Back wire	
	Testing & Code Compliance	<ul style="list-style-type: none"> cULus listed to UL 498, file no. E3663 Complies with Federal Spec. WC-596F CSA certified to C22.2, no. 42-99 file no. 7087 (6221-02) 7251N: NOM certified 	<ul style="list-style-type: none"> Listed to UL 498, file no. E3663 UL verified to Fed Spec WC-596F except cat. no. 5266AN CSA certified to C22.2, no. 42-99 file no. 2081 (6221-02) 	<ul style="list-style-type: none"> cULus listed to UL 498, file no. E146159 UL verified to Federal Spec. WC-596F 	
Specifications: Environmental		Flammability	Meets UL94 requirements, V2 rated	Meets UL94 requirements, V2 rated	Meets UL94 requirements, V2 rated
		Temperature Rating	-40°C to 75°C (-40°F to 167°F)	-40°C to 75°C (-40°F to 167°F)	-40°C to 75°C (-40°F to 167°F)
Specifications: Electrical		Dielectric Voltage	Withstands 1500V per UL 498, except 6260 & 6760 Series: 1250V, 7624N: 1554V, 7251N: 4160V	Withstands 1500V per UL 498	Withstands 1500V per UL 498
	Current Interrupting	Yes, at full-rated current	Yes, at full-rated current	Yes, at full-rated current	
	Temperature Rise	Max. 30°C (86°F) after 200 cycles of overload @ 200% of rated current (DC)	Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	
Specifications: Mechanical	Terminal Accommodation	#16 - #12 AWG, except 7624N, 9151N, 7251N: #18 - #10 AWG	#18 - #12 AWG	#18 - #12 AWG	
	Voltage Ratings	Permanently marked on device	Permanently marked on device	Permanently marked on device	
Materials:	Plug/Connector Outer Shell	Nylon	Nylon	Nylon	
	Interior Body	Nylon	Nylon	Nylon	
	Terminal Retainer	Polycarbonate	Polycarbonate	N/A	
	Blades	0.065" thick brass	0.065" thick brass	0.060" thick brass	
	Line Contacts	0.031" thick brass	0.031" thick brass	0.032" thick brass	
	Terminal Clamps	Steel, zinc plated	Steel, zinc plated	Brass	
	Terminal Screws	#8-32 brass, nickel plated	#8-32 brass, nickel plated	Steel, brass plated (hot) and zinc plated (neutral)	
	Ground Contact	0.041" thick brass	0.041" thick bronze	N/A	
	Ground Screw	#8-32 brass, zinc plated, green	#8-32 brass, green	Steel, zinc plated, green	
	Assembly/ Mounting Screws	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated	
	Cord Clamp	Nylon	Polypropylene	Nylon	
	Cord Clamp Screws	Steel, zinc plated	N/A	N/A	
Gasket/Dust Shield	Neoprene	Neoprene	N/A		