


Specifications



Photo is representative



Eaton 7621V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 647291

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton commercial grade decorator switch |
| CATALOG NUMBER | 7621V-BOX |
| UPC | 032664647291 |
| PRODUCT LENGTH/DEPTH | 1.29 in |
| PRODUCT HEIGHT | 4.19 in |
| PRODUCT WIDTH | 1.18 in |
| PRODUCT WEIGHT | 0.2 lb |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL Listed cULus Listed |
| PRODUCT TYPE | Commercial grade decorator switch |



Powering Business Worldwide

Product specifications

| | |
|----------------------------|---|
| ALLOWABLE WIRE SIZE | #14-10 AWG |
| SPECIAL FEATURES | Box |
| TYPE | Switch decorator |
| AMPERAGE RATING | 20A |
| VOLTAGE RATING | 120/277 V |
| NUMBER OF POLES | Single-pole |
| PHASE | Single-phase |
| WIRING METHOD | Back and push |
| SWITCH TYPE | Single-pole |
| MOUNTING METHOD | Flush |
| CLOSURE TYPE | Maintained |
| LOAD TYPE | LED Motor Control ELV INC Fan CFL HAL MLV FLR |
| MATERIAL | Thermoplastic |
| ACTUATOR | Antimicrobial paddle |
| COLOR | Ivory |

Resources

| | |
|-------------------------------|--|
| | Eaton Specification Sheet - 7621V-BOX |
| SPECIFICATIONS AND DATASHEETS | Arrow Hart commercial specification grade AC decorator switches spec sheet |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton 7621V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 647291

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton commercial grade decorator switch |
| CATALOG NUMBER | 7621V-BOX |
| UPC | 032664647291 |
| PRODUCT LENGTH/DEPTH | 1.29 in |
| PRODUCT HEIGHT | 4.19 in |
| PRODUCT WIDTH | 1.18 in |
| PRODUCT WEIGHT | 0.2 lb |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | UL Listed cULus Listed |
| PRODUCT TYPE | Commercial grade decorator switch |



Powering Business Worldwide

Product specifications

| | |
|----------------------------|---|
| ALLOWABLE WIRE SIZE | #14-10 AWG |
| SPECIAL FEATURES | Box |
| TYPE | Switch decorator |
| AMPERAGE RATING | 20A |
| VOLTAGE RATING | 120/277 V |
| NUMBER OF POLES | Single-pole |
| PHASE | Single-phase |
| WIRING METHOD | Back and push |
| SWITCH TYPE | Single-pole |
| MOUNTING METHOD | Flush |
| CLOSURE TYPE | Maintained |
| LOAD TYPE | LED Motor Control ELV INC Fan CFL HAL MLV FLR |
| MATERIAL | Thermoplastic |
| ACTUATOR | Antimicrobial paddle |
| COLOR | Ivory |

Resources

| | |
|-------------------------------|--|
| | Eaton Specification Sheet - 7621V-BOX |
| SPECIFICATIONS AND DATASHEETS | Arrow Hart commercial specification grade AC decorator switches spec sheet |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

