



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 800T 750 MCM Lug *Nsi Industries*

Catalog Number	800T
Manufacturer	Nsi Industries
Description	1 Port Aluminum Lug 800-300 MCM Aluminum Single Lugs Are Versatile and Reuseable Set Screw Connectors Made Of 6061T-6 Aluminum Alloy. Electro-Tin Plated For Low Contact Resistance. Suitable For Use With Both Copper and Aluminum Conductors. Temperature Rating 90 Degrees C. Rated 600 Volts (2000V Max. Per UL486B). UL 486A/B Listed. .
Weight per unit	0.4700 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Poles	1
Voltage Rating	600
Warranty	1 YEAR

### Material, Color, and Finish

Color	Silver
Finish	Aluminum

### Descriptions

Description	750 MCM LUG
extra long description	NSI 800T Dual Rated Lug 800-300 (10
Features	1 Port Aluminum Lug 800-300 MCM Aluminum Single Lugs are versatile and reuseable set screw connectors made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Temperature Rating 90 degrees C. Rated 600 volts (2000V max. per UL486B). UL 486A/B Listed. .
Long Description	1 Port Aluminum Lug 800-300 MCM Aluminum Single Lugs are versatile and reuseable set screw connectors made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Temperature Rating 90 degrees C. Rated 600 volts (2000V max. per UL486B). UL 486A/B Listed. .
Product Type	Dual Rated Lug 800-300 (100 Ea)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381001115
Manufacturers Part Number	800T
sub brand	Mechanical Connector
UPC	662381001115

## Packaging

Carton	1
Weight Per each	0.47

## Uses, Certifications, and Standards

environmental conditions	90 C
Temperature Rating	90 C