



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 552080407 8CON. 20G Thermostat Wire

*Southwire Company*

Catalog Number	552080407
Manufacturer	Southwire Company
Description	Thermostat Wire, Solid, 8 Conductors, #20 Awg Conductor Size, 150 V, 250 FT Overall Length, 0.173 In Outside Diameter, 0.006 In Insulation Thickness, Copper Conductor Material, Polypropylene Insulation Material, Red;White;Green;Blue;Yellow;Brown;Orange;Black, -20 °C Operating Temperature, +60 °C Operating Temperature, 30 LB/MFT
Weight per unit	0.0300 (lbs/ft)
Product Category	Jacketed Thermostat Wire & CBL

### Features

Number of Conductors	8 W
Stranding	SOLID

### Material, Color, and Finish

Color Code	Red, White, Green, Blue, Yellow, Brown, Orange, Black
Jacket Color	BROWN
Jacket Material	PVC

### Dimensions and Weight

Length	250 Foot
Outer Diameter	0.173 Inch

### Descriptions

Commodity Description	Jacketed Thermostat Wire & Cable
Description	8CON. 20G THERMOSTAT WIRE
extra long description	CL2 TYPE; 250 FOOT; 0.173 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 1581/13, NEC 725, ETL (CANADA AND US) APPROVAL; 150 VOLT VOLTAGE RATING; -20 TO 60 DEG C TEMPERATURE RATING; 8 CONDUCTOR(S); POLYPROPYLENE INSULATION MATERIAL; 20 AWG CONDUCTOR SIZE; RED, WHITE, GREEN, BLUE, YELLOW, BROWN, ORANGE, BLACK COLOR CODE; PVC JACKET MATERIAL; ROLL PACKAGE TYPE; SOLID STRANDING; BROWN JACKET COLOR; BAROSTAT BRAND; JACKET THICKNESS 0.015 INCH; INSULATION THICKNESS 0.006 INCH; INSULATED CONDUCTOR DIAME

### Manufacturer Information

Brand	Cables & Cords
Model	55208



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Thermostat and Doorbell Wire
Type	CL2

## Packaging

Carton	1000
Weight Per foot	0.03

## Uses, Certifications, and Standards

Approval	UL 1581/13, NEC 725, ETL (Canada and US)
Temperature Rating	-20 TO 60 DEG C