

Eaton's Arrow Hart
Industrial grade straight blade & locking devices

Arrow Hart

Superior design and performance make Eaton's straight blade and locking devices the ideal choice for industrial applications

EATON

Powering Business Worldwide

Table of contents	Page
Introduction	3
Features & benefits	4-8
Straight blade devices	9-10
Locking devices	11-17
Accessories	18
Straight blade dimensions	19
Locking dimensions	20-21
Straight blade & locking specifications	22-26
Certifications & compliances	27-29
Quick reference guide	30-31

Arrow Hart

Complete line of wiring devices for industrial & heavy duty construction environments



From everyday commercial use to heavy-duty industrial applications, Arrow Hart plugs and connectors ensure long lasting, dependable service in the most demanding environments

- A variety of grip styles enabling numerous applications
- Easily identified amperage/voltage ratings clearly marked on devices
- Rugged construction to ensure longer service life

Quick grip

Quick grip plugs and connectors are designed for quick, secure installation and easy, long-lasting use. They feature rugged nylon construction and a roomy wiring chamber for fast and easy installation. Our scalloped ergonomic design provides a comfortable grip during installation and operation.



Safety grip

Safety grip plugs and connectors combine durability and fast installation. Featuring dual-range external cord grip, safety grips provides positive cord gripping while limiting strain on conductors. The neoprene gasket seals around the cord for added terminal protection from external elements. The nylon construction is rugged and durable for dependable use.



Auto grip

Auto grip plugs and connectors feature a unique clamp design that secures cords during assembly and reduces installation time. The rugged tapered nylon body reduces impact and chemical exposure while providing easy handling for end users.



Ultra grip

Built with a contemporary flare and oval ergonomic design for a comfortable yet secure feel, ultra grip plugs and connectors offer excellent reliability and durability. A dual dovetail design provides superior cord grip retention, and the grommet allows usage across a wide range of cord diameters. Additionally, reversible inserts in the cord grip allow for exceptional clamp force on large diameter cords.




Arrow Hart quick grip plugs & connectors

Quick grip hospital and industrial grade plugs & connectors features & benefits

Commercial specification grade straight blade plugs & connectors

Designed for commercial applications, where ease-of-use, value and quality are critical.




Arrow Hart hospital grade straight blade plugs & connectors

Safety grip hospital grade plugs & connectors features & benefits

Hospital specification grade plugs & connectors

Built to meet and exceed UL Federal specification and hospital grade testing, Arrow Hart's hospital grade plugs and connectors assure reliable performance in the most demanding healthcare applications.



Safety grip hospital grade devices exceed federal spec. and hospital grade testing for use in demanding healthcare environments




Clear terminal cover allows for easy inspection of conductors and terminations



Retained quick drive assembly screws speed installation



Four position angled plug option is ideal for applications requiring power cord to lay close to walls and floors



Tapered, individual wire pockets guide stranded wire into contact area for ease of installation



Multiple-head drive screws provide versatility for ease of use

Arrow Hart auto grip plugs & connectors


Auto grip hospital and industrial grade plugs & connectors features & benefits

Industrial specification grade plugs, connectors, flanged inlets & outlets

Auto grip devices are designed for quick and easy installation and provide reliable performance in tough industrial environments.



Auto grip hospital grade devices exceed federal spec. and hospital grade testing for use in demanding healthcare environments



Unique clamp design secures cord during assembly, reducing installation time



Retained quick drive assembly screws speed installation



Multiple-head drive screws provide versatility for ease of use




Tapered, individual wire pockets guide stranded wire into contact area for ease of installation

Arrow Hart industrial grade ultra grip plugs and connectors

Ultra grip locking plugs & connectors features & benefits

The industry's most complete line of locking industrial devices

Superior design and performance make Arrow Hart's locking devices the ideal choice for industrial applications. Available in a wide range of NEMA, non-NEMA and flat cable configurations.



Arrow Hart industrial grade ultra grip plugs and connectors

Ultra grip receptacles features & benefits

The industry's most complete line of locking industrial devices

Arrow Hart offers the most rugged, feature-rich, broadest line of quality locking devices to meet the specific needs of demanding industrial applications. Available in NEMA and non-NEMA configurations.



Industrial flanged inlets & outlets features & benefits



Arrow Hart hospital grade straight blade plugs & connectors



AH8215HG







AH8219HG







AH8119W

15A Hospital grade straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	  5-15P 5-15R	Ultra grip plug	Black & white	AH8215HG
			Safety grip plug	Clear	AH8215HGC
		Safety grip angled body plug	Black & white	AH8215HGA	
		Safety grip angled body plug	Clear	AH8215HGAC	
		Quick grip plug	White	AH8115W	
		Auto grip plug	Black & white	5266NHG	
		Auto grip isolated ground plug	Orange	IG5266NHG	
		Ultra grip connector	Black & white	AH8219HG	
		Safety grip connector	Clear	AH8219HGC	
		Quick grip connector	White	AH8119W	
2P-3W	250	  6-15P 6-15R	Safety grip angled plug	Black & white	AH8225HGA
			Safety grip angled plug	Clear	AH8225HGAC

20A Hospital grade straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	  5-20P 5-20R	Ultra grip plug	Black & white	AH8315HG
			Safety grip angled plug	Black & white	AH8315HGA
			Safety grip angled plug	Clear	AH8315HGAC
			Auto grip plug	Black & white	5366NHG
			Ultra grip connector	Black & white	AH8319HG
			Auto grip connector	Black & white	5369NHG
2P-3W	250	  6-20P 6-20R	Safety grip angled plug	Black & white	AH8325HG
			Safety grip angled plug	Clear	AH8325HGAC

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial straight blade plugs and connectors



AH5266



AH5269



AH5879C







AH5878C







AH5965BK





15A Industrial grade straight blade devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Ultra grip plug	Black & white	AH5266
			Ultra grip plug	Black	AH5266BK
		Safety grip angled body plug	Black & white	AH5266A	
		Auto grip plug	Black & white	5266N	
		Ultra grip connector	Black & white	AH5269	
		Ultra grip connector	Black	AH5269BK	
		Auto grip connector	Black & white	5269N	
		Flanged outlet, back wire	Black & white	AH5279C	
		Flanged outlet, back wire, metal	Steel	AH5246	
		Flanged inlet, back wire	Black & white	AH5278C	
Flanged inlet, back wire, metal	Steel	AH5278			
2P-3W	250	 	Ultra grip plug	Black & white	AH5666
			Auto grip plug	Black & white	5666N
		Ultra grip connector	Black & white	AH5669	
		Auto grip connector	Black & white	5669N	
		Flanged outlet, back wire, nylon	Black & white	AH5679C	
		Flanged inlet, back wire, nylon	Black & white	AH5678C	





20A Industrial grade straight blade devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Ultra grip plug	Black & white	AH5366
			Ultra grip connector	Black & white	AH5369
		Flanged outlet, back wire, nylon	Black & white	AH5779C	
		Flanged inlet, back wire, nylon	Black & white	AH5778C	
2P-3W	250	 	Ultra grip plug	Black & white	AH5466
			Auto grip plug	Black & white	5466N
		Ultra grip connector	Black & white	AH5469	
		Auto grip connector	Black & white	5469N	
		Flanged outlet, back wire	Black & white	AH5879C	
		Flanged inlet, back wire	Black & white	AH5878C	

15A Industrial grade quick grip straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Quick grip plug	Black	AH5965BK
			Quick grip plug	Yellow	AH5965Y
		Quick grip connector	Black	AH5969BK	
		Quick grip connector	Yellow	AH5969Y	
2P-3W	250	 	Quick grip plug	Black	AH5666BK
			Quick grip plug	Yellow	AH5666Y
		Quick grip connector	Black	AH5669BK	
		Quick grip connector	Yellow	AH5669Y	

20A Industrial grade quick grip straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Quick grip plug	Black	AH5364BK
			Quick grip plug	Yellow	AH5364Y
		Quick grip connector	Black	AH5369BK	
		Quick grip connector	Yellow	AH5369Y	
2P-3W	250	 	Quick grip plug	Black	AH5464BK
			Quick grip plug	Yellow	AH5464Y
		Quick grip connector	Black	AH5469BK	
		Quick grip connector	Yellow	AH5469Y	

Accessories:
page 18

Dimensions &
cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



CWL515P



CWL515C



CWL515R





CWL515FO











CWL515FI



15/10A Industrial grade locking devices

Pole-Wire	V/AC	NON-NEMA	Description	Color	Catalog no.
3P-3W	125/ 250	  Receptacle Plug	Safety grip plug	Black & white	4767
			Safety grip angled body plug	Black & white	4767AN
			Safety grip connector	Black & white	4755
			Duplex receptacle	Black	7580
			Single receptacle	Black	7582

15A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.			
2P-2W	125	  L1-15R L1-15P	Safety grip plug	Black	7546			
			Safety grip plug	Black	7548			
			Safety grip connector	Black	7506			
			Duplex receptacle	Black	7540			
			Single receptacle	Black	CWL115R			
			Flanged outlet	Black	CWL115FO			
2P-3W	125	  L5-15R L5-15P	Safety grip plug	Black & white	CWL515P			
			Safety grip angled body plug	Black & white	CWL515PAN			
			Safety grip connector	Black & white	CWL515C			
			Safety grip angled body connector	Black & white	CWL515CAN			
			Duplex receptacle	Black	4700			
			Duplex combination straight blade & locking	Black	5792			
			Single receptacle	Black	CWL515R			
			Duplex receptacle, isolated ground	Orange	IG4700			
			Single receptacle, isolated ground	Orange	IGL515R			
			Flanged outlet	Black & white	CWL515FO			
			Flanged inlet	Black & white	CWL515FI			
			250		  L6-15R L6-15P	Safety grip plug	Black & white	CWL615P
						Safety grip connector	Black & white	CWL615C
						Duplex receptacle	Black	6580
Single receptacle	Black	CWL615R						
Single receptacle, isolated ground	Orange	IGL615R						
Flanged outlet	Black & white	CWL615FO						
277		  L7-15R L7-15P	Safety grip plug	Black & white	CWL715P			
			Safety grip connector	Black & white	CWL715C			
			Duplex receptacle	Black	4750			
			Single receptacle	Black	CWL715R			
			Flanged outlet	Black & white	CWL715FO			
Flanged inlet	Black & white	CWL715FI						

20/10A Industrial grade locking devices

Pole-Wire	V/AC	NON-NEMA	Description	Color	Catalog no.
4P-5W	250/ 600	  Receptacle Plug	Ultra grip plug	Black & white	AH3521BK
			Ultra grip connector	Black & white	AH3523BK
			Flanged outlet	Black	AH3525BK
			Flanged inlet	Black	AH3524BK

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL520P



AHCL520C



AHCL520R





















AHCL520FO



AHCL520FI

20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-2W	250	 	Safety grip plug	Black & white	CWL220P
			Safety grip connector	Black & white	CWL220C
			Single receptacle	Black	CWL220R
			Flanged outlet	Black & white	CWL220FO
			Flanged inlet	Black & white	CWL220FI
2P-3W	125	 	Color coded ultra grip plug	Yellow & black	AHCL520P
			Color coded ultra grip connector	Yellow & black	AHCL520C
			Color coded single receptacle	Yellow & black	AHCL520R
			Single receptacle, isolated ground	Orange	IGL520R
			Color coded flanged outlet	Yellow & black	AHCL520FO
	Color coded flanged inlet	Yellow & black	AHCL520FI		
	250	 	Color coded ultra grip plug	Blue & black	AHCL620P
			Color coded ultra grip connector	Blue & black	AHCL620C
			Color coded single receptacle	Blue & black	AHCL620R
			Single receptacle, isolated ground	Orange	IGL620R
Color coded flanged outlet			Blue & black	AHCL620FO	
Color coded flanged inlet	Blue & black	AHCL620FI			
277	 	Color coded ultra grip plug	Gray & black	AHCL720P	
		Color coded ultra grip connector	Gray & black	AHCL720C	
		Color coded single receptacle	Gray & black	AHCL720R	
		Single receptacle, isolated ground	Orange	IGL720R	
		Colored coded flanged outlet	Gray & black	AHCL720FO	
Colored coded flanged inlet	Gray & black	AHCL720FI			
347	 	Safety grip plug	Black & white	L2420P	
		Single receptacle	Black	L2420R	
480	 	Colored coded ultra grip plug	Red & black	AHCL820P	
		Colored coded ultra grip connector	Red & black	AHCL820C	
		Colored coded single receptacle	Red & black	AHCL820R	
		Single receptacle, isolated ground	Orange	IGL820R	
		Colored coded flanged outlet	Red & black	AHCL820FO	
Colored coded flanged inlet	Red & black	AHCL820FI			
600	 	Auto grip plug	Black & white	CWL920P	
		Auto grip connector	Black & white	CWL920C	
		Single receptacle	Black	CWL920R	
		Flanged outlet	Black & white	CWL920FO	
		Flanged inlet	Black & white	CWL920FI	
		Flanged inlet	Black & white	CWL920FI	
3P-3W	125/250	 	Safety grip plug	Gray	9965C
			Safety grip connector	Gray	7314C
			Single receptacle	Black	7310B
			Flanged outlet	Gray	7328N
			Flanged inlet	Gray	7327N
	 	Colored coded ultra grip plug	Orange & black	AHCL1020P	
		Colored coded ultra grip connector	Orange & black	AHCL1020C	
		Colored coded single receptacle	Orange & black	AHCL1020R	
		Colored coded flanged outlet	Orange & black	AHCL1020FO	
		Colored coded flanged inlet	Orange & black	AHCL1020FI	

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL1520P



AHCL1520C



AHCL1520R



AHCL1520FO



AHCL1520FI

20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.				
3P-3W	250	 L11-20R	 L11-20P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1120P			
				Color coded ultra grip connector, 3-phase	Blue & black	AHCL1120C			
		Color coded single receptacle, 3-phase	Blue & black	AHCL1120R					
		Color coded flanged outlet, 3-phase	Blue & black	AHCL1120FO					
		Color coded flanged inlet, 3-phase	Blue & black	AHCL1120FI					
	480	 L12-20R	 L12-20P	Auto grip plug, 3-phase	Black & white	CWL1220P			
				Auto grip connector, 3-phase	Black & white	CWL1220C			
				Single receptacle, 3-phase	Black	CWL1220R			
				Flanged outlet, 3-phase	Black & white	CWL1220FO			
				Flanged inlet, 3-phase	Black & white	CWL1220FI			
3P-4W	125/250	 L14-20R	 L14-20P	Color coded ultra grip plug	Orange & black	AHCL1420P			
				Color coded ultra grip connector	Orange & black	AHCL1420C			
				Color coded single receptacle	Orange & black	AHCL1420R			
				Single receptacle, isolated ground	Orange	IGL1420R			
				Color coded flanged outlet	Orange & black	AHCL1420FO			
		Color coded flanged inlet	Orange & black	AHCL1420FI					
		250	 L15-20R	 L15-20P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1520P		
					Ultra grip plug, 3-phase	Black	AHL1520PBK		
					Color coded ultra grip connector, 3-phase	Blue & black	AHCL1520C		
					Ultra grip connector, 3-phase	Black	AHL1520CBK		
	Color coded single receptacle, 3-phase				Blue & black	AHCL1520R			
	Single receptacle, isolated ground, 3-phase				Orange	IGL1520R			
	Color coded flanged outlet, 3-phase				Blue & black	AHCL1520FO			
	Color coded flanged inlet, 3-phase				Blue & black	AHCL1520FI			
	480				 L16-20R	 L16-20P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1620P
							Color coded ultra grip connector, 3-phase	Red & black	AHCL1620C
		Color coded single receptacle, 3-phase	Red & black	AHCL1620R					
		Single receptacle, isolated ground, 3-phase	Orange	IGL1620R					
		Color coded flanged outlet, 3-phase	Red & black	AHCL1620FO					
		Color coded flanged inlet, 3-phase	Red & black	AHCL1620FI					
4P-4W		120/208	 Receptacle	 Plug			Safety grip plug, 3-phase	Gray	7411C
							Safety grip connector, 3-phase	Gray	7413C
							Single receptacle, 3-phase	Black	7410B
							Flanged outlet, 3-phase	Gray	7409N
	Flanged inlet, 3-phase				Gray	7408N			
	 L18-20R		 L18-20P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1820P			
				Color coded ultra grip connector, 3-phase	Blue & black	AHCL1820C			
				Color coded single receptacle, 3-phase	Blue & black	AHCL1820R			
				Color coded flanged outlet, 3-phase	Blue & black	AHCL1820FO			
				Color coded flanged inlet, 3-phase	Blue & black	AHCL1820FI			

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL2220P



AHCL2220C



AHCL2220R













AHCL2220FO







AHCL2220FI

20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
4P-4W	277/480	  L19-20R L19-20P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1920P
			Color coded ultra grip connector, 3-phase	Red & black	AHCL1920C
		Color coded single receptacle, 3-phase	Red & black	AHCL1920R	
		Color coded flanged outlet, 3-phase	Red & black	AHCL1920FO	
		Color coded flanged inlet, 3-phase	Red & black	AHCL1920FI	
	347/600	  L20-20R L20-20P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2020P
			Color coded ultra grip connector, 3-phase	Black & black	AHCL2020C
			Color coded single receptacle, 3-phase	Black & black	AHCL2020R
			Color coded flanged outlet, 3-phase	Black & black	AHCL2020FO
			Color coded flanged inlet, 3-phase	Black & black	AHCL2020FI
4P-5W	120/208	  L21-20R L21-20P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL2120P
			Ultra grip plug, 3-phase	Black	AHL2120PBK
		Ultra grip plug, 3-phase, flat cable	Black & white	AHL2120PF	
		Color coded ultra grip connector, 3-phase	Blue & black	AHCL2120C	
		Ultra grip connector, 3-phase	Black	AHL2120CBK	
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2120CF	
		Color coded single receptacle, 3-phase	Blue & black	AHCL2120R	
		Single receptacle, isolated ground, 3-phase	Orange	IGL2120R	
		Color coded flanged outlet, 3-phase	Blue & black	AHCL2120FO	
		Color coded flanged inlet, 3-phase	Blue & black	AHCL2120FI	
	277/480	  L22-20R L22-20P	Color coded ultra grip plug, 3-phase	Red & black	AHCL2220P
			Color coded ultra grip connector, 3-phase	Red & black	AHCL2220C
			Color coded single receptacle, 3-phase	Red & black	AHCL2220R
			Color coded flanged outlet, 3-phase	Red & black	AHCL2220FO
			Color coded flanged inlet, 3-phase	Red & black	AHCL2220FI
347/600	  L23-20R L23-20P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2320P	
		Color coded ultra grip connector, 3-phase	Black & black	AHCL2320C	
		Color coded single receptacle, 3-phase	Black & black	AHCL2320R	
		Color coded flanged outlet, 3-phase	Black & black	AHCL2320FO	
		Color coded flanged inlet, 3-phase	Black & black	AHCL2320FI	

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	  L5-30R L5-30P	Color coded ultra grip plug	Yellow & black	AHCL530P
			Ultra grip plug, isolated ground	Orange	IGL530P
		Color coded ultra grip connector	Yellow & black	AHCL530C	
		Color coded single receptacle	Yellow & black	AHCL530R	
		Single receptacle, isolated ground	Orange	IGL530R	
		Color coded flanged outlet	Yellow & black	AHCL530FO	
		Color coded flanged inlet	Yellow & black	AHCL530FI	
	240	  L25-30R L25-30P	Ultra grip plug	Black & white	AHL2530P
			Ultra grip connector	Black & white	AHL2530C
			Single receptacle	Black	AHL2530R
			Single receptacle, isolated ground	Orange	IG2530R

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL730P



AHCL730C



AHCL730R



AHCL730FO



AHCL730FI

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	250	L6-30R L6-30P	Color coded ultra grip plug	Blue & black	AHCL630P
			Color coded ultra grip connector	Blue & black	AHCL630C
		Color coded single receptacle	Blue & black	AHCL630R	
		Single receptacle, isolated ground	Orange	IGL630R	
		Color coded flanged outlet	Blue & black	AHCL630FO	
		Color coded flanged inlet	Blue & black	AHCL630FI	
	277	L7-30R L7-30P	Color coded ultra grip plug	Gray & black	AHCL730P
			Color coded ultra grip connector	Gray & black	AHCL730C
		Color coded single receptacle	Gray & black	AHCL730R	
		Single receptacle, isolated ground	Orange	IGL730R	
		Color coded flanged outlet	Gray & black	AHCL730FO	
		Color coded flanged inlet	Gray & black	AHCL730FI	
480	L8-30R L8-30P	Color coded ultra grip plug	Red & black	AHCL830P	
		Color coded ultra grip connector	Red & black	AHCL830C	
	Color coded single receptacle	Red & black	AHCL830R		
	Single receptacle, isolated ground	Orange	IGL830R		
	Color coded flanged outlet	Red & black	AHCL830FO		
	Color coded flanged inlet	Red & black	AHCL830FI		
600	L9-30R L9-30P	Auto grip plug	Black & white	CWL930P	
		Auto grip connector	Black & white	CWL930C	
		Single receptacle	Black	CWL930R	
		Flanged outlet	Black & white	CWL930FO	
		Flanged inlet	Black & white	CWL930FI	
		3P-3W	125/250	Receptacle Plug	Ultra grip plug
Ultra grip connector	Black & white				AH3333N
Color coded single receptacle	Orange & black			AHCL3330R	
Flanged outlet	Black & white			AH3336N	
Flanged inlet	Black & white			AH3337N	
L10-30R L10-30P	Color coded ultra grip plug			Orange & black	AHCL1030P
	Color coded ultra grip connector		Orange & black	AHCL1030C	
	Color coded single receptacle		Orange & black	AHCL1030R	
	Color coded flanged outlet		Orange & black	AHCL1030FO	
	Color coded flanged inlet		Orange & black	AHCL1030FI	
	250		L11-30R L11-30P	Color coded ultra grip plug, 3-phase	Blue & blue
Color coded ultra grip connector, 3-phase				Blue & blue	AHCL1130C
Color coded single receptacle, 3-phase			Blue & Black	AHCL1130R	
Color coded flanged outlet, 3-phase			Blue & blue	AHCL1130FO	
Color coded flanged inlet, 3-phase			Blue & blue	AHCL1130FI	
480			L12-30R L12-30P	Auto grip plug, 3-phase	Black & white
	Auto grip connector, 3-phase			Black & white	CWL1230C
	Single receptacle, 3-phase		Black	CWL1230R	
	Flanged outlet, 3-phase	Black & white	CWL1230FO		
	Flanged inlet, 3-phase	Black & white	CWL1230FI		

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL1430P



AHCL1430C



AHCL1430R










AHCL1430FO



AHCL1430FI

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
3P-3W	600	 L13-30R L13-30P	Auto grip plug, 3-phase	Black & white	CWL1330P
			Auto grip connector, 3-phase	Black & white	CWL1330C
			Single receptacle, 3-phase	Black	CWL1330R
			Flanged outlet, 3-phase	Black & white	CWL1330FO
			Flanged inlet, 3-phase	Black & white	CWL1330FI
3P-4W	125/250	 L14-30R L14-30P	Color coded ultra grip plug	Orange & black	AHCL1430P
			Color coded ultra grip connector	Orange & black	AHCL1430C
			Color coded single receptacle	Orange & black	AHCL1430R
			Single receptacle, isolated ground	Orange	IGL1430R
			Color coded flanged outlet	Orange & black	AHCL1430FO
	Color coded flanged inlet	Orange & black	AHCL1430FI		
	250	 L15-30R L15-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1530P
			Color coded ultra grip connector, 3-phase	Blue & black	AHCL1530C
			Color coded single receptacle, 3-phase	Blue & black	AHCL1530R
			Single receptacle, isolated ground, 3-phase	Orange	IGL1530R
Color coded flanged outlet, 3-phase			Blue & black	AHCL1530FO	
Color coded flanged inlet, 3-phase	Blue & black	AHCL1530FI			
480	 L16-30R L16-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1630P	
		Color coded ultra grip connector, 3-phase	Red & black	AHCL1630C	
		Color coded single receptacle, 3-phase	Red & black	AHCL1630R	
		Color coded flanged outlet, 3-phase	Red & black	AHCL1630FO	
		Color coded flanged inlet, 3-phase	Red & black	AHCL1630FI	
600	 L17-30R L17-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL1730P	
		Color coded ultra grip connector, 3-phase	Black & black	AHCL1730C	
		Color coded single receptacle, 3-phase	Black & black	AHCL1730R	
		Color coded flanged outlet, 3-phase	Black & black	AHCL1730FO	
		Color coded flanged inlet, 3-phase	Black & black	AHCL1730FI	
4P-4W	120/208	 Receptacle Plug	Ultra grip plug, 3-phase	Black & white	AH3431N
			Ultra grip connector, 3-phase	Black & white	AH3433N
			Color coded single receptacle, 3-phase	Blue & black	AHCL3430R
			Flanged outlet, 3-phase	Black & white	AH3436N
			Flanged inlet, 3-phase	Black & white	AH3434N
	 L18-30R L18-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1830P	
		Color coded ultra grip connector, 3-phase	Blue & black	AHCL1830C	
		Color coded single receptacle, 3-phase	Blue & black	AHCL1830R	
		Color coded flanged outlet, 3-phase	Blue & black	AHCL1830FO	
		Color coded flanged inlet, 3-phase	Blue & black	AHCL1830FI	

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL2130P



AHCL2130C



AHCL2130R



AHCL2130FO



AHCL2130FI

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.			
4P-4W	277/480	 L19-30R L19-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1930P			
			Color coded ultra grip connector, 3-phase	Red & black	AHCL1930C			
		Color coded single receptacle, 3-phase	Red & black	AHCL1930R				
		Color coded flanged outlet, 3-phase	Red & black	AHCL1930FO				
		Color coded flanged inlet, 3-phase	Red & black	AHCL1930FI				
347/600	277/480	 L20-30R L20-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2030P			
			Color coded ultra grip connector, 3-phase	Black & black	AHCL2030C			
			Color coded flanged outlet, 3-phase	Black & black	AHCL2030R			
			Color coded flanged outlet, 3-phase	Black & black	AHCL2030FO			
			Color coded flanged inlet, 3-phase	Black & black	AHCL2030FI			
4P-5W	120/208	 L21-30R L21-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL2130P			
			Ultra grip plug, 3-phase, flat cable	Black & white	AHL2130PF			
			Color coded ultra grip connector, 3-phase	Blue & black	AHCL2130C			
			Ultra grip connector, 3-phase, flat cable	Black & white	AHL2130CF			
			Color coded single receptacle, 3-phase	Blue & black	AHCL2130R			
			Single receptacle, isolated ground, 3-phase	Orange	IGL2130R			
			Color coded flanged outlet, 3-phase	Blue & black	AHCL2130FO			
			Color coded flanged inlet, 3-phase	Blue & black	AHCL2130FI			
			240/415	120/208	 L26-30R L26-30P	Ultra grip plug, 3-phase	Black & white	AHL2630P
						Ultra grip connector, 3-phase	Black & white	AHL2630C
Single receptacle, 3-phase	Black	AHL2630R						
Single receptacle, isolated ground, 3-phase	Orange	IG2630R						
277/480	120/208	 L22-30R L22-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL2230P			
			Ultra grip plug, 3-phase, flat cable	Black & white	AHL2230PF			
			Color coded ultra grip connector, 3-phase	Red & black	AHCL2230C			
			Ultra grip connector, 3-phase, flat cable	Black & white	AHL2230CF			
			Color coded single receptacle, 3-phase	Red & black	AHCL2230R			
			Single receptacle, isolated ground, 3-phase	Orange	IGL2230R			
			Color coded flanged outlet, 3-phase	Red & black	AHCL2230FO			
			Color coded flanged inlet, 3-phase	Red & black	AHCL2230FI			
			347/600	277/480	 L23-30R L23-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2330P
						Ultra grip plug, 3-phase, flat cable	Black & white	AHL2330PF
Color coded ultra grip connector, 3-phase	Black & black	AHCL2330C						
Ultra grip connector, 3-phase, flat cable	Black & white	AHL2330CF						
Color coded single receptacle, 3-phase	Black & black	AHCL2330R						
Single receptacle, isolated ground, 3-phase	Orange	IGL2330R						
Color coded flanged outlet, 3-phase	Black & black	AHCL2330FO						
Color coded flanged inlet, 3-phase	Black & black	AHCL2330FI						

Accessories:
page 18

Dimensions & cord diameters:
pages 19-21

Spec information:
pages 22-26

Compliances:
pages 27-29

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade accessories



BS1



BM2



BL1



WLRS1



7420



WP1

Accessories for industrial grade straight blade & locking devices

Amp	Electrical Characteristics					Boot		Receptacle Covers			FI/FO	Receptacle (1-Gang) 302/304 Stainless Steel Wallplates					
	NEMA	Pole-Wire	G/NG	Voltage	Phase	Plug	Conn.	Heavy-duty Single	Duplex	Standard Single		Cover	Standard Single	Duplex	Mid-size Single	Duplex	Oversized Single
10/15	NON	3P-3W	NG	277/480	—	BS1	BS2	WLRS1	—	7420	WP1	93091	—	93991	—	93891	—
15	L1-15	2P-2W	NG	125	—	—	—	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	5-15	2P-3W	G	125	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L5-15	2P-3W	G	125	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	6-15	2P-3W	G	250	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L6-15	2P-3W	G	250	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
20/10	NON	4P-5W	G	250/600	—	BL1	BL2	—	—	—	WP2	93111	—	PJ720*	—	—	—
20	5-20	2P-3W	G	125	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L5-20	2P-3W	G	125	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L2-20	2P-2W	NG	250	—	BS1	BS2	WLRS1	—	7420	WP1	93091	—	93991	—	93891	—
	6-20	2P-3W	G	250	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L6-20	2P-3W	G	250	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L11-20	3P-3W	NG	250	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L15-20	3P-4W	G	250	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L7-20	2P-3W	G	277	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L8-20	2P-3W	G	480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L12-20	3P-3W	NG	480	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L16-20	3P-4W	G	480	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L9-20	2P-3W	G	600	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L18-20	4P-4W	NG	120/208	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	4P-4W	NG	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L21-20	4P-5W	G	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L10-20	3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L14-20	3P-4W	G	277/480	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L19-20	4P-4W	NG	277/480	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
L22-20	4P-5W	G	277/480	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L20-20	4P-4W	NG	347/600	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L23-20	4P-5W	G	347/600	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
30	L5-30	2P-3W	G	125	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L6-30	2P-3W	G	250	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L11-30	3P-3W	NG	250	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L15-30	3P-4W	G	250	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L7-30	2P-3W	G	277	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L8-30	2P-3W	G	480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L12-30	3P-3W	NG	480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L16-30	3P-4W	G	480	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L9-30	2P-3W	G	600	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L13-30	3P-3W	NG	600	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L17-30	3P-4W	G	600	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L18-30	4P-4W	NG	120/208	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	4P-4W	NG	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L21-30	4P-5W	G	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L10-30	3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L14-30	3P-4W	G	277/480	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L19-30	4P-4W	NG	277/480	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L22-30	4P-5W	G	277/480	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
L20-30	4P-4W	NG	347/600	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L23-30	4P-5W	G	347/600	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	

Note: *Polycarbonate only (B, GY, V, W)

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade straight blade plug & connector dimensions

Table 1. Ultra grip plugs & connectors

Family	A	B	C	D	Cord Diameter
Ultra grip plug	1.38" (35.1mm)	2.07" (52.6mm)	1.69" (42.9mm)	1.55" (39.4mm)	0.25 - 0.66" (6.4-16.8mm)
Ultra grip connector	1.38" (35.1mm)	2.89" (73.4mm)	1.69" (42.9mm)	1.55" (39.4mm)	0.25 - 0.66" (6.4-16.8mm)




Table 2. Safety grip plugs & connectors

Family	A	B	C	D	Cord Diameter
Safety grip plug, hospital grade	1.40" (35.6mm)	2.11" (53.6mm)	1.53" (38.9mm)	1.45" (36.8mm)	0.30-0.65" (7.6-16.6mm)
Safety grip plug, angled, hospital grade	1.39" (35.3mm)	1.29" (32.8mm)	1.52" (38.6mm)	2.09" (53.1mm)	0.30-0.65" (7.6-16.6mm)
Safety grip plug, angled	1.38" (35.1mm)	1.30" (33.0mm)	1.51" (38.4mm)	2.07" (52.6mm)	0.30-0.65" (7.6-16.6mm)
Safety grip connector, hospital grade	1.38" (35.1mm)	2.98" (75.7mm)	1.52" (38.6mm)	1.45" (36.8mm)	0.30-0.65" (7.6-16.6mm)




Table 3. Quick grip plugs & connectors

Family	A	B	C	D	Cord Diameter
Quick grip plug	1.40" (35.6mm)	1.96" (50.0mm)	1.67" (42.4mm)	1.46" (37.1mm)	0.23-0.65" (5.8-16.5mm)
Quick grip connector	1.40" (35.6mm)	2.59" (65.8mm)	1.67" (42.4mm)	1.46" (37.1mm)	0.23-0.65" (5.8-16.5mm)



Table 4. Flanged inlets & outlets

Family	A	B	C	D	E	F
Flanged outlet, nylon	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
Flanged inlet, nylon	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
Flanged outlet, metal	1.40" (35.6mm)	1.11" (28.2mm)	1.44" (35.6mm)	2.47" (62.7mm)	0.20" (5.1mm)	2.04" (52.6mm)
Flanged inlet, metal	1.57" (39.9mm)	1.36" (34.5mm)	1.64" (38.9mm)	2.48" (63.0mm)	0.286" (7.3mm)	2.01" (51.1mm)



Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking device dimensions

Table 5. Ultra grip locking plugs & connectors

Family	A	B	C	D	Cord Diameter
Ultra grip plug, 2P-3W, 3P-3W	1.78" (45.2mm)	2.59" (65.8mm)	2.23" (56.6mm)	2.10" (53.3mm)	0.38-1.00" (9.6 - 25.4mm)
Ultra grip plug, 3P-4W, 4P-4W, 4P-5W	2.18" (55.4mm)	2.82" (71.6mm)	2.13" (54.1mm)	2.30" (58.4mm)	0.38-1.16" (9.6 - 29.5mm)
Ultra grip connector, 2P-3W, 3P-3W	1.78" (45.2mm)	3.61" (91.7mm)	2.23" (56.6mm)	2.10" (53.3mm)	0.38-1.00" (9.6 - 25.4mm)
Ultra grip connector, 3P-4W, 4P-4W, 4P-5W	1.97" (50.0mm)	3.84" (97.5mm)	2.46" (62.5mm)	2.30" (58.4mm)	0.38-1.16" (9.6 - 29.5mm)






Table 6. Safety grip locking plugs & connectors

Family	A	B	C	Cord Diameter
Safety grip 15/10A, non-NEMA plug	1.36" (34.5mm)	2.09" (53.1mm)	1.51" (38.4mm)	0.33-0.66" (8.4-16.8mm)
Safety grip NEMA L1-15 plug	1.55" (39.4mm)	1.56" (39.6mm)	1.57" (39.9mm)	0.31-0.47" (7.9-11.9mm)
Safety grip 20A: NEMA L2-20 plug	1.37" (34.8mm)	2.07" (52.6mm)	1.51" (38.4mm)	0.33-0.66" (8.4-16.8mm)
Safety grip 20A: non-NEMA 277/480V/AC plug	1.75" (44.4mm)	2.42" (61.5mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip NEMA L24-20 plug	1.82" (46.2mm)	2.63" (66.8mm)	2.12" (53.8mm)	0.33-1.15" (8.4-29.2mm)
Safety grip 20A 2P-3W, 3P-3W plug	1.16" (29.5mm)	2.48" (63.0mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 20A: 4P-4W plug	1.93" (49.0mm)	2.80" (71.1mm)	2.33" (59.2mm)	0.63-1.16" (16.0-29.5mm)
Safety grip 30A: 2P-3W, 3P-3W plug	1.91" (48.5mm)	2.48" (63.0mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 15/10A, non-NEMA connector	1.36" (34.5mm)	2.87" (72.9mm)	1.52" (38.6mm)	0.33-0.66" (8.4-16.8mm)
Safety grip NEMA L1-15 connector	1.28" (32.5mm)	2.04" (51.8mm)	1.36" (34.5mm)	0.30-0.56" (7.6-14.2mm)
Safety grip 20A, NEMA L2-20 connector	1.37" (34.8mm)	2.01" (51.1mm)	1.52" (38.6mm)	0.33-0.66" (8.4-16.8mm)
Safety grip 20A: non-NEMA 277/480V/AC connector	1.75" (44.4mm)	3.32" (84.3mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 20A, 2P-3W, 3P-3W connector	1.83" (46.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 20A: 4P-4W connector	1.93" (49.0mm)	3.75" (95.3mm)	2.31" (58.7mm)	0.63-1.16" (16.0-29.5mm)
Safety grip 30A: 2P-3W, 3P-3W connector	1.85" (47.0mm)	3.55" (90.2mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)










Table 7. Locking plugs & connectors

Family	A	B	C	D	Cord Diameter
Plug, NEMA L9-20, L9-30	1.83" (47.5mm)	2.85" (72.3mm)	2.13" (54.1mm)	—	0.30-0.95" (7.6-24.1mm)
Plug, NEMA L12-20, L12-30, L13-30	1.83" (47.0mm)	2.85" (72.3mm)	2.13" (54.1mm)	—	0.38-1.00" (9.5-25.4mm)
Plug, Angled 15A	1.37" (34.8mm)	1.30" (33.0mm)	1.50" (38.1mm)	2.08" (52.8mm)	0.33-0.66" (8.4-16.8mm)
Connector, NEMA L9-20, L9-30	1.83" (47.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	—	0.30-0.95" (7.6-24.1mm)
Connector, NEMA L12-20, L12-30, L13-30	1.83" (47.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	—	0.38-1.00" (9.5-25.4mm)



Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking device dimensions

Table 8. Locking receptacles

Family	A	B	C	D	E	F
Small receptacle, 10/15A	1.40" (35.6mm)	1.53" (38.9mm)	1.72" (43.7mm)	0.82" (20.8mm)	3.22" (81.8mm)	4.03" (102.4mm)
Small receptacle, NEMA L1-15	1.36" (34.5mm)	1.40" (35.6mm)	1.68" (42.7mm)	0.95" (24.1mm)	3.33" (84.6mm)	3.69" (93.7mm)
Small receptacle, NEMA L2-20	1.37" (34.8mm)	1.37" (34.8mm)	2.02" (51.3mm)	1.12" (28.4mm)	3.21" (81.5mm)	3.62" (92.0mm)
Small receptacle, NEMA L5-15, L6-15, L7-15	1.39" (35.3mm)	1.54" (39.1mm)	1.72" (43.7mm)	0.82" (20.8mm)	3.21" (81.5mm)	4.04" (102.6mm)
NEMA L24-20	1.57" (39.9mm)	1.62" (41.1mm)	2.31" (58.7mm)	1.04" (26.5mm)	3.30" (83.8mm)	3.64" (92.5mm)
20A	1.56" (39.6mm)	1.56" (39.6mm)	2.64" (67.1mm)	1.06" (26.9mm)	3.22" (81.8mm)	3.64" (92.5mm)
30A	1.56" (39.6mm)	1.61" (40.9mm)	2.64" (67.1mm)	1.09" (27.7mm)	3.21" (81.5mm)	3.63" (92.2mm)
Duplex receptacle, 10/15A	1.11" (28.2mm)	1.59" (40.4mm)	2.80" (71.1mm)	0.82" (20.8mm)	3.29" (83.6mm)	4.05" (102.9mm)
Duplex receptacle, 15A	1.09" (27.7mm)	1.50" (38.1mm)	2.63" (66.8mm)	0.97" (24.6mm)	3.32" (84.3mm)	3.63" (92.2mm)






Table 9. Locking flanged inlets

Family	A	B	C	D	E	F
15A: 2P-2W & 2P-3W	1.56" (39.6mm)	1.92" (48.8mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
20A: 2P-3W & 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
20A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
20A: NEMA L9-20, L12-20	1.94" (49.3mm)	2.09" (53.1mm)	2.04" (51.8mm)	2.88" (73.2mm)	0.20" (5.1mm)	1.25" (31.8mm)
30A: 2P-3W, 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
30A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
30A: NEMA L9-30, L12-30, L13-30	1.94" (49.3mm)	2.02" (51.3mm)	2.12" (53.8mm)	2.88" (73.2mm)	0.19" (4.8mm)	1.25" (31.8mm)










Table 10. Locking flanged outlets

Family	A	B	C	D	E	F
15A: 2P-2W & 2P-3W	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
20A: NEMA L2-20	1.48" (37.6mm)	1.69" (42.9mm)	1.56" (39.7mm)	2.50" (63.5mm)	0.54" (13.7mm)	2.06" (52.4mm)
20A: 2P-3W, 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
20A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
20A: NEMA L9-20, L12-20	1.94" (49.3mm)	2.09" (53.1mm)	2.04" (51.8mm)	2.87" (72.9mm)	0.19" (4.8mm)	1.25" (31.8mm)
30A: 2P-3W, 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
30A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
30A: NEMA L9-30, L12-30, L13-30	1.94" (49.3mm)	2.02" (51.3mm)	2.12" (53.8mm)	2.86" (72.6mm)	0.20" (5.1mm)	1.20" (30.5mm)



Compliances, specifications and availability are subject to change without notice.

Arrow Hart hospital & industrial grade straight blade devices specification & performance data

15 & 20A Hospital grade plugs & connectors NEMA 5-15, 6-15, 5-20, 6-20		15 & 20A Hospital grade quick grip plugs & connectors NEMA 5-15	
Wiring type	Back wire	Wiring type	Back wire
Testing & code compliance	<ul style="list-style-type: none"> cULus listed to 498, file no. E15058; file no. E15012 (hospital grade) UL verified to Fed Spec WC-596G 	Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E15012 UL verified to Fed Spec WC-596G
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #18 - #12 AWG Voltage ratings: Permanently marked on device	Mechanical specifications	Terminal accommodation: #18 - #12 AWG Voltage ratings: Permanently marked on device
Material specifications	Plug/connector outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.060" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: EPDM	Material specifications	Plug/connector outer shell: Nylon Interior body: N/A Terminal retainer: Polycarbonate Blades: 0.060" thick brass Line contacts: 0.030" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: N/A
15 & 20A Industrial grade plugs & connectors NEMA 5-15, 6-15, 5-20, 6-20		15 & 20A Industrial grade quick grip plugs & connectors NEMA 5-15, 6-15, 5-20, 6-20	
Wiring type	Back wire	Wiring type	Back wire
Testing & code compliance	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E3663 Complies with Fed Spec WC-596F CSA certified to C22.2, no. 42-99 file no. 7087 (6221-02) 7251N: NOM certified 	Testing & code compliance	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E15012 UL verified to Fed Spec WC-596G
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)
Mechanical specifications	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device	Mechanical specifications	Terminal accommodation: #18 - #12 AWG Voltage ratings: Permanently marked on device
Material specifications	Plug/connector outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground contact: 0.041" thick brass Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: EPDM	Material specifications	Plug/connector outer shell: Nylon Interior body: N/A Terminal retainer: Polycarbonate Blades: 0.060" thick brass Line contacts: 0.030" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground contact: Brass Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: N/A

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade straight blade & locking devices specification & performance data

	15 & 20A Industrial grade flanged inlets NEMA 5-15, 6-15, 5-20, 6-20	15 & 20A Industrial grade flanged outlets NEMA 5-15, 6-15, 5-20, 6-20
Wiring type	Side wire	Side wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E3663 cUL Listed to CSA C22.2, no. 42-M1999 5278C, 5678C: also NOM certified 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 CSA certified to C22.2, no. 42-99 & 182.3-M1987 file no. 7087 (6233-01)
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) at maximum rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 AWG Voltage ratings: Permanently marked on device
Material specifications	Plug/connector outer shell: Nylon (except 5278 steel) Interior body: Lexan (except 5278 urea) Terminal retainer: Lexan (except 5278 urea) Blades: 0.062" thick brass Line contacts: N/A Terminal clamps: Steel Terminal screws: 8-32 steel, brass plated (hot) or nickel plated (neutral) (except 5278 #8-32 brass) Ground screw: #8-32 steel, zinc plated (green) (except 5278 #8-32 brass) Assembly screws/rivets: Steel screws (except 5278 steel rivets, zinc plated)	Plug/connector outer shell: Nylon (except 5246 steel) Interior body: Lexan (except 5246 nylon) Terminal retainer: Lexan (except 5246 nylon) Blades: N/A Line contacts: 0.031" thick brass Terminal clamps: Brass Terminal screws: #8-32 steel, brass plated (hot) or nickel plated (neutral) (except 5246, brass) Ground screw: #8-32 brass, zinc plated (green) Assembly screws/rivets: Steel screws (except 5246C steel rivets)

	15A Plugs & connectors NEMA L5-15, L6-15, L7-15	15A Plugs & connectors Non-NEMA 10/15A	15 & 20A Plugs & connectors NEMA L1-15, L2-20
Wiring Type	Back wire	Back wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> cUL Listed to UL498, file no. E3663 UL verified to Fed Spec WC-596F cUL Listed to CSA C22.2, no. 42 file no. E3663 	<ul style="list-style-type: none"> UL recognized component for US & Canada, file no. E366 	<ul style="list-style-type: none"> Listed to UL498, file no. E3663 cUL Listed to C22.2, no. 42 file no. E3663 L2-20 cUL Listed to C22.2, no. 42, file no. E3663 L2-20 NOM certified
Environmental Specifications	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)
Electrical Specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload at 200% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)
Mechanical Specifications	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated, nickel plated (neutral screw) Ground screw: #8-32 brass plated (green) Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: EPDM	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass, tin plated Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated, nickel plated (neutral screw) Ground screw: #8-32 brass plated (green) Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: Neoprene	Outer shell: Nylon Interior body: Nylon Terminal retainer: Nylon Blades: Brass Line contacts: Brass (except L2-20 tin plated) Terminal clamps: Steel, zinc plated Terminal screws: Brass Ground screw: Brass Assembly screws: Steel, nickel plated (except L1-15 steel) Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: Neoprene

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices specification & performance data

20 & 30A Ultra grip plugs & connectors
NEMA L5-20, L6-20, L11-20, L15-20, L7-20, L8-20, L16-20, L18-20, L21-20, L10-20, L14-20, L19-20, L22-20, L20-20, L23-20, L5-30, L6-30, L11-30, L15-30, L7-30, L8-30, L16-30, L17-30, L18-30, L21-30, L10-30, L14-30, L19-30, L22-30, L20-30, L23-30, L25-30
Non-NEMA 30A

20 & 30A Auto grip plugs & connectors
NEMA L12-20, L9-20, L12-30, L9-30, L13-30, L26-30

20A Safety grip plugs & connectors
NEMA L24-20, Non-NEMA 20A

Wiring type	Back wire	Back wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E3663, except L10-30: UL Listed; L2120_F & L2130_F series not listed L8-30 cUL Listed to C22.2, no. 42, file no. E3663 NOM certified, except L8-30, L10-30, L22-30, L2120_F series 	<ul style="list-style-type: none"> cULus Listed to UL498 and C22.2, no. 42-10, UL file E15012 Fed Spec WC-596H for 25-30 and 26-30 	<ul style="list-style-type: none"> cULus Listed to UL498 and C22.2, no. 42-10, UL file E15012 Fed Spec WC-596H for 25-30 and 26-30
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F) Except flat cable: -40°C to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F) Except L24-20: -40°C to 75°C (-40°F to 167°F)
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #18 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #16 - #8 AWG (except L24-20 #18 - #8) Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass, tin plated Terminal clamps: Steel, tin plated Terminal screws: #10-32 brass, zinc plated (neutral screw) Ground screw: #10-32 brass Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: EPDM	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass Terminal clamps: Steel Terminal screws: #10-32 brass, zinc plated (neutral screw) Ground screw: #10-32 brass Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, zinc plated Gasket/dust shield: EPDM	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass Terminal clamps: Steel Terminal screws: #8-32 brass zinc plated (neutral screw), (except L24-20 brass) Ground screw: #8-32 brass plated (green) Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: Neoprene

15A Single & duplex receptacles
NEMA L5-15, L6-15, L7-15, Non-NEMA 15/10A

15A Single & duplex receptacles
NEMA L1-15

15A Isolated ground receptacles
NEMA L5-15, L6-15

20A Single receptacle
NEMA L2-20, L24-20

Wiring type	Back & side wire	Back & side wire	Back & side wire	Back & side wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. 2369 UL verified to Fed Spec WC-596G, except CWL515R Non NEMA: UL recognized component, file no. E2369 CSA certified to C22.2, no. 42 	<ul style="list-style-type: none"> UL recognized component, file no. E2369 	<ul style="list-style-type: none"> Listed to UL498, file no. 2369 CSA certified to C22.2, no. 42, except IGL615R 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369
Environmental specifications	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 115°C (-40°F to 239°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 115°C (-40°F to 239°F)	Flammability: Meets UL94 requirements; V0 rated, (except L24-20; V2 rated) Temperature rating: -40°C to 105°C (-40°F to 221°F), (except L24-20, -40°C to 115°C (-40°F to 239°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC), (except Non-NEMA 15/10A, Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device
Material specifications	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick pre-plated steel Auto ground clip: N/A Line contacts: 0.036" thick brass Terminal screws: #8-32 brass screws, nickel plated Ground screw: #8-32 brass screw (green) Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick pre-plated steel Auto ground clip: Yes Line contacts: 0.036" thick brass Terminal screws: #8-32 brass Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick pre-plated steel Auto ground clip: Yes Line contacts: 0.036" thick brass Terminal screws: #8-32 brass screws, nickel plated Ground screw: #8-32 brass screw (green) Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated (except L24-20, brass) Auto ground clip: Yes Line contacts: 0.036" thick brass, bronze (except L24-20, brass) Terminal screws: #8-32 brass, tin plated (except L24-20, brass) Ground screw: N/A (except L24-20, brass) Mounting screws: Steel, zinc plated

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices specification & performance data

	20A Single receptacles NEMA L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, Non-NEMA 20A	30A Single receptacles NEMA L5-30, L6-30, L7-30, L8-30, L9-30, L10-30, L11-30, L12-30, L13-30, L14-30, L15-30, L16-30, L17-30, L18-30, L19-30, L20-30, L21-30, L22-30, L23-30, L25-30, L26-30 Non-NEMA 30A	20 & 30A Isolated ground single receptacles NEMA L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, L25-30, L26-30
Wiring type	Back & side wire	Back & side wire	Back & side wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 NEMA L5-20, L6-20, L7-20, L10-20, L14-20, L15-20, L18-20 & L21-20 also UL verified to Fed Spec WC-596G CSA certified to C22.2, no. 42 except 7310B, NEMA L11-20, L12-20, 7410B, L18-20, L19-20, L20-20 NEMA L11-20, L14-20, L15-20, L18-20, L21-20, L22-20 also NOM certified 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 NEMA L5-30, L6-30, L7-30, L14-30, L15-30, L20-30, L21-30, L23-30 also UL verified to Fed Spec WC-596G CSA certified to C22.2, no. 42 except NEMA L11-20, L12-20, AH3330-2, L10-30, L11-30, L12-30, L13-30, AH3430, L18-30, L19-30, L20-30 NEMA L5-30, L10-30, L11-30, L14-30, L15-30, L18-30 also NOM certified 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 CSA certified to C22.2, no. 42 except NEMA L5-30 NOM certified, except for L7-20, L8-20, L6-30, L7-30, L8-30, L16-20, L21-30, L22-30, L23-30
Environmental specifications	Flammability: Meets UL94 requirements; V0 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: w/o impact -40°C to 70°C (-40°F to 158°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device
Material specifications	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated Line contacts: 0.041" thick brass Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Terminal Clamps/Plates: 0.041" thick brass Ground Contacts: 0.041" thick brass Back Plate: 0.041" thick brass, nickel plated Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated Line contacts: 0.041" thick brass Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Terminal Clamps/Plates: 0.041" thick brass Ground Contacts: 0.041" thick brass Back Plate: 0.041" thick brass, nickel plated Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated Line contacts: 0.041" thick brass Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Terminal Clamps/Plates: 0.041" thick brass Ground Contacts: 0.041" thick brass Back Plate: 0.041" thick brass, nickel plated Mounting screws: Steel, zinc plated

	15A Flanged inlets & outlets NEMA L5-15, L6-15, L7-15	15 & 20A Flanged inlets & outlets NEMA L1-15, L2-20	20 & 30A Flanged inlets & outlets NEMA L5-20, L6-20, L8-30, L11-20, L14-30, L14-30, L21-30, L21-30
Wiring type	Back wire	Side wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 CWL615FI, CWL715FI also cUL listed to UL498, file no. E3663 CWL615FI also UL verified to Fed Spec WC-596/102-1 CSA certified to C22.2, no. 42 except CWL515FO 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 	<ul style="list-style-type: none"> AHL520FI, AHL520FO, AHL1430FI, AHL2130FI listed to UL498, file no. E2369; AHL1430FI, AHL2130FI is file no. E3663 AHL620FI, AHL830FI, AHL1120FO cULus Listed to UL498, file no. E3663 AHL520FO, AHL1430FI, AHL2130FI, AHL2130FO also CSA certified to C22.2, no. 42 AHL830FI, AHL1120FO, AHL1430FO CSA certified to C22.2, no. 42 AHL1430FI, AHL1430FO, AHL2130FI, AHL2130FO NOM certified
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets: max. 30°C (86°F) @ maximum rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets: max. 30°C (86°F) @ maximum rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets: max. 30°C (86°F) @ maximum rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG (L2-20 #14 - #10 AWG) Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #8-32 brass Ground screw: #8-32 brass (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Plated brass Interior body: GF Nylon (L1-15FI, Phenolic) Terminal retainer: N/A Blades: 0.062" thick brass Line contacts: 0.031" thick brass (L1-15, 0.032" thick bronze) Terminal clamps: N/A Terminal screws: #6-32 brass Ground screw: #8-32 brass (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices specification & performance data

20 & 30A Flanged inlets
NEMA L7-20, L8-20, L5-30, L6-30, L7-30, L10-20, L11-20, L10-30, L11-30, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, L21-20, L22-20, L23-20, L22-30, L23-30, Non-NEMA 20 & 30A, Non-NEMA 20/10A

20 & 30A Flanged outlets
NEMA L8-20, L6-30, L7-30, L8-30, L10-20, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L21-20, L22-20, L23-20, L22-30, L23-30

20 & 30A Flanged outlets
NEMA L6-20, L7-20, L5-30, L10-30, L11-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, Non-NEMA 20 & 30A, Non-NEMA 20/10A

Wiring type	Back wire	Back wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498 file no. E3663 cUL Listed to UL498, file no. E3663 	<ul style="list-style-type: none"> Listed to UL498 file no. E2369 CSA certified to C22.2, no. 42 	<ul style="list-style-type: none"> Listed to UL498 file no. E2369 CSA certified to C22.2, no. 42
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) @ maximum rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: N/A Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass plated (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: N/A Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass plated (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: N/A Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass plated (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated

Compliances, specifications and availability are subject to change without notice.

Arrow Hart straight blade & locking devices certifications & compliances

Straight blade devices

Catalog no.	cULus	UL	CSA	FUS	NOM	NAFTA	RoHS
AH5246	•			•	•		•
AH5266	•			•		•	•
AH5266A	•			•		•	•
AH5266BK	•			•		•	•
AH5269	•			•		•	•
AH5269BK	•			•		•	•
AH5278	•				•		•
AH5278C	•			•			•
AH5279C		•	•			•	•
AH5364BK	•			•			•
AH5364Y	•			•			•
AH5366	•			•			•
AH5369	•			•			•
AH5369BK	•			•			•
AH5369Y	•			•			•
AH5464BK	•			•			•
AH5464Y	•			•			•
AH5466	•			•		•	•
AH5469	•			•		•	•
AH5469BK	•			•			•
AH5469Y	•			•			•
AH5666	•			•		•	•
AH5666BK	•			•			•
AH5666Y	•			•			•
AH5669	•			•		•	•
AH5669BK	•			•			•
AH5669Y	•			•			•
AH5678C	•			•		•	•
AH5679C		•				•	•
AH5778C	•			•		•	•
AH5779C		•				•	•
AH5878C	•			•		•	•
AH5879C		•				•	•
AH5965BK	•			•			•
AH5965Y	•			•			•
AH5969BK	•			•			•
AH5969Y	•			•			•
AH8115W				•			•
AH8119W	•			•			•
AH8215HG	•			•		•	•
AH8215HGA	•			•		•	•
AH8215HGAC	•			•		•	•
AH8215HGC	•			•		•	•
AH8219HG	•			•		•	•
AH8219HGC	•			•		•	•
AH8225HGA	•			•			•
AH8225HGAC	•			•			•
AH8315HG	•			•		•	•
AH8315HGA	•			•		•	•
AH8315HGAC	•			•		•	•
AH8319HG	•			•		•	•
AH8325HG	•			•			•
AH8325HGAC	•			•			•

Locking devices

Catalog no.	cULus	UL	CSA	FUS	RU	cRUus	NOM	NAFTA	RoHS
4700		•	•	•					•
4750		•	•	•				•	•
4755						•		•	•
4767						•		•	•
4767AN						•		•	•
5792		•	•					•	•
6580		•	•	•					•
7310B		•							•
7314C	•							•	•
7327N	•							•	•
7328N		•							•
7408N	•								•
7409N		•							•
7410B		•							•
7411C	•						•	•	•
7413C	•							•	•
7506	•								•
7540		•							•
7546	•								•
7548	•								•
7580					•			•	•
7582					•			•	•
9965C	•							•	•
AHCL3330R		•						•	•
AH3331N	•							•	•
AH3333N	•							•	•
AH3336N		•						•	•
AH3337N	•							•	•
AHCL3430R		•						•	•
AH3431N	•							•	•
AH3433N	•							•	•
AH3434N	•								•
AH3436N	•								•
AH3521BK	•								•
AH3523BK	•								•
AH3524BK	•								•
AH3525BK		•							•
AHCL1020C	•						•	•	•
AHCL1020FI	•						•	•	•
AHCL1020FO	•						•	•	•
AHCL1020P	•						•	•	•
AHCL1020R		•		•			•	•	•
AHCL1030C	•						•	•	•
AHCL1030FI	•						•	•	•
AHCL1030FO	•						•	•	•
AHCL1030P	•						•	•	•
AHCL1030R		•					•	•	•
AHCL1120C	•						•	•	•
AHCL1120FI	•						•	•	•
AHCL1120FO	•						•	•	•
AHCL1120P	•						•	•	•
AHCL1120R		•					•	•	•
AHCL1130C	•						•	•	•

KEY: cULus cULus UL CSA FUS Fed Spec RU RU cRUus NOM NAFTA RoHS

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Compliances, specifications and availability are subject to change without notice.

Arrow Hart locking devices certifications & compliances

Locking devices

Catalog no.	cULus	UL	CSA	FUS	RU	cRUus	NOM	NAFTA	ROHS
AHCL1130FI	•						•	•	•
AHCL1130FO	•						•		•
AHCL1130P	•						•		•
AHCL1130R		•					•	•	•
AHCL1420C	•						•	•	•
AHCL1420FI	•						•	•	•
AHL1420FIBK	•						•	•	•
AHCL1420FO	•						•	•	•
AHL1420FOBK		•	•						•
AHCL1420P	•						•	•	•
AHCL1420R		•	•	•			•	•	•
AHCL1430C	•						•	•	•
AHCL1430FI	•						•	•	•
AHCL1430FO	•						•	•	•
AHCL1430P	•						•	•	•
AHCL1430R		•	•	•			•	•	•
AHCL1520C	•						•	•	•
AHL1520CBK	•						•	•	•
AHCL1520FI	•						•	•	•
AHCL1520FO	•						•	•	•
AHCL1520P	•						•	•	•
AHCL1520PBK	•						•	•	•
AHCL1520R		•	•	•			•	•	•
AHCL1530C	•						•	•	•
AHCL1530FI	•						•	•	•
AHCL1530FO	•						•	•	•
AHCL1530P	•						•	•	•
AHCL1530R		•	•	•			•	•	•
AHCL1620C	•						•	•	•
AHCL1620FI	•						•	•	•
AHCL1620FO	•						•	•	•
AHCL1620P	•						•	•	•
AHCL1620R		•	•				•	•	•
AHCL1630C	•						•	•	•
AHCL1630FI	•						•	•	•
AHCL1630FO	•						•	•	•
AHCL1630P	•						•	•	•
AHCL1630R		•	•				•	•	•
AHCL1730C	•						•	•	•
AHCL1730FI	•						•	•	•
AHCL1730FO	•						•	•	•
AHCL1730P	•						•	•	•
AHCL1730R		•	•				•	•	•
AHCL1820C	•						•	•	•
AHCL1820FI	•						•		•
AHCL1820FO	•						•		•
AHCL1820P	•						•	•	•
AHCL1820R		•		•			•	•	•
AHCL1830C	•						•	•	•
AHCL1830P	•						•	•	•
AHCL1830R		•					•	•	•
AHCL1920C	•						•	•	•
AHCL1920FI	•						•	•	•

KEY: cULus cULus UL CSA FUS Fed Spec RU cRUus NOM NAFTA ROHS

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Locking devices

Catalog no.	cULus	UL	CSA	FUS	RU	cRUus	NOM	NAFTA	ROHS
AHCL1920FO		•					•		•
AHCL1920P	•						•	•	•
AHCL1920R		•					•	•	•
AHCL2020C	•						•	•	•
AHCL2020FI	•						•	•	•
AHCL2020FO	•						•		•
AHCL2020P	•						•	•	•
AHCL2020R		•					•	•	•
AHCL2120C	•						•	•	•
AHL2120CBK	•						•	•	•
AHL2120CF							•	•	•
AHCL2120FI	•						•	•	•
AHCL2120FO	•						•		•
AHCL2120P	•						•	•	•
AHL2120PBK	•						•	•	•
AHL2120PF							•	•	•
AHCL2120R		•	•	•			•	•	•
AHCL2130C	•						•	•	•
AHL2130CF							•	•	•
AHCL2130FI	•						•	•	•
AHCL2130FO	•						•	•	•
AHCL2130P	•						•	•	•
AHL2130PF							•	•	•
AHCL2130R		•		•			•	•	•
AHCL2220C	•						•	•	•
AHCL2220FI	•						•		•
AHCL2220FO	•						•	•	•
AHCL2220P	•						•	•	•
AHCL2220R		•	•				•	•	•
AHCL2320C	•						•	•	•
AHCL2320FI	•						•	•	•
AHCL2320FO	•						•		•
AHCL2320P	•						•	•	•
AHCL2320R		•	•				•	•	•
AHL2530P	•						•		•
AHL2530C	•						•		•
AHL2530R	•						•		•
AHL2630P	•						•		•
AHL2630C	•						•		•
AHL2630R	•						•		•
AHCL520C	•						•	•	•
AHCL520FI	•						•	•	•
AHCL520FO	•						•	•	•
AHCL520P	•						•	•	•
AHCL520R		•	•	•			•		•
AHCL530C	•						•	•	•
AHCL530P	•						•	•	•
AHCL530R		•	•	•			•	•	•
AHCL620C	•						•	•	•
AHCL620FI	•						•	•	•
AHCL620FO	•						•	•	•
AHCL620P	•						•	•	•
AHCL620R		•	•	•			•	•	•

KEY: cULus cULus UL CSA FUS Fed Spec RU cRUus NOM NAFTA ROHS

Compliances, specifications and availability are subject to change without notice.

Arrow Hart locking devices certifications & compliances

Locking devices

Catalog no.	cULus	UL	CSA	FCS	RU	cRUus	NOM	NAFTA	ROHS
AHCL630C	•							•	•
AHCL630FI	•							•	•
AHCL630FO	•							•	•
AHCL630P	•							•	•
AHCL630R		•	•	•				•	•
AHCL720C	•							•	•
AHCL720FI	•							•	•
AHCL720FO	•							•	•
AHCL720P	•							•	•
AHCL720R		•	•	•				•	•
AHCL730C	•							•	•
AHCL730FI	•							•	•
AHCL730FO	•							•	•
AHCL730P	•							•	•
AHCL730R		•	•	•				•	•
AHCL820C	•							•	•
AHCL820FI	•							•	•
AHCL820FO	•							•	•
AHCL820P	•							•	•
AHCL820R		•	•					•	•
AHCL830C	•							•	•
AHCL830FI	•							•	•
AHCL830FO	•							•	•
AHCL830P	•							•	•
AHCL830R		•	•					•	•
CWL115FI	•							•	•
CWL115FO	•							•	•
CWL115R		•						•	•
CWL1220C	•							•	•
CWL1220FI	•							•	•
CWL1220FO	•							•	•
CWL1220P	•							•	•
CWL1220R		•						•	•
CWL1230C		•	•					•	•
CWL1230FI		•	•					•	•
CWL1230FO	•	•						•	•
CWL1230P		•	•					•	•
CWL1230R		•						•	•
CWL1330C		•	•					•	•
CWL1330FI		•	•					•	•
CWL1330FO	•							•	•
CWL1330P		•	•					•	•
CWL1330R		•						•	•
CWL1830FI	•							•	•
CWL1830FO	•							•	•
CWL220C	•						•	•	•
CWL220FO	•							•	•
CWL220P	•						•	•	•
CWL220R		•						•	•
CWL515FI	•							•	•
CWL515FO	•							•	•
CWL515R		•	•	•				•	•
CWL530FI	•							•	•

KEY: cULus UL CSA FCS Fed Spec RU cRUus NOM NAFTA ROHS

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Compliances, specifications and availability are subject to change without notice.

Locking devices


































Catalog no.	cULus	UL	CSA	FCS	RU	cRUus	NOM	NAFTA	ROHS
CWL530FO	•							•	•
CWL615C	•			•				•	•
CWL615FI	•			•				•	•
CWL615FO	•			•				•	•
CWL615P	•			•				•	•
CWL615R		•	•	•				•	•
CWL715C	•			•				•	•
CWL715FI	•			•				•	•
CWL715FO	•			•				•	•
CWL715P	•			•				•	•
CWL715R		•	•	•				•	•
CWL920C		•	•					•	•
CWL920FI		•	•					•	•
CWL920FO	•							•	•
CWL920P		•	•					•	•
CWL920R		•	•					•	•
CWL930C	•							•	•
CWL930FI	•							•	•
CWL930FO	•							•	•
CWL930P	•							•	•
CWL930R		•	•					•	•
IG4700		•	•					•	•
IGL515R		•	•					•	•
IGL520R		•	•				•	•	•
IGL530P	•							•	•
IGL530R		•	•					•	•
IGL615R		•	•	•				•	•
IGL620R		•	•	•			•	•	•
IGL630R	•	•						•	•
IGL720R		•	•	•				•	•
IGL730R		•	•					•	•
IGL820R		•	•				•	•	•
IGL830R		•	•					•	•
IGL1420R		•	•					•	•
IGL1430R		•	•				•	•	•
IGL1520R		•	•	•			•	•	•
IGL1530R		•	•				•	•	•
IGL1620R		•	•				•	•	•
IGL2120R		•	•				•	•	•
IGL2130R		•	•				•	•	•
IGL2530R	•			•				•	•
IGL2630R	•			•				•	•
L2420P	•							•	•
L2420R			•					•	•

Arrow Hart quick reference guide

Pole-Wire	Amp.	V/AC	NEMA		Page	Grip style	Plug	Connector	Single Receptacle	Duplex Receptacle	Flanged Inlet	Flanged Outlet			
2P-2W	15	125	L1-15		11	Safety	7546	7506	CWL115R	7540	CWL115FI	CWL115FO			
	20	125	L2-20		12	Safety	CWL220P	CWL220C	CWL220R			CWL220FO			
2P-3W	15	125	5-15		9, 10	Ultra	AH5266 AH5266BK AH8215HG	AH5269 AH5269BK AH8219HG				AH5278 AH5278C	AH5246 AH5279C		
						9, 10	Safety	AH5266A AH8215HGA AH8215HGAC AH8215HGC	AH8219HGC						
						9, 10	Auto	5266NHG IG5266NHG 5266N	5269NHG 5269N						
						10	Quick	AH5965BK AH5965Y AH8115W	AH5969BK AH5969Y AH8119W						
	125	L5-15		11	Safety	CWL515P CWL515PAN	CWL515C CWL515CAN	CWL515R IGL515R	4700 5792 IG4700		CWL515FI	CWL515FO			
	250	6-15		10	Ultra	AH5666	AH5669					AH5678C	AH5679C		
					9	Safety	AH8225HGA AH8225HGAC								
					10	Auto	5666N	5669N							
					10	Quick	AH5666BK AH5666Y	AH5669BK AH5669Y							
	250	L6-15		11	Safety	CWL615P	CWL615C	CWL615R IGL615R	6580		CWL615FI	CWL615FO			
	277	L7-15		11	Safety	CWL715P	CWL715C	CWL715R	4750		CWL715FI	CWL715FO			
	20	125	5-20		9, 10	Ultra	AH5366 AH8315HG	AH5369 AH8319HG					AH5778C	AH5779C	
						9	Safety	AH8315HGA AH8315HGAC							
						9	Auto	5366NHG	5369NHG						
						10	Quick	AH5364BK AH5364Y	AH5369BK AH5369Y						
		125	L5-20		12	Ultra	AHCL520P	AHCL520C	AHCL520R IGL520R			AHCL520FI	AHCL520FO		
		250	6-20		10	Ultra	AH5466	AH5469					AH5878C	AH5879C	
						9	Safety	AH8325HG AH8325HGAC							
						10	Auto	5466N	5469N						
						10	Quick	AH5464BK AH5464Y	AH5469BK AH5469Y						
		250	L6-20		12	Ultra	AHCL620P	AHCL620C	AHCL620R IGL620R			AHCL620FI	AHCL620FO		
		277	L7-20		12	Ultra	AHCL720P	AHCL720C	AHCL720R IGL720R			AHCL720FI	AHCL720FO		
347		L24-20		12	Safety	L2420P			L2420R						
480	L8-20		12	Ultra	AHCL820P	AHCL820C	AHCL820R IGL820R			AHCL820FI	AHCL820FO				
600	L9-20		12	Auto	CWL920P	CWL920C	CWL920R			CWL920FI	CWL920FO				
30	125	L5-30		14	Ultra	AHCL530P AHIGL530P	AHCL530C	AHCL530R IGL530R			AHCL530FI	AHCL530FO			
	240	L25-30		14	Ultra	AHL2530P	AHL2530C	AHL2530R IGL2530R							
	250	L6-30		15	Ultra	AHCL630P	AHCL630C	AHCL630R IGL630R			AHCL630FI	AHCL630FO			
	277	L7-30		15	Ultra	AHCL730P	AHCL730C	AHCL730R IGL730R			AHCL730FI	AHCL730FO			
	480	L8-30		15	Ultra	AHCL830P	AHCL830C	AHCL830R IGL830R			AHCL830FI	AHCL830FO			
	600	L9-30		15	Auto	CWL930P	CWL930C	CWL930R			CWL930FI	CWL930FO			

Compliances, specifications and availability are subject to change without notice.

Arrow Hart quick reference guide

Pole-Wire	Amp.	V/AC	NEMA	Page	Grip style	Plug	Connector	Single Receptacle	Duplex Receptacle	Flanged Inlet	Flanged Outlet	
3P-3W	15/10	125/250	Non-NEMA Locking		11	Safety	4767 4767AN	4755	7582 7580			
	20	125/250	L10-20		12	Ultra	AHCL1020P	AHCL1020C	AHCL1020R		AHCL1020FI	AHCL1020FO
				Non-NEMA Locking		12	Safety	9965C	7314C	7310B	7327N	7328N
		250	L11-20		13	Ultra	AHCL1120P	AHCL1120C	AHCL1120R		AHCL1120FI	AHCL1120FO
		480	L12-20		13	Auto	CWL1220P	CWL1220C	CWL1220R		CWL1220FI	CWL1220FO
	30	125/250	L10-30		15	Ultra	AHCL1030P	AHCL1030C	AHCL1030R		AHCL1030FI	AHCL1030FO
				Non-NEMA Locking		15		AH3331N	AH3333N	AHCL3330R	AH3337N	AH3336N
		250	L11-30		15	Ultra	AHCL1130P	AHCL1130C	AHCL1130R		AHCL1130FI	AHCL1130FO
		480	L12-30		15	Auto	CWL1230P	CWL1230C	CWL1230R		CWL1230FI	CWL1230FO
600		L13-30		16	Auto	CWL1330P	CWL1330C	CWL1330R		CWL1330FI	CWL1330FO	
3P-4W	20	125/250	L14-20		13	Ultra	AHCL1420P	AHCL1420C	AHCL1420R IGL1420	AHCL1420FI AHCL1420FIBK	AHCL1420FO AHL1420FOBK	
		250	L15-20		13	Ultra	AHCL1520P AHL1520PBK	AHCL1520C AHL1520CBK	AHCL1520R IGL1520	AHCL1520FI	AHCL1520FO	
		480	L16-20		13	Ultra	AHCL1620P	AHCL1620C	AHCL1620R IGL1620	AHCL1620FI	AHCL1620FO	
	30	125/250	L14-30		16	Ultra	AHCL1430P	AHCL1430C	AHCL1430R IGL1430	AHCL1430FI	AHCL1430FO	
		250	L15-30		16	Ultra	AHCL1530P	AHCL1530C	AHCL1530R IGL1530	AHCL1530FI	AHCL1530FO	
		480	L16-30		16	Ultra	AHCL1630P	AHCL1630C	AHCL1630R	AHCL1630FI	AHCL1630FO	
		600	L17-30		16	Ultra	AHCL1730P	AHCL1730C	AHCL1730R	AHCL1730FI	AHCL1730FO	
		4P-4W	20	120/208	Non-NEMA Locking		13	Safety	7411C	7413C	7410B	7408N
120/208	L18-20				13	Ultra	AHCL1820P	AHCL1820C	AHCL1820R	AHCL1820FI	AHCL1820FO	
277/480	L19-20				14	Ultra	AHCL1920P	AHCL1920C	AHCL1920R	AHCL1920FI	AHCL1920FO	
347/600	L20-20				14	Ultra	AHCL2020P	AHCL2020C	AHCL2020R	AHCL2020FI	AHCL2020FO	
30	120/208		Non-NEMA Locking		16	Ultra	AH3431N	AH3433N	AHCL3430R	AH3434N	AH3436N	
	120/208		L18-30		16	Ultra	AHCL1830P	AHCL1830C	AHCL1830R	AHCL1830FI	AHCL1830FO	
	277/480		L19-30		17	Ultra	AHCL1930P	AHCL1930C	AHCL1930R	AHCL1930FI	AHCL1930FO	
	347/600		L20-30		17	Ultra	AHCL2030P	AHCL2030C	AHCL2030R	AHCL2030FI	AHCL2030FO	
4P-5W	20	120/208	L21-20		14	Ultra	AHCL2120P AHL2120PBK AHL2120PF	AHCL2120C AHL2120CBK AHL2120CF	AHCL2120R IGL2120	AHCL2120FI	AHCL2120FO	
		277/480	L22-20		14	Ultra	AHCL2220P	AHCL2220C	AHCL2220R	AHCL2220FI	AHCL2220FO	
		347/600	L23-20		14	Ultra	AHCL2320P	AHCL2320C	AHCL2320R	AHCL2320FI	AHCL2320FO	
	20/10	250/600	Non-NEMA Locking		11	Ultra	AH3521BK	AH3523BK		AH3524BK	AH3525BK	
		30	120/208	L21-30		17	Ultra	AHCL2130P AHL2130PF	AHCL2130C AHL2130CF	AHCL2130R IGL2130	AHCL2130FI	AHCL2130FO
			240/415	L26-30		17	Ultra	AHL2630P	AHL2630C	AHL2630R IGL2630R		
			277/480	L22-30		17	Ultra	AHCL2230P AHL2230PF	AHCL2230C AHL2230CF	AHCL2230R IGL2230	AHCL2230FI	AHCL2230FO
			347/600	L23-30		17	Ultra	AHCL2330P AHL2330PF	AHCL2330C AHL2330CF		AHCL2330FI	AHCL2330FO

Compliances, specifications and availability are subject to change without notice.

We make what matters work.*

* At Eaton, we believe that power is a fundamental part of just about everything people do. Technology, transportation, energy and infrastructure-these are things the world relies on every day. That's why Eaton is dedicated to helping our customers find new ways to manage electrical, hydraulic and mechanical power more efficiently, safely and sustainably. To improve people's lives, the communities where we live and work, and the planet our future generations depend upon. Because that's what really matters. And we're here to make sure it works.

See more at Eaton.com/whatmatters

Visit our website:
www.eaton.com/wiringdevices

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. BR630009EN
February 2019

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/wiringdevices

Follow us on social media to get the
latest product and support information.

