

Eaton's Arrow Hart
Industrial grade straight blade & locking devices

Arrow Hart

Superior design and performance make Eaton's straight blade and locking devices the ideal choice for industrial applications

EATON

Powering Business Worldwide

Table of contents	Page
Introduction	3
Features & benefits	4-8
Straight blade devices	9-10
Locking devices	11-18
Accessories	19
Straight blade dimensions	20
Locking dimensions	21-22
Straight blade & locking specifications	23-27
Certifications & compliances	28-30
Quick reference guide	31-33



Complete line of wiring
devices for industrial &
heavy-duty construction
environments

Arrow Hart



From everyday commercial use to heavy-duty industrial applications, Arrow Hart plugs and connectors ensure long lasting, dependable service in the most demanding environments

- A variety of grip styles enabling numerous applications
- Easily identified amperage/voltage ratings clearly marked on devices
- Rugged construction to ensure longer service life

Quick grip

Quick grip plugs and connectors are designed for quick, secure installation and easy, long-lasting use. They feature rugged nylon construction and a roomy wiring chamber for fast and easy installation. Our scalloped ergonomic design provides a comfortable grip during installation and operation.



Safety grip

Safety grip plugs and connectors combine durability and fast installation. Featuring dual-range external cord grip, safety grips provides positive cord gripping while limiting strain on conductors. The neoprene gasket seals around the cord for added terminal protection from external elements. The nylon construction is rugged and durable for dependable use.



Auto grip

Auto grip plugs and connectors feature a unique clamp design that secures cords during assembly and reduces installation time. The rugged tapered nylon body reduces impact and chemical exposure while providing easy handling for end users.



Ultra grip

Built with a contemporary flare and oval ergonomic design for a comfortable yet secure feel, ultra grip plugs and connectors offer excellent reliability and durability. A dual dovetail design provides superior cord grip retention, and the grommet allows usage across a wide range of cord diameters. Additionally, reversible inserts in the cord grip allow for exceptional clamp force on large diameter cords.




Arrow Hart quick grip plugs & connectors

Quick grip hospital and industrial grade plugs & connectors features & benefits

Commercial specification grade straight blade plugs & connectors

Designed for commercial applications, where ease-of-use, value and quality are critical.



Arrow Hart hospital grade straight blade plugs & connectors

Safety grip hospital grade plugs & connectors features & benefits

Hospital specification grade plugs & connectors

Built to meet and exceed UL Federal specification and hospital grade testing, Arrow Hart's hospital grade plugs and connectors assure reliable performance in the most demanding healthcare applications.



Safety grip hospital grade devices exceed federal spec. and hospital grade testing for use in demanding healthcare environments



Clear terminal cover allows for easy inspection of conductors and terminations



Retained quick drive assembly screws speed installation



Four position angled plug option is ideal for applications requiring power cord to lay close to walls and floors



Tapered, individual wire pockets guide stranded wire into contact area for ease of installation



Multiple-head drive screws provide versatility for ease of use

Arrow Hart auto grip plugs & connectors

Auto grip hospital and industrial grade plugs & connectors features & benefits

Industrial specification grade plugs, connectors, flanged inlets & outlets

Auto grip devices are designed for quick and easy installation and provide reliable performance in tough industrial environments.



Auto grip hospital grade devices exceed federal spec. and hospital grade testing for use in demanding healthcare environments



Unique clamp design secures cord during assembly, reducing installation time



Retained quick drive assembly screws speed installation



Multiple-head drive screws provide versatility for ease of use




Tapered, individual wire pockets guide stranded wire into contact area for ease of installation

Arrow Hart industrial grade ultra grip plugs and connectors


Ultra grip locking plugs & connectors redesign features & benefits

The industry's most complete line of locking industrial devices

Superior design and performance make Arrow Hart's locking devices the ideal choice for industrial applications. Available in a wide range of NFMA non-NFMA and flat cable configurations



Auto grip hospital and industrial grade plugs & connectors features & benefits



Arrow Hart industrial grade ultra grip plugs and connectors

Ultra grip receptacles features & benefits

The industry's most complete line of locking industrial devices

Arrow Hart offers the most rugged, feature-rich, broadest line of quality locking devices to meet the specific needs of demanding industrial applications. Available in NEMA and non-NEMA configurations.



Industrial flanged inlets & outlets features & benefits



Arrow Hart hospital grade straight blade plugs & connectors



AH8215HG







AH8219HG







AH8119W

15A Hospital grade straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	  5-15P 5-15R	Ultra grip plug	Black & white	AH8215HG
			Safety grip plug	Clear	AH8215HGC
		Safety grip angled body plug	Black & white	AH8215HGGA	
		Safety grip angled body plug	Clear	AH8215HGAC	
		Quick grip plug	White	AH8115W	
		Auto grip plug	Black & white	5266NHG	
		Auto grip isolated ground plug	Orange	IG5266NHG	
		Ultra grip connector	Black & white	AH8219HG	
		Safety grip connector	Clear	AH8219HGC	
		Quick grip connector	White	AH8119W	
Auto grip connector	Black & white	5269NHG			
2P-3W	250	  6-15P 6-15R	Safety grip angled plug	Black & white	AH8225HGGA
			Safety grip angled plug	Clear	AH8225HGAC

20A Hospital grade straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	  5-20P 5-20R	Ultra grip plug	Black & white	AH8315HG
			Safety grip angled plug	Black & white	AH8315HGGA
			Safety grip angled plug	Clear	AH8315HGAC
			Auto grip plug	Black & white	5366NHG
			Ultra grip connector	Black & white	AH8319HG
			Auto grip connector	Black & white	5369NHG
2P-3W	250	  6-20P 6-20R	Safety grip angled plug	Black & white	AH8325HG
			Safety grip angled plug	Clear	AH8325HGAC

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial straight blade plugs and connectors



AH5266



AH5269



AH5879C







AH5878C







AH5965BK



15A Industrial grade straight blade devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Ultra grip plug	Black & white	AH5266
			Ultra grip plug	Black	AH5266BK
			Safety grip angled body plug	Black & white	AH5266A
			Auto grip plug	Black & white	5266N
			Economy series plug	Black & white	5266
			Economy series angled body plug	Black & white	5266AN
			Ultra grip connector	Black & white	AH5269
			Ultra grip connector	Black	AH5269BK
			Auto grip connector	Black & white	5269N
			Economy series connector	Black & white	5269
			Flanged outlet, back wire	Black & white	5279C
			Flanged outlet, back wire, metal	Steel	5246
			Flanged inlet, back wire	Black & white	5278C
			Flanged inlet, back wire, metal	Steel	5278
250		 	Ultra grip plug	Black & white	AH5666
			Auto grip plug	Black & white	5666N
			Economy Series plug	Black & white	5666
			Economy Series angles body plug	Black & white	5666AN
			Ultra grip connector	Black & white	AH5669
			Auto grip connector	Black & white	5669N
			Economy series connector	Black & white	5669
			Flanged outlet, back wire, nylon	Black & white	5679C
			Flanged inlet, back wire, nylon	Black & white	5678C

20A Industrial grade straight blade devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Ultra grip plug	Black & white	AH5366
			Auto grip plug	Black & White	5366N
			Economy series plug	Black	5366
			Economy series angled body plug	Black	5366AN
			Ultra grip connector	Black & white	AH5369
			Auto grip connector	Black & White	5369N
			Economy series connector	Black	5369
			Flanged outlet, back wire, nylon	Black & white	5779C
			Flanged inlet, back wire, nylon	Black & white	5778C
			250		 
Auto grip plug	Black & white	5466N			
Economy series plug	Black & white	5466			
Economy series angled body plug	Black & white	5466AN			
Ultra grip connector	Black & white	AH5469			
Auto grip connector	Black & white	5469N			
Economy series connector	Black & white	5469			
Flanged outlet, back wire	Black & white	5879C			
Flanged inlet, back wire	Black & white	5878C			

15A Industrial grade quick grip straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Quick grip plug	Black	AH5965BK
			Quick grip plug	Yellow	AH5965Y
			Quick grip connector	Black	AH5969BK
			Quick grip connector	Yellow	AH5969Y

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade straight blade and locking devices



CWL515P



CWL515C



CWL515R





CWL515FO







CWL515FI

Accessories:
page 19
Dimensions & cord diameters:
pages 20-22
Spec information:
pages 23-27
Compliances:
pages 28-30



15A Industrial grade quick grip straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no
2P-3W	250	 	Quick grip plug	Black	AH5666BK
			Quick grip plug	Yellow	AH5666Y
		Quick grip connector	Black	AH5669BK	
		Quick grip connector	Yellow	AH5669Y	





20A Industrial grade quick grip straight blade plugs & connectors

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125	 	Quick grip plug	Black	AH5364BK
			Quick grip plug	Yellow	AH5364Y
		Quick grip connector	Black	AH5369BK	
		Quick grip connector	Yellow	AH5369Y	
	250	 	Quick grip plug	Black	AH5464BK
			Quick grip plug	Yellow	AH5464Y
		Quick grip connector	Black	AH5469BK	
		Quick grip connector	Yellow	AH5469Y	

15/10A Industrial grade locking devices

Pole-Wire	V/AC	NON-NEMA	Description	Color	Catalog no.
3P-3W	125/ 250	 	Safety grip plug	Black & white	4767
			Safety grip angled body plug	Black & white	4767AN
			Auto grip plug	Black & white	4597N
			Safety grip connector	Black & white	4755
			Auto grip connector	Black & white	7565N
			Duplex receptacle	Black	7580
			Single receptacle	Black	7582

15A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.			
2P-2W	125	 	Standard industrial plug	Black	7546			
			Standard industrial plug	Black	7548			
			Economy series plug	Black & white	L115P			
			Standard industrial connector	Black	7506			
			Duplex receptacle	Black	7540			
			Single receptacle	Black	CWL115R			
			Flanged outlet	Black	CWL115FO			
			Flanged inlet	Black	CWL115FI			
				125	 	Safety grip plug	Black & white	CWL515P
						Safety grip angled body plug	Black & white	CWL515PAN
Auto grip plug	Black & White	4721N						
Auto grip plug	White	4721NW						
Armored vinyl plug	Yellow	2473						
Economy series plug	Black & White	4720						
Safety grip connector	Black & white	CWL515C						
Safety grip angled body connector	Black & white	CWL515CAN						
Auto grip connector	Black & white	4731N						
Armored vinyl connector	Yellow	2493						
Economy series connector	Black & white	4729						
Duplex receptacle	Black	4700						
Duplex combination straight blade & locking	Black	5792						
Single receptacle	Black	CWL515R						
Duplex receptacle, isolated ground	Orange	IG4700						
Single receptacle, isolated ground	Orange	IGL515R						
Flanged outlet	Black & white	CWL515FO						
Flanged inlet	Black & white	CWL515FI						

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL520P



AHCL520C



AHCL520R



AHCL520FO



AHCL520FI

15A Industrial grade locking devices (continued)

Pole-Wire	V/AC	NON-NEMA	Description	Color	Catalog no.
2P-3W	250	 L6-15R L6-15P	Safety grip plug	Black & white	CWL615P
			Auto grip plug	Black & white	6565N
			Economy series plug		4570
			Safety grip connector	Black & white	CWL615C
			Auto grip connector	Black & white	6566N
			Economy series connector	Black & white	4579
			Duplex receptacle	Black	6580
			Single receptacle	Black	CWL615R
			Single receptacle, economy series	Black	4560
			Single receptacle, isolated ground	Orange	IGL615R
277		 L7-15R L7-15P	Safety grip plug	Black & white	CWL715P
			Auto grip plug	Black & white	4771N
			Economy series plug	Black & white	4770
			Safety grip connector	Black & white	CWL715C
			Auto grip connector	Black & white	4772N
			Duplex receptacle	Black	4750
			Single receptacle	Black	CWL715R
			Flanged outlet	Black & white	CWL715FO
			Flanged inlet	Black & white	CWL715FI

20/10A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
4P-5W	250/ 600	 Receptacle Plug	Ultra grip plug	Black & white	AH3521BK
			Ultra grip connector	Black & white	AH3523BK
			Flanged outlet	Black	AH3525BK
			Flanged inlet	Black	AH3524BK

20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-2W	250	 L2-20R L2-20P	Safety grip plug	Black & white	CWL220P
			Safety grip plug, polarized	Black & white	CWL220P-6
			Safety grip connector	Black & white	CWL220C
			Single receptacle	Black	CWL220R
			Flanged outlet	Black & white	CWL220FO
2P-3W	125	 L5-20R L5-20P	Color coded ultra grip plug	Yellow & black	AHCL520P
			Armored vinyl plug	Yellow	2363
			Economy series plug	Black & white	L520P
			Color coded ultra grip connector	Yellow & black	AHCL520C
			Armored vinyl connector	Yellow	2353
			Economy series connector	Black & white	L520C
			Color coded single receptacle	Yellow & black	AHCL520R
			Single receptacle, isolated ground	Orange	IGL520R
			Single receptacle, economy series	Black	L520R
			Color coded flanged outlet	Yellow & black	AHCL520FO
			Color coded flanged inlet	Yellow & black	AHCL520FI

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL620P



AHCL620C



AHCL620R



AHCL620FO



AHCL620FI

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30















20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.							
2P-3W	250	 L6-20R	 L6-20P	Color coded ultra grip plug	Blue & black	AHCL620P						
				Armored vinyl plug	Yellow	2364						
						Economy series plug	Black & white	L620P				
						Color coded ultra grip connector	Blue & black	AHCL620C				
						Armored vinyl connector	Yellow	2354				
						Economy series connector	Black & white	L620C				
						Color coded single receptacle	Blue & black	AHCL620R				
						Single receptacle, isolated ground	Orange	IGL620R				
						Single receptacle, economy series	Black	L620R				
						Color coded flanged outlet	Blue & black	AHCL620FO				
Color coded flanged inlet	Blue & black	AHCL620FI										
277		 L7-20R	 L7-20P	Color coded ultra grip plug	Gray & black	AHCL720P						
				Color coded ultra grip connector	Gray & black	AHCL720C						
						Color coded single receptacle	Gray & black	AHCL720R				
						Single receptacle, isolated ground	Orange	IGL720R				
						Colored coded flanged outlet	Gray & black	AHCL720FO				
						Colored coded flanged inlet	Gray & black	AHCL720FI				
347		 L24-20R	 L24-20P	Standard industrial plug	Black & white	L2420P						
				Single receptacle	Black	L2420R						
480		 L8-20R	 L8-20P	Color coded ultra grip plug	Red & black	AHCL820P						
				Color coded ultra grip connector	Red & black	AHCL820C						
						Color coded single receptacle	Red & black	AHCL820R				
						Single receptacle, isolated ground	Orange	IGL820R				
						Color coded flanged outlet	Red & black	AHCL820FO				
						Color coded flanged inlet	Red & black	AHCL820FI				
600		 L9-20R	 L9-20P	Standard Industrial plug	Black & white	CWL920P						
				Standard Industrial connector	Black & white	CWL920C						
						Single receptacle	Black	CWL920R				
						Flanged outlet	Black & white	CWL920FO				
						Flanged inlet	Black & white	CWL920FI				
						3P-3W	125/250	 Receptacle	 Plug	Standard Industrial plug	Gray	9965C
Standard Industrial connector	Gray	7314C										
Single receptacle	Black	7310B										
Flanged outlet	Gray	7328N										
Flanged inlet	Gray	7327N										
		 L10-20R	 L10-20P	Colored coded ultra grip plug	Orange & black	AHCL1020P						
				Armored vinyl plug	Yellow	2365						
						Colored coded ultra grip connector	Orange & black	AHCL1020C				
						Armored vinyl connector	Yellow	2355				
						Single receptacle, economy series	Black	L620R				
						Colored coded single receptacle	Orange & black	AHCL1020R				
						Colored coded flanged outlet	Orange & black	AHCL1020FO				
						Colored coded flanged inlet	Orange & black	AHCL1020FI				
						250		 L11-20R	 L11-20P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1120P
										Color coded ultra grip connector, 3-phase	Blue & black	AHCL1120C
				Color coded single receptacle, 3-phase	Blue & black			AHCL1120R				
				Color coded flanged outlet, 3-phase	Blue & black			AHCL1120FO				
				Color coded flanged inlet, 3-phase	Blue & black			AHCL1120FI				
480		 L12-20R	 L12-20P	Standard industrial plug, 3-phase	Black & white	CWL1220P						
				Standard industrial connector, 3-phase	Black & white	CWL1220C						
						Single receptacle, 3-phase	Black	CWL1220R				
						Flanged outlet, 3-phase	Black & white	CWL1220FO				
				Flanged inlet, 3-phase	Black & white	CWL1220FI						

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices

20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.		
3P-4W	125/250	  L14-20R L14-20P	Color coded ultra grip plug	Orange & black	AHCL1420P		
			Economy series plug	Black & white	L1420P		
		Color coded ultra grip connector	Orange & black	AHCL1420C			
		Economy series connector	Black & white	L1420C			
		Color coded single receptacle	Orange & black	AHCL1420R			
		Single receptacle, isolated ground	Orange	IGL1420R			
		Single receptacle, economy series	Black	L1420R			
		Color coded flanged outlet	Orange & black	AHCL1420FO			
		Color coded flanged inlet	Orange & black	AHCL1420FI			
		250		  L15-20R L15-20P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1520P
Ultra grip plug, 3-phase	Black				AHL1520PBK		
Economy series plug, 3-phase	Black & white			L1520P			
Color coded ultra grip connector, 3-phase	Blue & black			AHCL1520C			
Ultra grip connector, 3-phase	Black			AHL1520CBK			
Economy series connector, 3-phase	Black & White			L1520C			
Color coded single receptacle, 3-phase	Blue & black			AHCL1520R			
Single receptacle, isolated ground, 3-phase	Orange			IGL1520R			
Single receptacle, economy series, 3-phase	Black			L1520R			
Color coded flanged outlet, 3-phase	Blue & black			AHCL1520FO			
Color coded flanged inlet, 3-phase	Blue & black	AHCL1520FI					
480		  L16-20R L16-20P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1620P		
			Ultra grip plug, 3-phase	Black	AHL1620PBK		
		Color coded ultra grip connector, 3-phase	Red & black	AHCL1620C			
		Ultra grip connector, 3-phase	Black	AHL1620CBK			
		Color coded single receptacle, 3-phase	Red & black	AHCL1620R			
		Single receptacle, isolated ground, 3-phase	Orange	IGL1620R			
		Color coded flanged outlet, 3-phase	Red & black	AHCL1620FO			
		Color coded flanged inlet, 3-phase	Red & black	AHCL1620FI			
		4P-4W	120/208	  Receptacle Plug	Standard industrial plug, 3-phase	Gray	7411C
					Standard industrial connector, 3-phase	Gray	7413C
Single receptacle, 3-phase	Black			7410B			
Flanged outlet, 3-phase	Gray			7409N			
Flanged inlet, 3-phase	Gray			7408N			
  L18-20R L18-20P	Color coded ultra grip plug, 3-phase			Blue & black	AHCL1820P		
	Color coded ultra grip connector, 3-phase			Blue & black	AHCL1820C		
	Color coded single receptacle, 3-phase			Blue & black	AHCL1820R		
	Color coded flanged outlet, 3-phase			Blue & black	AHCL1820FO		
	Color coded flanged inlet, 3-phase			Blue & black	AHCL1820FI		
277/480		  L19-20R L19-20P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1920P		
			Color coded ultra grip connector, 3-phase	Red & black	AHCL1920C		
			Color coded single receptacle, 3-phase	Red & black	AHCL1920R		
			Color coded flanged outlet, 3-phase	Red & black	AHCL1920FO		
			Color coded flanged inlet, 3-phase	Red & black	AHCL1920FI		
347/600		  L20-20R L20-20P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2020P		
			Color coded ultra grip connector, 3-phase	Black & black	AHCL2020C		
			Color coded single receptacle, 3-phase	Black & black	AHCL2020R		
			Color coded flanged outlet, 3-phase	Black & black	AHCL2020FO		
			Color coded flanged inlet, 3-phase	Black & black	AHCL2020FI		



AHCL1620P



AHCL1620C



AHCL1620R



AHCL1620FO



AHCL1620FI

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL2320P



AHCL2320C



AHCL2320R



AHCL2320FO



AHCL2320FI

20A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
4P-5W	120/208		Color coded ultra grip plug, 3-phase	Blue & black	AHCL2120P
			Ultra grip plug, 3-phase	Black	AHL2120PBK
		Ultra grip plug, 3-phase, flat cable	Black & white	AHL2120PF	
		Color coded ultra grip connectorw, 3-phase	Blue & black	AHCL2120C	
		Ultra grip connector, 3-phase	Black	AHL2120CBK	
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2120CF	
		Color coded single receptacle, 3-phase	Blue & black	AHCL2120R	
		Single receptacle, isolated ground, 3-phase	Orange	IGL2120R	
		Color coded flanged outlet, 3-phase	Blue & black	AHCL2120FO	
		Color coded flanged inlet, 3-phase	Blue & black	AHCL2120FI	
277/480			Color coded ultra grip plug, 3-phase	Red & black	AHCL2220P
			Color coded ultra grip connector, 3-phase	Red & black	AHCL2220C
		Color coded single receptacle, 3-phase	Red & black	AHCL2220R	
		Color coded flanged outlet, 3-phase	Red & black	AHCL2220FO	
		Color coded flanged inlet, 3-phase	Red & black	AHCL2220FI	
347/600			Color coded ultra grip plug, 3-phase	Black & black	AHCL2320P
			Color coded ultra grip connector, 3-phase	Black & black	AHCL2320C
		Color coded single receptacle, 3-phase	Black & black	AHCL2320R	
		Color coded flanged outlet, 3-phase	Black & black	AHCL2320FO	
		Color coded flanged inlet, 3-phase	Black & black	AHCL2320FI	

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.
2P-3W	125		Color coded ultra grip plug	Yellow & black	AHCL530P
			Ultra grip plug, isolated ground	Orange	IGL530P
		Economy series plug	Black	L530P	
		Color coded ultra grip connector	Yellow & black	AHCL530C	
		Economy series connector	Black	L530C	
		Color coded single receptacle	Yellow & black	AHCL530R	
		Single receptacle, isolated ground	Orange	IGL530R	
		Single receptacle, economy series	Black	L530R	
		Color coded flanged outlet	Yellow & black	AHCL530FO	
		Color coded flanged inlet	Yellow & black	AHCL530FI	
240			Ultra grip plug	Black & white	AHL2530P
			Ultra grip connector	Black & white	AHL2530C
		Single receptacle	Black	AHL2530R	
250			Single receptacle, isolated ground	Orange	IG2530R
			Color coded ultra grip plug	Blue & black	AHCL630P
		Economy series plug	Black & white	L630P	
		Color coded ultra grip connector	Blue & black	AHCL630C	
		Economy series connector	Black & white	L630C	
		Color coded single receptacle	Blue & black	AHCL630R	
		Single receptacle, isolated ground	Orange	IGL630R	
		Single receptacle, economy series	Black	L630R	
		Color coded flanged outlet	Blue & black	AHCL630FO	
		Color coded flanged inlet	Blue & black	AHCL630FI	

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL730P



AHCL730C



AHCL730R



AHCL730FO



AHCL730FI

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.				
2P-3W	277	 L7-30R	 L7-30P	Color coded ultra grip plug	Gray & black	AHCL730P			
				Color coded ultra grip connector	Gray & black	AHCL730C			
		Color coded single receptacle	Gray & black	AHCL730R					
		Single receptacle, isolated ground	Orange	IGL730R					
		Color coded flanged outlet	Gray & black	AHCL730FO					
	480	 L8-30R	 L8-30P	Color coded ultra grip plug	Red & black	AHCL830P			
				Color coded ultra grip connector	Red & black	AHCL830C			
				Color coded single receptacle	Red & black	AHCL830R			
				Single receptacle, isolated ground	Orange	IGL830R			
				Color coded flanged outlet	Red & black	AHCL830FO			
600	 L9-30R	 L9-30P	Color coded flanged inlet	Gray & black	AHCL730FI				
			Standard industrial plug	Black & white	CWL930P				
			Standard industrial connector	Black & white	CWL930C				
			Single receptacle	Black	CWL930R				
			Flanged outlet	Black & white	CWL930FO				
			Flanged inlet	Black & white	CWL930FI				
			3P-3W	125/250	 Receptacle	 Plug	Ultra grip plug	Black & white	AH3331N
							Ultra grip connector	Black & white	AH3333N
							Color coded single receptacle	Orange & black	AHCL3330R
							Flanged outlet	Black & white	AH3336N
Flanged inlet	Black & white	AH3337N							
 L10-30R	 L10-30P	Color coded ultra grip plug			Orange & black	AHCL1030P			
		Color coded ultra grip connector			Orange & black	AHCL1030C			
		Color coded single receptacle			Orange & black	AHCL1030R			
		Color coded flanged outlet			Orange & black	AHCL1030FO			
		Color coded flanged inlet			Orange & black	AHCL1030FI			
250	 L11-30R	 L11-30P	Color coded ultra grip plug, 3-phase	Blue & blue	AHCL1130P				
			Color coded ultra grip connector, 3-phase	Blue & blue	AHCL1130C				
			Color coded single receptacle, 3-phase	Blue & Black	AHCL1130R				
			Color coded flanged outlet, 3-phase	Blue & blue	AHCL1130FO				
			Color coded flanged inlet, 3-phase	Blue & blue	AHCL1130FI				
480	 L12-30R	 L12-30P	Standard industrial plug, 3-phase	Black & white	CWL1230P				
			Standard industrial connector, 3-phase	Black & white	CWL1230C				
			Single receptacle, 3-phase	Black	CWL1230R				
			Flanged outlet, 3-phase	Black & white	CWL1230FO				
			Flanged inlet, 3-phase	Black & white	CWL1230FI				
600	 L13-30R	 L13-30P	Standard industrial plug, 3-phase	Black & white	CWL1330P				
			Standard industrial connector, 3-phase	Black & white	CWL1330C				
			Single receptacle, 3-phase	Black	CWL1330R				
			Flanged outlet, 3-phase	Black & white	CWL1330FO				
			Flanged inlet, 3-phase	Black & white	CWL1330FI				

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices



AHCL1430P



AHCL1430C



AHCL1430R



AHCL1430FO



AHCL1430FI

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.			
3P-4W	125/250	 L14-30R	 L14-30P	Color coded ultra grip plug	Orange & black	AHCL1430P		
				Economy series plug	Black & white	L1430P		
				 L14-30R	 L14-30P	Color coded ultra grip connector	Orange & black	AHCL1430C
		Economy series connector	Black & white			L1430C		
						Color coded single receptacle	Orange & black	AHCL1430R
						Single receptacle, isolated ground	Orange	IGL1430R
						Single receptacle, economy series	Black	L1430R
						Color coded flanged outlet	Orange & black	AHCL1430FO
						Color coded flanged inlet	Orange & black	AHCL1430FI
		250		 L15-30R	 L15-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1530P
Economy series plug	Black & White					L1530P		
				 L15-30R	 L15-30P	Color coded ultra grip connector, 3-phase	Blue & black	AHCL1530C
Economy series connector	Black & White					L1530C		
						Color coded single receptacle, 3-phase	Blue & black	AHCL1530R
						Single receptacle, isolated ground, 3-phase	Orange	IGL1530R
						Single receptacle, economy series,	Black	L1530R
						Color coded flanged outlet, 3-phase	Blue & black	AHCL1530FO
						Color coded flanged inlet, 3-phase	Blue & black	AHCL1530FI
480				 L16-30R	 L16-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1630P
		Color coded ultra grip connector, 3-phase	Red & black			AHCL1630C		
				 L16-30R	 L16-30P	Color coded single receptacle, 3-phase	Red & black	AHCL1630R
						Color coded flanged outlet, 3-phase	Red & black	AHCL1630FO
						Color coded flanged inlet, 3-phase	Red & black	AHCL1630FI
600		 L17-30R	 L17-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL1730P		
				Color coded ultra grip connector, 3-phase	Black & black	AHCL1730C		
				 L17-30R	 L17-30P	Color coded single receptacle, 3-phase	Black & black	AHCL1730R
						Color coded flanged outlet, 3-phase	Black & black	AHCL1730FO
						Color coded flanged inlet, 3-phase	Black & black	AHCL1730FI
4P-4W	120/208	 Receptacle	 Plug	Ultra grip plug, 3-phase	Black & white	AH3431N		
				Ultra grip connector, 3-phase	Black & white	AH3433N		
				 Receptacle	 Plug	Color coded single receptacle, 3-phase	Blue & black	AHCL3430R
						Flanged outlet, 3-phase	Black & white	AH3436N
						Flanged inlet, 3-phase	Black & white	AH3434N
				 L18-30R	 L18-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL1830P
						Color coded ultra grip connector, 3-phase	Blue & black	AHCL1830C
						Color coded single receptacle, 3-phase	Blue & black	AHCL1830R
						Color coded flanged outlet, 3-phase	Blue & black	AHCL1830FO
						Color coded flanged inlet, 3-phase	Blue & black	AHCL1830FI
277/480		 L19-30R	 L19-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL1930P		
				Color coded ultra grip connector, 3-phase	Red & black	AHCL1930C		
				 L19-30R	 L19-30P	Color coded single receptacle, 3-phase	Red & black	AHCL1930R
						Color coded flanged outlet, 3-phase	Red & black	AHCL1930FO
						Color coded flanged inlet, 3-phase	Red & black	AHCL1930FI
347/600		 L20-30R	 L20-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2030P		
				Color coded ultra grip connector, 3-phase	Black & black	AHCL2030C		
						Color coded flanged outlet, 3-phase	Black & black	AHCL2030R
						Color coded flanged outlet, 3-phase	Black & black	AHCL2030FO
						Color coded flanged inlet, 3-phase	Black & black	AHCL2030FI

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade straight blade plug & connector dimensions



AHCL2130P



AHCL2130C



AHCL2130R











AHCL2130FO



AHCL2130FI

30A Industrial grade locking devices

Pole-Wire	V/AC	NEMA	Description	Color	Catalog no.		
4P-5W	120/208	  L21-30R L21-30P	Color coded ultra grip plug, 3-phase	Blue & black	AHCL2130P		
			Ultra grip plug, 3-phase, flat cable	Black & white	AHL2130PF		
		Color coded ultra grip connector, 3-phase	Blue & black	AHCL2130C			
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2130CF			
		Color coded single receptacle, 3-phase	Blue & black	AHCL2130R			
		Single receptacle, isolated ground, 3-phase	Orange	IGL2130R			
		Color coded flanged outlet, 3-phase	Blue & black	AHCL2130FO			
		Color coded flanged inlet, 3-phase	Blue & black	AHCL2130FI			
		240/415		  L26-30R L26-30P	Ultra grip plug, 3-phase	Black & white	AHL2630P
					Ultra grip connector, 3-phase	Black & white	AHL2630C
Single receptacle, 3-phase	Black				AHL2630R		
Single receptacle, isolated ground, 3-phase	Orange				IG2630R		
277/480		  L22-30R L22-30P	Color coded ultra grip plug, 3-phase	Red & black	AHCL2230P		
			Ultra grip plug, 3-phase, flat cable	Black & white	AHL2230PF		
		Color coded ultra grip connector, 3-phase	Red & black	AHCL2230C			
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2230CF			
		Color coded single receptacle, 3-phase	Red & black	AHCL2230R			
		Single receptacle, isolated ground, 3-phase	Orange	IGL2230R			
		Color coded flanged outlet, 3-phase	Red & black	AHCL2230FO			
		Color coded flanged inlet, 3-phase	Red & black	AHCL2230FI			
		347/600		  L23-30R L23-30P	Color coded ultra grip plug, 3-phase	Black & black	AHCL2330P
					Ultra grip plug, 3-phase, flat cable	Black & white	AHL2330PF
Color coded ultra grip connector, 3-phase	Black & black				AHCL2330C		
Ultra grip connector, 3-phase, flat cable	Black & white				AHL2330CF		
Color coded single receptacle, 3-phase	Black & black				AHCL2330R		
Single receptacle, isolated ground, 3-phase	Orange				IGL2330R		
Color coded flanged outlet, 3-phase	Black & black				AHCL2330FO		
Color coded flanged inlet, 3-phase	Black & black				AHCL2330FI		

Accessories:
page 19

Dimensions & cord diameters:
pages 20-22

Spec information:
pages 23-27

Compliances:
pages 28-30

Compliances, specifications and availability are subject to change without notice.



BS1



BM2



BL1



WLRS1



7420



WP1

Accessories for industrial grade straight blade & locking devices

Amp	Electrical Characteristics					Boot		Receptacle Covers			FI/FO	Receptacle (1-Gang) 302/304 Stainless Steel Wallplates						
	NEMA	Pole-Wire	G/NG	Voltage	Phase	Plug	Conn.	Heavy-duty Single	Duplex	Standard Single	Cover	Standard Single	Duplex	Mid-size Single	Duplex	Oversized Single	Duplex	
10/15	NON	3P-3W	NG	277/480	—	BS1	BS2	WLRS1	—	7420	WP1	93091	—	93991	—	93891	—	
15	L1-15	2P-2W	NG	125	—	—	—	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	5-15	2P-3W	G	125	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	L5-15	2P-3W	G	125	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	6-15	2P-3W	G	250	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	L6-15	2P-3W	G	250	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	L7-15	2P-3W	G	277	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
20/10	NON	4P-5W	G	250/600	—	BL1	BL2	—	—	—	WP2	93111	—	PJ720*	—	—	—	
20	5-20	2P-3W	G	125	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	L5-20	2P-3W	G	125	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L2-20	2P-2W	NG	250	—	BS1	BS2	WLRS1	—	7420	WP1	93091	—	93991	—	93891	—	
	6-20	2P-3W	G	250	—	BS1	BS2	WLRS1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801	
	L6-20	2P-3W	G	250	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L11-20	3P-3W	NG	250	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L15-20	3P-4W	G	250	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L7-20	2P-3W	G	277	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L8-20	2P-3W	G	480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L12-20	3P-3W	NG	480	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L16-20	3P-4W	G	480	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L9-20	2P-3W	G	600	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L18-20	4P-4W	NG	120/208	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	NON	4P-4W	NG	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L21-20	4P-5W	G	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L10-20	3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	NON	3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L14-20	3P-4W	G	277/480	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L19-20	4P-4W	NG	277/480	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L22-20	4P-5W	G	277/480	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L20-20	4P-4W	NG	347/600	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	L23-20	4P-5W	G	347/600	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
	30	L5-30	2P-3W	G	125	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
		L6-30	2P-3W	G	250	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—
L11-30		3P-3W	NG	250	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L15-30		3P-4W	G	250	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L7-30		2P-3W	G	277	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L8-30		2P-3W	G	480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L12-30		3P-3W	NG	480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L16-30		3P-4W	G	480	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L9-30		2P-3W	G	600	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L13-30		3P-3W	NG	600	3	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L17-30		3P-4W	G	600	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L18-30		4P-4W	NG	120/208	3	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
NON		4P-4W	NG	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L21-30		4P-5W	G	120/208	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L10-30		3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
NON		3P-3W	NG	277/480	—	BM1	BM2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L14-30		3P-4W	G	277/480	—	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L19-30		4P-4W	NG	277/480	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L22-30		4P-5W	G	277/480	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L20-30		4P-4W	NG	347/600	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	
L23-30		4P-5W	G	347/600	3-Y	BL1	BL2	WLRS2	—	7420	WP2	93111	—	PJ720*	—	—	—	

Note: *Polycarbonate only (B, GY, V, W)

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade straight blade plug & connector dimensions

Table 1. Ultra grip plugs & connectors

Family	A	B	C	D	Cord Diameter
Ultra grip plug	1.38" (35.1mm)	2.07" (52.6mm)	1.69" (42.9mm)	1.55" (39.4mm)	0.25 - 0.66" (6.4-16.8mm)
Ultra grip connector	1.38" (35.1mm)	2.89" (73.4mm)	1.69" (42.9mm)	1.55" (39.4mm)	0.25 - 0.66" (6.4-16.8mm)




Table 2. Safety grip plugs & connectors

Family	A	B	C	D	Cord Diameter
Safety grip plug, hospital grade	1.40" (35.6mm)	2.11" (53.6mm)	1.53" (38.9mm)	1.45" (36.8mm)	0.30-0.65" (7.6-16.6mm)
Safety grip plug, angled, hospital grade	1.39" (35.3mm)	1.29" (32.8mm)	1.52" (38.6mm)	2.09" (53.1mm)	0.30-0.65" (7.6-16.6mm)
Safety grip plug, angled	1.38" (35.1mm)	1.30" (33.0mm)	1.51" (38.4mm)	2.07" (52.6mm)	0.30-0.65" (7.6-16.6mm)
Safety grip connector, hospital grade	1.38" (35.1mm)	2.98" (75.7mm)	1.52" (38.6mm)	0.87" (22.1mm)	0.30-0.65" (7.6-16.6mm)




Table 3. Quick and Auto grip plugs & connectors

Family	A	B	C	D	Cord Diameter
Quick grip plug	1.40" (35.6mm)	1.96" (50.0mm)	1.67" (42.4mm)	1.46" (37.1mm)	0.23-0.65" (5.8-16.5mm)
Quick grip connector	1.40" (35.6mm)	2.59" (65.8mm)	1.67" (42.4mm)	1.46" (37.1mm)	0.23-0.65" (5.8-16.5mm)
Auto grip plug	1.37" (34.8mm)	1.83" (46.5mm)	1.51" (38.4mm)		0.33-0.66" (8.3-16.7mm)
Auto grip connector	1.37" (34.8mm)	1.83" (46.5mm)	1.51" (38.4mm)		0.33-0.66" (8.3-16.7mm)





Table 4. Flanged inlets & outlets

Family	A	B	C	D	E	F
Flanged outlet, nylon	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
Flanged inlet, nylon	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
Flanged outlet, metal	1.40" (35.6mm)	1.11" (28.2mm)	1.44" (35.6mm)	2.47" (62.7mm)	0.20" (5.1mm)	2.04" (52.6mm)
Flanged inlet, metal	1.57" (39.9mm)	1.36" (34.5mm)	1.64" (38.9mm)	2.48" (63.0mm)	0.286" (7.3mm)	2.01" (51.1mm)



Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking device dimensions

Table 5. Ultra grip locking plugs & connectors

Family	A	B	C	D	Cord Diameter
Ultra grip plug, 2P-3W, 3P-3W	1.78" (45.2mm)	2.59" (65.8mm)	2.23" (56.6mm)	2.10" (53.3mm)	0.38-1.00" (9.6 - 25.4mm)
Ultra grip plug, 3P-4W, 4P-4W, 4P-5W	2.18" (55.4mm)	2.82" (71.6mm)	2.46" (62.5mm)	2.30" (58.4mm)	0.38-1.16" (9.6 - 29.5mm)
Ultra grip connector, 2P-3W, 3P-3W	1.78" (45.2mm)	3.61" (91.7mm)	2.23" (56.6mm)	2.10" (53.3mm)	0.38-1.00" (9.6 - 25.4mm)
Ultra grip connector, 3P-4W, 4P-4W, 4P-5W	1.97" (50.0mm)	3.84" (97.5mm)	2.46" (62.5mm)	2.30" (58.4mm)	0.38-1.16" (9.6 - 29.5mm)




Table 6. Safety grip locking plugs & connectors

Family	A	B	C	D	Cord Diameter
Safety grip plug, NEMA L2-20	1.37" (34.8mm)	1.50" (38.1mm)	2.06" (52.3mm)	–	0.33-0.66" (8.4-16.7mm)
Safety grip plug, 15A & 10/15A locking	1.37" (34.8mm)	1.50" (38.1mm)	2.06" (52.3mm)	–	0.33-0.66" (8.4-16.7mm)
Safety grip plug, 15A locking angled	1.28" (32.5mm)	1.47" (37.3mm)	1.50" (38.1mm)	2.06" (52.3mm)	0.33-0.66" (8.4-16.7mm)
Safety grip connector, NEMA L2-20	1.37" (34.8mm)	2.88" (73.0mm)	1.50" (38.1mm)	1.00" (25.4mm)	0.33-0.66" (8.4-16.7mm)
Safety grip connector, 15A & 10/15A locking	1.37" (34.8mm)	2.88" (73.0mm)	1.50" (38.1mm)	1.00" (25.4mm)	0.33-0.66" (8.4-16.7mm)




Table 7. Auto and Economy grip locking plugs & connectors

Family	A	B	C	Cord Diameter
Auto grip plug, 15A & 10/15A locking	1.38" (34.9mm)	1.83" (46.5mm)	1.52" (38.6mm)	0.33-0.66" (8.4-16.7mm)
Auto grip connector, 15A & 10/15A locking	1.38" (34.9mm)	1.83" (46.5mm)	1.52" (38.6mm)	0.33-0.66" (8.4-16.7mm)
Economy grip plug, 20A & 30A locking	1.66" (42.2mm)	2.23" (56.6mm)	1.82" (46.23mm)	0.33-0.66" (8.4-16.7mm)
Economy grip connector, 20A & 30A locking	1.65" (41.9mm)	3.13" (79.5mm)	1.82" (46.23mm)	0.33-0.66" (8.4-16.7mm)





Table 8. Standard industrial locking plugs & connectors

Family	A	B	C	Cord Diameter
Standard industrial plug, NEMA L9-20, L9-30	1.83" (47.5mm)	2.13" (54.1mm)	2.85" (72.3mm)	0.30-0.95" (7.6-16.7mm)
Standard industrial plug, NEMA L12-20, L12-30, L13-30	1.83" (47.5mm)	2.13" (54.1mm)	2.85" (72.3mm)	0.38-1.00" (9.5-25.4mm)
Standard industrial connector, NEMA L9-20, L9-30	1.83" (47.5mm)	3.44" (87.3mm)	2.12" (53.8mm)	0.30-0.95" (7.6-16.7mm)
Standard industrial connector, NEMA L12-20, L12-30, L13-30	1.83" (47.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	0.38-1.00" (9.5-25.4mm)



Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking device dimensions

Table 9. Locking receptacles

Family	A	B	C	D	E
Single receptacle, 15A & 10/15A locking	1.40" (35.6mm)	1.53" (38.9mm)	1.72" (43.7mm)	0.82" (20.8mm)	3.22" (81.8mm)
Single receptacle, 20/10A locking	1.37" (34.8mm)	1.37" (34.8mm)	2.02" (51.3mm)	1.12" (28.4mm)	3.21" (81.5mm)
Economy series receptacles, 20A & 30A locking, 2-P, 3-W; 3-P, 3-W; 3P-4W	1.70" (43.2mm)	2.39" (60.7mm)	1.15" (29.2mm)	3.28" (83.3mm)	1.55" (39.4mm)
Single receptacle, 20A locking 2-P, 3-W & 3-P, 3-W	1.56" (39.6mm)	1.56" (39.6mm)	2.64" (67.1mm)	1.06" (26.9mm)	3.22" (81.8mm)
Single receptacle, 30A locking 2-P, 3-W & 3-P, 3-W	1.56" (39.6mm)	1.61" (40.9mm)	2.64" (67.1mm)	1.09" (27.7mm)	3.21" (83.6mm)
Single receptacle, 20A locking 3-P, 4-W; 4-P, 4-W & 4-P, 5-W	1.56" (39.6mm)	1.56" (39.6mm)	2.64" (67.1mm)	1.06" (26.9mm)	3.22" (81.8mm)
Single receptacle, 30A locking 3-P, 4-W; 4-P, 4-W & 4-P, 5-W	1.56" (39.6mm)	1.61" (40.9mm)	2.64" (67.1mm)	1.09" (27.7mm)	3.21" (83.6mm)
Duplex receptacle, 15A & 10/15A locking	1.11" (28.2mm)	1.59" (40.4mm)	0.82" (20.8mm)	3.29" (83.6mm)	4.05" (102.9mm)







Table 10. Locking flanged inlets

Family	A	B	C	D
15A locking	2.56" (65.0mm)	1.56" (39.6mm)	1.71" (43.4mm)	1.92" (48.8mm)
20A locking 2-P, 3-W & 3-P, 3-W	2.87" (72.9mm)	1.94" (49.3mm)	2.06" (52.3mm)	2.19" (55.6mm)
20A locking 3-P, 4-W; 4-P, 4-W; 4-P, 5-W	3.06" (77.7mm)	2.03" (51.6mm)	2.19" (55.6mm)	2.19" (55.6mm)
20A locking NEMA L9-20, L12-20	2.87" (72.9mm)	1.94" (49.3mm)	2.06" (52.3mm)	2.09" (53.1mm)
30A locking 2-P, 3-W & 3-P, 3-W	2.87" (72.9mm)	1.94" (49.3mm)	2.06" (52.3mm)	2.19" (55.6mm)
30A locking 3-P, 4-W; 4-P, 4-W; 4-P, 5-W	3.06" (77.7mm)	2.03" (51.6mm)	2.19" (55.6mm)	2.19" (55.6mm)
30A locking NEMA L9-30, L12-30, L13-30	2.87" (72.9mm)	1.94" (49.3mm)	2.02" (51.3mm)	2.02" (51.3mm)











Table 11. Locking flanged outlets

Family	A	B	C	D
15A locking	2.56" (65.0mm)	1.14" (29.0mm)	1.71" (43.4mm)	0.92" (23.4mm)
20A locking 2-P, 3-W & 3-P, 3-W	2.87" (72.9mm)	2.03" (51.6mm)	2.06" (52.3mm)	2.24" (56.9mm)
20A locking 3-P, 4-W; 4-P, 4-W; 4-P, 5-W	3.06" (77.7mm)	2.03" (51.6mm)	2.19" (55.6mm)	2.24" (56.9mm)
20A locking NEMA L9-20, L12-20	2.87" (72.9mm)	1.94" (49.3mm)	2.06" (52.3mm)	1.95" (49.5mm)
30A locking 2-P, 3-W & 3-P, 3-W	2.87" (72.9mm)	1.94" (49.3mm)	2.06" (52.3mm)	2.24" (56.9mm)
30A locking 3-P, 4-W; 4-P, 4-W; 4-P, 5-W	3.06" (77.7mm)	2.03" (51.6mm)	2.19" (55.6mm)	2.24" (56.9mm)
30A locking NEMA L9-30, L12-30, L13-30	2.87" (72.9mm)	1.94" (49.3mm)	2.12" (53.8mm)	2.02" (51.3mm)



Compliances, specifications and availability are subject to change without notice.

Arrow Hart hospital & industrial grade straight blade devices specification & performance data

15 & 20A Hospital grade plugs & connectors NEMA 5-15, 6-15, 5-20, 6-20		15 & 20A Hospital grade quick grip plugs & connectors NEMA 5-15	
Wiring type	Back wire	Back wire	
Testing & code compliance	<ul style="list-style-type: none"> cULus listed to 498, file no. E15058; file no. E15012 (hospital grade) UL verified to Fed Spec WC-596G 	<ul style="list-style-type: none"> Listed to UL498, file no. E15012 UL verified to Fed Spec WC-596G 	
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	
Mechanical specifications	Terminal accommodation: #18 - #12 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #18 - #12 AWG Voltage ratings: Permanently marked on device	
Material specifications	Plug/connector outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.060" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: EPDM	Plug/connector outer shell: Nylon Interior body: N/A Terminal retainer: Polycarbonate Blades: 0.060" thick brass Line contacts: 0.030" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: N/A	
15 & 20A Industrial grade plugs & connectors NEMA 5-15, 6-15, 5-20, 6-20		15 & 20A Industrial grade quick grip plugs & connectors NEMA 5-15, 6-15, 5-20, 6-20	
Wiring type	Back wire	Back wire	
Testing & code compliance	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E3663 Complies with Fed Spec WC-596F CSA certified to C22.2, no. 42-99 file no. 7087 (6221-02) 7251N: NOM certified 	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E15012 UL verified to Fed Spec WC-596G 	
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	
Mechanical specifications	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #18 - #12 AWG Voltage ratings: Permanently marked on device	
Material specifications	Plug/connector outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground contact: 0.041" thick brass Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: EPDM	Plug/connector outer shell: Nylon Interior body: N/A Terminal retainer: Polycarbonate Blades: 0.060" thick brass Line contacts: 0.030" thick brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated (hot) and zinc plated (neutral screw) Ground contact: Brass Ground screw: #8-32 steel, zinc plated (green) Assembly/mounting screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel Gasket/dust shield: N/A	

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade straight blade & locking devices specification & performance data

	15 & 20A Industrial grade flanged inlets NEMA 5-15, 6-15, 5-20, 6-20	15 & 20A Industrial grade flanged outlets NEMA 5-15, 6-15, 5-20, 6-20
Wiring type	Side wire	Side wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E3663 cUL Listed to CSA C22.2, no. 42-M1999 5278C, 5678C: also NOM certified 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 CSA certified to C22.2, no. 42-99 & 182.3-M1987 file no. 7087 (6233-01)
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) at maximum rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 AWG Voltage ratings: Permanently marked on device
Material specifications	Plug/connector outer shell: Nylon (except 5278 steel) Interior body: Lexan (except 5278 urea) Terminal retainer: Lexan (except 5278 urea) Blades: 0.062" thick brass Line contacts: N/A Terminal clamps: Steel Terminal screws: #8-32 steel, brass plated (hot) or nickel plated (neutral) (except 5278 #8-32 brass) Ground screw: #8-32 steel, zinc plated (green) (except 5278 #8-32 brass) Assembly screws/rivets: Steel screws (except 5278 steel rivets, zinc plated)	Plug/connector outer shell: Nylon (except 5246 steel) Interior body: Lexan (except 5246 nylon) Terminal retainer: Lexan (except 5246 nylon) Blades: N/A Line contacts: 0.031" thick brass Terminal clamps: Brass Terminal screws: #8-32 steel, brass plated (hot) or nickel plated (neutral) (except 5246, brass) Ground screw: #8-32 brass, zinc plated (green) Assembly screws/rivets: Steel screws (except 5246C steel rivets)

	15A Plugs & connectors NEMA L5-15, L6-15, L7-15	15A Plugs & connectors Non-NEMA 10/15A	15 & 20A Plugs & connectors NEMA L1-15, L2-20
Wiring Type	Back wire	Back wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E3663 UL verified to Fed Spec WC-596F cUL Listed to CSA C22.2, no. 42 file no. E3663 	<ul style="list-style-type: none"> UL recognized component for US & Canada, file no. E366 	<ul style="list-style-type: none"> Listed to UL498, file no. E3663 cUL Listed to C22.2, no. 42 file no. E3663 L2-20 cUL Listed to C22.2, no. 42, file no. E3663 L2-20 NOM certified
Environmental Specifications	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)
Electrical Specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload at 200% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)
Mechanical Specifications	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #16 - #12 AWG Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated, nickel plated (neutral screw) Ground screw: #8-32 brass plated (green) Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: EPDM	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass, tin plated Terminal clamps: Steel, zinc plated Terminal screws: #8-32 steel, brass plated, nickel plated (neutral screw) Ground screw: #8-32 brass plated (green) Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: Neoprene	Outer shell: Nylon Interior body: Nylon Terminal retainer: Nylon Blades: Brass Line contacts: Brass (except L2-20 tin plated) Terminal clamps: Steel, zinc plated Terminal screws: Brass Ground screw: Brass Assembly screws: Steel, nickel plated (except L1-15 steel) Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: Neoprene

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices specification & performance data

	20 & 30A Ultra grip plugs & connectors NEMA L5-20, L6-20, L11-20, L15-20, L7-20, L8-20, L16-20, L18-20, L21-20, L10-20, L14-20, L19-20, L22-20, L20-20, L23-20, L5-30, L6-30, L11-30, L15-30, L7-30, L8-30, L16-30, L17-30, L18-30, L21-30, L10-30, L14-30, L19-30, L22-30, L20-30, L23-30, L25-30 Non-NEMA 30A	20 & 30A Auto grip plugs & connectors NEMA L12-20, L9-20, L12-30, L9-30, L13-30, L26-30	20A Safety grip plugs & connectors NEMA L24-20, Non-NEMA 20A
Wiring type	Back wire	Back wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> cULus Listed to UL498, file no. E3663, except L10-30: UL Listed; L2120_F & L2130_F series not listed L8-30 cUL Listed to C22.2, no. 42, file no. E3663 NOM certified, except L8-30, L10-30, L22-30, L2120_F series 	<ul style="list-style-type: none"> cULus Listed to UL498 and C22.2, no. 42-10, UL file E15012 Fed Spec WC-596H for 25-30 and 26-30 	<ul style="list-style-type: none"> cULus Listed to UL498 and C22.2, no. 42-10, UL file E15012 Fed Spec WC-596H for 25-30 and 26-30
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F) Except flat cable: -40°C to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 60°C (-40°F to 140°F) Except L24-20: -40°C to 75°C (-40°F to 167°F)
Electrical specifications	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)	Dielectric voltage: Twice the device rating + 1000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #18 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #16 - #8 AWG (except L24-20 #18 - #8) Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass, tin plated Terminal clamps: Steel, tin plated Terminal screws: #10-32 brass, zinc plated (neutral screw) Ground screw: #10-32 brass Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: EPDM	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass Terminal clamps: Steel Terminal screws: #10-32 brass, zinc plated (neutral screw) Ground screw: #10-32 brass Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, zinc plated Gasket/dust shield: EPDM	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: Brass Line contacts: Brass Terminal clamps: Steel Terminal screws: #8-32 brass zinc plated (neutral screw), (except L24-20 brass) Ground screw: #8-32 brass plated (green) Assembly screws: Steel, nickel plated Cord clamp: Nylon Cord clamp screws: Steel, nickel plated Gasket/dust shield: Neoprene

	15A Single & duplex receptacles NEMA L5-15, L6-15, L7-15, Non-NEMA 15/10A	15A Single & duplex receptacles NEMA L1-15	15A Isolated ground receptacles NEMA L5-15, L6-15	20A Single receptacle NEMA L2-20, L24-20
Wiring type	Back & side wire	Back & side wire	Back & side wire	Back & side wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. 2369 UL verified to Fed Spec WC-596G, except CWL515R Non NEMA: UL recognized component, file no. E2369 CSA certified to C22.2, no. 42 	<ul style="list-style-type: none"> UL recognized component, file no. E2369 	<ul style="list-style-type: none"> Listed to UL498, file no. 2369 CSA certified to C22.2, no. 42, except IGL615R 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369
Environmental specifications	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 115°C (-40°F to 239°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 115°C (-40°F to 239°F)	Flammability: Meets UL94 requirements; V0 rated, (except L24-20; V2 rated) Temperature rating: -40°C to 105°C (-40°F to 221°F), (except L24-20, -40°C to 115°C (-40°F to 239°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC), (except Non-NEMA 15/10A, Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device
Material specifications	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick pre-plated steel Auto ground clip: N/A Line contacts: 0.036" thick brass Terminal screws: #8-32 brass screws, nickel plated Ground screw: #8-32 brass screw (green) Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick pre-plated steel Auto ground clip: Yes Line contacts: 0.036" thick brass Terminal screws: #8-32 brass Ground screw: N/A Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick pre-plated steel Auto ground clip: Yes Line contacts: 0.036" thick brass Terminal screws: #8-32 brass screws, nickel plated Ground screw: #8-32 brass screw (green) Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated (except L24-20, brass) Auto ground clip: Yes Line contacts: 0.036" thick brass, bronze (except L24-20, brass) Terminal screws: #8-32 brass, tin plated (except L24-20, brass) Ground screw: N/A (except L24-20, brass) Mounting screws: Steel, zinc plated

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices specification & performance data

	20A Single receptacles NEMA L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, Non-NEMA 20A	30A Single receptacles NEMA L5-30, L6-30, L7-30, L8-30, L9-30, L10-30, L11-30, L12-30, L13-30, L14-30, L15-30, L16-30, L17-30, L18-30, L19-30, L20-30, L21-30, L22-30, L23-30, L25-30, L26-30 Non-NEMA 30A	20 & 30A Isolated ground single receptacles NEMA L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, L25-30, L26-30
Wiring type	Back & side wire	Back & side wire	Back & side wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 NEMA L5-20, L6-20, L7-20, L10-20, L14-20, L15-20, L18-20 & L21-20 also UL verified to Fed Spec WC-596G CSA certified to C22.2, no.42 except 7310B, NEMA L11-20, L12-20, 7410B, L18-20, L19-20, L20-20 NEMA L11-20, L14-20, L15-20, L18-20, L21-20, L22-20 also NOM certified 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 NEMA L5-30, L6-30, L7-30, L14-30, L15-30, L20-30, L21-30, L23-30 also UL verified to Fed Spec WC-596G CSA certified to C22.2, no. 42 except NEMA L11-20, L12-20, AH3330-2, L10-30, L11-30, L12-30, L13-30, AH3430, L18-30, L19-30, L20-30 NEMA L5-30, L10-30, L11-30, L14-30, L15-30, L18-30 also NOM certified 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 CSA certified to C22.2, no. 42 except NEMA L5-30 NOM certified, except for L7-20, L8-20, L6-30, L7-30, L8-30, L16-20, L21-30, L22-30, L23-30
Environmental specifications	Flammability: Meets UL94 requirements; V0 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: w/o impact -40°C to 70°C (-40°F to 158°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device
Material specifications	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated Line contacts: 0.041" thick brass Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Terminal Clamps/Plates: 0.041" thick brass Ground Contacts: 0.041" thick brass Back Plate: 0.041" thick brass, nickel plated Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated Line contacts: 0.041" thick brass Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Terminal Clamps/Plates: 0.041" thick brass Ground Contacts: 0.041" thick brass Back Plate: 0.041" thick brass, nickel plated Mounting screws: Steel, zinc plated	Face: Glass-filled nylon Base: Glass-filled nylon Mounting strap: 0.050" thick steel, zinc plated Line contacts: 0.041" thick brass Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Terminal Clamps/Plates: 0.041" thick brass Ground Contacts: 0.041" thick brass Back Plate: 0.041" thick brass, nickel plated Mounting screws: Steel, zinc plated

	15A Flanged inlets & outlets NEMA L5-15, L6-15, L7-15	15 & 20A Flanged inlets & outlets NEMA L1-15, L2-20	20 & 30A Flanged inlets & outlets NEMA L5-20, L6-20, L8-30, L11-20, L14-30, L14-30, L21-30, L21-30
Wiring type	Back wire	Side wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 CWL615FI, CWL715FI also cUL listed to UL498, file no. E3663 CWL615FI also UL verified to Fed Spec WC-596/102-1 CSA certified to C22.2, no.42 except CWL515FO 	<ul style="list-style-type: none"> Listed to UL498, file no. E2369 	<ul style="list-style-type: none"> AHL520FI, AHL520FO, AHL1430FI, AHL2130FI listed to UL498, file no. E2369; AHL1430FI, AHL2130FI is file no. E3663 AHL620FI, AHL830FI, AHL1120FO cUL Listed to UL498, file no. E3663 AHL520FO, AHL1430FI, AHL2130FI, AHL2130FO also CSA certified to C22.2, no. 42 AHL830FI, AHL1120FO, AHL1430FO CSA certified to C22.2, no. 42 AHL1430FI, AHL1430FO, AHL2130FI, AHL2130FO NOM certified
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: -40°C to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V0 rated Temperature rating: -40°C to 105°C (-40°F to 221°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets; max. 30°C (86°F) @ maximum rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets; max. 30°C (86°F) @ maximum rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets; max. 30°C (86°F) @ maximum rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG (L2-20) #14 - #10 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #8-32 brass Ground screw: #8-32 brass (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Plated brass Interior body: GF Nylon (L1-15FI, Phenolic) Terminal retainer: N/A Blades: 0.062" thick brass Line contacts: 0.031" thick brass (L1-15, 0.032" thick bronze) Terminal clamps: N/A Terminal screws: #6-32 brass Ground screw: #8-32 brass (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated

Compliances, specifications and availability are subject to change without notice.

Arrow Hart industrial grade locking devices specification & performance data

20 & 30A Flanged inlets
NEMA L7-20, L8-20, L5-30, L6-30, L7-30, L10-20, L11-20, L10-30, L11-30, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, L21-20, L22-20, L23-20, L22-30, L23-30, Non-NEMA
20 & 30A, Non-NEMA 20/10A







20 & 30A Flanged outlets
NEMA L8-20, L6-30, L7-30, L8-30, L10-20, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L21-20, L22-20, L23-20, L22-30, L23-30

20 & 30A Flanged outlets
NEMA L6-20, L7-20, L5-30, L10-30, L11-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, Non-NEMA
20 & 30A, Non-NEMA 20/10A


Wiring type	Back wire	Back wire	Back wire
Testing & code compliance	<ul style="list-style-type: none"> Listed to UL498 file no. E3663 cUL Listed to UL498, file no. E3663 	<ul style="list-style-type: none"> Listed to UL498 file no. E2369 CSA certified to C22.2, no. 42 	<ul style="list-style-type: none"> Listed to UL498 file no. E2369 CSA certified to C22.2, no. 42
Environmental specifications	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)	Flammability: Meets UL94 requirements; V2 rated Temperature rating: w/o impact -40°C to 60°C (-40°F to 140°F)
Electrical specifications	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) @ maximum rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	Dielectric voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current interrupting: Yes, at full-rated current Temperature rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical specifications	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device	Terminal accommodation: #14 - #8 AWG Voltage ratings: Permanently marked on device
Material specifications	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: 0.062" thick brass Line contacts: N/A Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass plated (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: N/A Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass plated (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated	Outer shell: Nylon Interior body: Nylon Terminal retainer: Polycarbonate Blades: N/A Line contacts: 0.031" thick brass Terminal clamps: Steel Terminal screws: #10-32 brass, nickel plated (neutral screw) Ground screw: #10-32 brass plated (green) Assembly screws: Steel, zinc plated Mounting screws: Steel, zinc plated

Arrow Hart straight blade & locking devices certifications & compliances

Straight blade devices

Catalog no.	 cULus	 UL	 CSA	 Fed Spec	 NOM	 USMCA
AH5246	•					
AH5266		•	•	•	•	•
AH5266A		•	•	•	•	•
AH5266BK		•	•	•	•	•
AH5269		•	•		•	•
AH5269BK		•	•		•	•
AH5278	•					
AH5278C	•					
AH5279C		•			•	•
AH5364BK	•			•	•	
AH5364Y	•			•	•	
AH5366		•	•	•	•	
AH5369		•	•		•	
AH5369BK		•	•		•	
AH5369Y		•	•		•	
AH5464BK	•			•	•	
AH5464Y	•			•	•	
AH5466		•	•	•	•	•
AH5469		•	•		•	•
AH5469BK		•	•		•	
AH5469Y		•	•		•	
AH5666	•			•	•	•
AH5666BK	•			•	•	
AH5666Y	•			•	•	
AH5669	•			•	•	•
AH5669BK	•			•	•	
AH5669Y	•			•	•	
AH5678C	•			•	•	•
AH5679C		•			•	•
AH5778C	•			•	•	
AH5779C		•			•	•
AH5878C	•			•	•	
AH5879C		•			•	•
AH5965BK	•			•		
AH5965Y	•			•		
AH5969BK	•			•		
AH5969Y	•			•		
AH8115W	•			•		
AH8119W	•			•		
AH8215HG	•			•	•	
AH8215HGA	•			•	•	
AH8215HGAC	•			•	•	
AH8215HGC	•			•	•	
AH8219HG	•			•	•	
AH8219HGC	•			•	•	
AH8225HGA	•			•		
AH8225HGAC	•			•		
AH8315HG	•			•	•	•
AH8315HGA	•			•	•	•
AH8315HGAC	•			•	•	•
AH8319HG	•			•	•	•
AH8325HG	•			•		
AH8325HGAC	•			•		

KEY:  cULus  UL  CSA

 Fed Spec









 RU

 cRUus

 NOM

 USMCA









Locking devices


Catalog no.	 cULus	 UL	 CSA	 Fed Spec	 RU	 cRUus	 NOM	 USMCA
4700		•	•	•				
4750		•	•	•				•
4755						•		•
4767						•		•
4767AN						•		•
5792		•	•					•
6580		•	•	•				
7310B		•						
7314C	•							•
7327N	•							•
7328N		•						
7408N	•							
7409N		•						
7410B		•						
7411C	•						•	•
7413C	•							•
7506	•							
7540		•						
7546	•							
7548	•							
7580					•			•
7582					•			•
9965C	•							•
AHCL3330R		•						•
AH3331N	•							•
AH3333N	•							•
AH3336N		•						•
AH3337N	•							•
AHCL3430R		•						•
AH3431N	•							•
AH3433N	•							•
AH3434N	•							•
AH3436N	•							•
AH3521BK	•							•
AH3523BK	•							•
AH3524BK	•							•
AH3525BK		•						•
AHCL1020C	•						•	•
AHCL1020FI	•						•	•
AHCL1020FO	•						•	•
AHCL1020P	•						•	•
AHCL1020R		•		•			•	•
AHCL1030C	•						•	•
AHCL1030FI	•						•	•
AHCL1030FO	•						•	•
AHCL1030P	•						•	•
AHCL1030R		•					•	•
AHCL1120C	•						•	•
AHCL1120FI	•						•	•
AHCL1120FO	•						•	•
AHCL1120P	•						•	•
AHCL1120R		•					•	•
AHCL1130C	•						•	•

Compliances, specifications and availability are subject to change without notice.

Arrow Hart locking devices certifications & compliances









Locking devices

Catalog no.								
AHCL1130FI	•						•	•
AHCL1130FO	•						•	
AHCL1130P	•						•	
AHCL1130R		•					•	•
AHCL1420C	•						•	•
AHCL1420FI	•						•	•
AHL1420FIBK	•							•
AHCL1420FO	•						•	•
AHL1420FOBK		•	•					
AHCL1420P	•						•	•
AHCL1420R		•	•	•			•	•
AHCL1430C	•						•	•
AHCL1430FI	•						•	•
AHCL1430FO	•						•	•
AHCL1430P	•						•	•
AHCL1430R		•	•	•			•	•
AHCL1520C	•						•	•
AHL1520CBK	•							•
AHCL1520FI	•						•	•
AHCL1520FO	•						•	•
AHCL1520P	•						•	•
AHCL1520PBK	•							•
AHCL1520R		•	•	•			•	•
AHCL1530C	•						•	•
AHCL1530FI	•						•	•
AHCL1530FO	•						•	•
AHCL1530P	•						•	•
AHCL1530R		•	•	•			•	•
AHCL1620C	•						•	•
AHCL1620FI	•						•	•
AHCL1620FO	•						•	•
AHCL1620P	•						•	•
AHCL1620R		•	•				•	•
AHCL1630C	•						•	•
AHCL1630FI	•						•	•
AHCL1630FO	•						•	•
AHCL1630P	•						•	•
AHCL1630R		•	•				•	•
AHCL1730C	•						•	•
AHCL1730FI	•						•	•
AHCL1730FO	•						•	•
AHCL1730P	•						•	•
AHCL1730R		•	•				•	•
AHCL1820C	•						•	•
AHCL1820FI	•						•	
AHCL1820FO	•						•	
AHCL1820P	•						•	•
AHCL1820R		•		•			•	•
AHCL1830C	•						•	•
AHCL1830P	•						•	•
AHCL1830R		•					•	•
AHCL1920C	•						•	•
AHCL1920FI	•						•	•

KEY:  cULus  UL  CSA  Fed Spec  RU  cRUus  NOM  USMCA

Compliances, specifications and availability are subject to change without notice.

Locking devices

Catalog no.								
AHCL1920FO		•						•
AHCL1920P	•							•
AHCL1920R		•						•
AHCL2020C	•							•
AHCL2020FI	•							•
AHCL2020FO	•							•
AHCL2020P	•							•
AHCL2020R		•						•
AHCL2120C	•							•
AHL2120CBK	•							•
AHL2120CF								•
AHCL2120FI	•							•
AHCL2120FO	•							•
AHCL2120P	•							•
AHL2120PBK	•							•
AHL2120PF								•
AHCL2120R		•	•	•				•
AHCL2130C	•							•
AHL2130CF								•
AHCL2130FI	•							•
AHCL2130FO	•							•
AHCL2130P	•							•
AHL2130PF								•
AHCL2130R		•		•				•
AHCL2220C	•							•
AHCL2220FI	•							•
AHCL2220FO	•							•
AHCL2220P	•							•
AHCL2220R		•	•					•
AHCL2320C	•							•
AHCL2320FI	•							•
AHCL2320FO	•							•
AHCL2320P	•							•
AHCL2320R		•	•					•
AHL2530P	•					•		
AHL2530C	•					•		
AHL2530R	•					•		
AHL2630P	•					•		
AHL2630C	•					•		
AHL2630R	•					•		
AHCL520C	•							•
AHCL520FI	•							•
AHCL520FO	•							•
AHCL520P	•							•
AHCL520R		•	•	•				•
AHCL530C	•							•
AHCL530P	•							•
AHCL530R		•	•	•				•
AHCL620C	•							•
AHCL620FI	•							•
AHCL620FO	•							•
AHCL620P	•							•
AHCL620R		•	•	•				•

Arrow Hart locking devices certifications & compliances

Locking devices

Catalog no.	cULus	UL	CSA	FCS	RU	cRUus	NOM	USMCA
AHCL630C	•							•
AHCL630FI	•							•
AHCL630FO	•							•
AHCL630P	•							•
AHCL630R		•	•	•				•
AHCL720C	•							•
AHCL720FI	•							•
AHCL720FO	•							•
AHCL720P	•							•
AHCL720R		•	•	•				•
AHCL730C	•							•
AHCL730FI	•							•
AHCL730FO	•							•
AHCL730P	•							•
AHCL730R		•	•	•				•
AHCL820C	•							•
AHCL820FI	•							•
AHCL820FO	•							•
AHCL820P	•							•
AHCL820R		•	•					•
AHCL830C	•							•
AHCL830FI	•							•
AHCL830FO	•							•
AHCL830P	•							•
AHCL830R		•	•					•
CWL115FI	•							•
CWL115FO	•							•
CWL115R		•						•
CWL1220C	•							•
CWL1220FI	•							•
CWL1220FO	•							•
CWL1220P	•							•
CWL1220R		•						•
CWL1230C		•	•					•
CWL1230FI		•	•					•
CWL1230FO	•	•						•
CWL1230P		•	•					•
CWL1230R		•						•
CWL1330C		•	•					•
CWL1330FI		•	•					•
CWL1330FO	•							•
CWL1330P		•	•					•
CWL1330R		•						•
CWL1830FI	•							•
CWL1830FO	•							•
CWL220C	•							•
CWL220FO	•							•
CWL220P	•							•
CWL220R		•						•
CWL515FI	•							•
CWL515FO	•							•
CWL515R		•	•	•				•
CWL530FI	•							•










Locking devices

Catalog no.	cULus	UL	CSA	FCS	RU	cRUus	NOM	USMCA
CWL530FO	•							•
CWL615C	•			•				•
CWL615FI	•			•				•
CWL615FO	•			•				•
CWL615P	•			•				•
CWL615R		•	•	•				•
CWL715C	•			•				•
CWL715FI	•			•				•
CWL715FO	•			•				•
CWL715P	•			•				•
CWL715R		•	•	•				•
CWL920C		•	•					•
CWL920FI		•	•					•
CWL920FO	•							•
CWL920P		•	•					•
CWL920R		•	•					•
CWL930C	•							•
CWL930FI	•							•
CWL930FO	•							•
CWL930P	•							•
CWL930R		•	•					•
IGL4700		•	•					•
IGL515R		•	•					•
IGL520R		•	•					•
IGL530P	•							•
IGL530R		•	•					•
IGL615R		•	•	•				•
IGL620R		•	•	•				•
IGL630R		•	•					•
IGL720R		•	•	•				•
IGL730R		•	•					•
IGL820R		•	•					•
IGL830R		•	•					•
IGL1420R		•	•					•
IGL1430R		•	•					•
IGL1520R		•	•	•				•
IGL1530R		•	•					•
IGL1620R		•	•					•
IGL2120R		•	•					•
IGL2130R		•	•					•
IGL2530R	•			•				•
IGL2630R	•			•				•
L2420P	•							•
L2420R				•				•

KEY: cULus UL CSA Fed Spec RU cRUus NOM USMCA























Compliances, specifications and availability are subject to change without notice.

Arrow Hart quick reference guide

Pole-Wire	Amp.	V/AC	NEMA		Page	Grip style	Plug	Connector	Single Receptacle	Duplex Receptacle	Flanged Inlet	Flanged Outlet	
2P-2W	15	125	L1-15		11	Standard industrial	7546 7548	7506	CWL115R	7540	CWL115FI	CWL115FO	
						Economy	L115P						
	20	125	L2-20		12	Safety	CWL220P CWL220P-6	CWL220C	CWL220R			CWL220FO	
2P-3W	15	125	5-15		9, 10	Ultra	AH5266 AH5266BK AH8215HG	AH5269 AH5269BK AH8219HG				5278 5278C	5246 5279C
						9, 10	Safety	AH5266A AH8215HGA AH8215HGAC AH8215HGC	AH8219HGC				
						9, 10	Auto	5266NHG IG5266NHG 5266N	5269NHG 5269N				
						10	Quick	AH5965BK AH5965Y AH8115W	AH5969BK AH5969Y AH8119W				
						10	Economy	5266 5266AN	5269				
						125	L5-15		11	Safety	CWL515P CWL515PAN	CWL515C CWL515CAN	CWL515R IGL515R
				11	Auto	4721N 4721NW	4731N						
				11	Armored vinyl	2473	2493						
				11	Economy	4720	4729						
	250	6-15		10	Ultra	AH5666 AH5666BK	AH5669BK				5678C	5679C	
					9	Safety	AH8225HGA AH8225HGAC						
					10	Auto	5666N	5669N					
10					Quick	AH5666BK AH5666Y	AH5669BK AH5669Y						
10					Economy	5666 5666AN	5669						
250	L6-15		11	Safety	CWL615P	CWL615C	CWL615R IGL615R	6580	CWL615FI	CWL615FO			
				12	Auto	6565N	6566N						
				12	Economy	4570	4579	4560					
277	L7-15		11	Safety	CWL715P	CWL715C	CWL715R	4750	CWL715FI	CWL715FO			
				12	Auto	4771N	4772N						
				12	Economy	4770							
20	125	5-20		9, 10	Ultra	AH5366 AH8315HG	AH5369 AH8319HG				5778C	5779C	
					9	Safety	AH8315HGA AH8315HGAC						
					9, 10	Auto	5366NHG 5366N	5369NHG 5369N					
					11	Quick	AH5364BK AH5364Y	AH5369BK AH5369Y					
					10	Economy	5366 5366AN	5369					
					125	L5-20		12	Ultra	AHCL520P	AHCL520C	AHCL520R IGL520R	
			12	Armored vinyl	2363	2353							
			12	Economy	L520P	L520C	L520R						

Compliances, specifications and availability are subject to change without notice.

Arrow Hart quick reference guide

Pole-Wire	Amp.	V/AC	NEMA		Page	Grip style	Plug	Connector	Single Receptacle	Duplex Receptacle	Flanged Inlet	Flanged Outlet		
2P-3W	20	250	6-20		10	Ultra	AH5466	AH5469			5878C	5879C		
					9	Safety	AH8325HG AH8325HGAC							
					10	Auto	5466N	5469N						
					11	Quick	AH5464BK AH5464Y	AH5469BK AH5469Y						
					10	Economy	5466 5466AN	5469						
250	L6-20		12	Ultra	AHCL620P AH5466BK	AHCL620C AH5469BK	AHCL620R IGL620R	AHCL620FI	AHCL620FO					
			13	Armored vinyl	2364	2354								
			13	Economy	L620P	L620C	L620R							
277	L7-20		13	Ultra	AHCL720P	AHCL720C	AHCL720R IGL720R	AHCL720FI	AHCL720FO					
347	L24-20		13	Standard industrial	L2420P		L2420R							
480	L8-20		13	Ultra	AHCL820P	AHCL820C	AHCL820R IGL820R	AHCL820FI	AHCL820FO					
600	L9-20		13	Standard industrial	CWL920P	CWL920C	CWL920R	CWL920FI	CWL920FO					
30	125	L5-30		14	Ultra	AHCL530P AHIGL530P	AHCL530C	AHCL530R IGL530R	AHCL530FI	AHCL530FO				
					Economy	L530P	L530C	L530R						
	240	L25-30		14	Ultra	AHL2530P	AHL2530C	AHL2530R IGL2530R						
	250	L6-30		15	Ultra	AHCL630P	AHCL630C	AHCL630R IGL630R	AHCL630FI	AHCL630FO				
				15	Economy	L630P	L630C	L630R						
	277	L7-30		16	Ultra	AHCL730P	AHCL730C	AHCL730R IGL730R	AHCL730FI	AHCL730FO				
	480	L8-30		16	Ultra	AHCL830P	AHCL830C	AHCL830R IGL830R	AHCL830FI	AHCL830FO				
	600	L9-30		16	Standard industrial	CWL930P	CWL930C	CWL930R	CWL930FI	CWL930FO				
	3P-3W	15/10	125/250	Non-NEMA Locking		11	Safety	4767 4767AN	4755	7582	7580			
		20	125/250	L10-20		13	Ultra	AHCL1020P	AHCL1020C	AHCL1020R	AHCL1020FI	AHCL1020FO		
						Non-NEMA Locking		12	Safety	9965C	7314C	7310B	7327N	7328N
250						L11-20		13	Ultra	AHCL1120P	AHCL1120C	AHCL1120R	AHCL1120FI	AHCL1120FO
480		L12-20		13	Auto	CWL1220P	CWL1220C	CWL1220R	CWL1220FI	CWL1220FO				
30		125/250	L10-30		16	Ultra	AHCL1030P	AHCL1030C	AHCL1030R	AHCL1030FI	AHCL1030FO			
						Non-NEMA Locking		16	Safety	AH3331N	AH3333N	AHCL3330R	AH3337N	AH3336N
					250	L11-30		16	Ultra	AHCL1130P	AHCL1130C	AHCL1130R	AHCL1130FI	AHCL1130FO
					480	L12-30		16	Auto	CWL1230P	CWL1230C	CWL1230R	CWL1230FI	CWL1230FO
					600	L13-30		16	Auto	CWL1330P	CWL1330C	CWL1330R	CWL1330FI	CWL1330FO

Compliances, specifications and availability are subject to change without notice.

Arrow Hart quick reference guide

Pole-Wire	Amp.	V/AC	NEMA		Page	Grip style	Plug	Connector	Single Receptacle	Duplex Receptacle	Flanged Inlet	Flanged Outlet
3P-4W	20	125/250	L14-20		14	Ultra	AHCL1420P	AHCL1420C	AHCL1420R IGL1420		AHCL1420FI AHCL1420FIBK	AHCL1420FO AHL1420FOBK
		250	L15-20		14	Ultra	AHCL1520P AHL1520PBK	AHCL1520C AHL1520CBK	AHCL1520R IGL1520		AHCL1520FI	AHCL1520FO
		480	L16-20		14	Ultra	AHCL1620P	AHCL1620C	AHCL1620R IGL1620		AHCL1620FI	AHCL1620FO
	30	125/250	L14-30		17	Ultra	AHCL1430P	AHCL1430C	AHCL1430R IGL1430		AHCL1430FI	AHCL1430FO
		250	L15-30		17	Ultra	AHCL1530P	AHCL1530C	AHCL1530R IGL1530		AHCL1530FI	AHCL1530FO
		480	L16-30		17	Ultra	AHCL1630P	AHCL1630C	AHCL1630R		AHCL1630FI	AHCL1630FO
		600	L17-30		17	Ultra	AHCL1730P	AHCL1730C	AHCL1730R		AHCL1730FI	AHCL1730FO
	4P-4W	20	120/208	Non-NEMA Locking		14	Safety	7411C	7413C	7410B		7408N
120/208			L18-20		14	Ultra	AHCL1820P	AHCL1820C	AHCL1820R		AHCL1820FI	AHCL1820FO
277/480			L19-20		14	Ultra	AHCL1920P	AHCL1920C	AHCL1920R		AHCL1920FI	AHCL1920FO
347/600			L20-20		14	Ultra	AHCL2020P	AHCL2020C	AHCL2020R		AHCL2020FI	AHCL2020FO
30		120/208	Non-NEMA Locking		17	Ultra	AH3431N	AH3433N	AHCL3430R		AH3434N	AH3436N
		120/208	L18-30		17	Ultra	AHCL1830P	AHCL1830C	AHCL1830R		AHCL1830FI	AHCL1830FO
		277/480	L19-30		17	Ultra	AHCL1930P	AHCL1930C	AHCL1930R		AHCL1930FI	AHCL1930FO
		347/600	L20-30		17	Ultra	AHCL2030P	AHCL2030C	AHCL2030R		AHCL2030FI	AHCL2030FO
4P-5W	20	120/208	L21-20		15	Ultra	AHCL2120P AHL2120PBK AHL2120PF	AHCL2120C AHL2120CBK AHL2120CF	AHCL2120R IGL2120		AHCL2120FI	AHCL2120FO
		277/480	L22-20		15	Ultra	AHCL2220P	AHCL2220C	AHCL2220R		AHCL2220FI	AHCL2220FO
		347/600	L23-20		15	Ultra	AHCL2320P	AHCL2320C	AHCL2320R		AHCL2320FI	AHCL2320FO
	20/10	250/600	Non-NEMA Locking		12	Ultra	AH3521BK	AH3523BK			AH3524BK	AH3525BK
	30	120/208	L21-30		18	Ultra	AHCL2130P AHL2130PF	AHCL2130C AHL2130CF	AHCL2130R IGL2130		AHCL2130FI	AHCL2130FO
		240/415	L26-30		18	Ultra	AHL2630P	AHL2630C	AHL2630R IGL2630R			
		277/480	L22-30		18	Ultra	AHCL2230P AHL2230PF	AHCL2230C AHL2230CF	AHCL2230R IGL2230		AHCL2230FI	AHCL2230FO
		347/600	L23-30		18	Ultra	AHCL2330P AHL2330PF	AHCL2330C AHL2330CF			AHCL2330FI	AHCL2330FO

Compliances, specifications and availability are subject to change without notice.





We make what matters work.*

* At Eaton, we believe that power is a fundamental part of just about everything people do. Technology, transportation, energy and infrastructure—these are things the world relies on every day. That's why Eaton is dedicated to helping our customers find new ways to manage electrical, hydraulic and mechanical power more efficiently, safely and sustainably. To improve people's lives, the communities where we live and work, and the planet our future generations depend upon. Because that's what really matters. And we're here to make sure it works.

See more at Eaton.com/whatmatters

Visit our website:
Eaton.com/ArrowHart

Connecting safety to reliability with
Arrow Hart products since 1890.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/arrowhart

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2022 Eaton
All Rights Reserved
Printed in USA
Publication No. BR630013EN
May 2022

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/arrowhart

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/arrowhart

Follow us on social media to get the
latest product and support information.

