



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60W47DPLX Straight Blade Duplex Recp IP67 15A 125V 515R

Pass & Seymour/Legrand

Catalog Number	60W47DPLX
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Watertight Duplex Receptacle, 15AMP 125VOLT, Nema Configuration 5-15R, Impact Resistant Valox Lid, Cover Plate, and Receptacle Body Withstand Impacts, Chemical, and Corrosion.
Weight per unit	1.3 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Cable
Cord Type	S, SO, ST, SJ, SJO, SJT, 18/3, to 12/3, .300" min to .625" max diameter
indoor/outdoor	Both
Material	Thermoplastic
Number of Phases	1.0
Number of Wires	3
Phase	1
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	18-12

Descriptions

Description	STRAIGHT BLADE DUPLEX RECP IP67 15A 125V 515R
extra long description	P&S 60W47DPLX STR BLD DPLX REC IP67
Features	Watertight
Long Description	Straight Blade Watertight Duplex Receptacle, 15amp 125volt, NEMA Configuration 5-15R, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.
Product Type	STR BLD DPLX Rec IP67 15A 125V 515R
Special Features	Watertight



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007033472
Manufacturers Part Number	60W47DPLX
UPC	785007033472

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	RECEPTACLE

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	1.3

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized
Mounting	BOX
nema rating	4X/6P
Operating Temperature	-40°-60°C
standard	CSA Listed, FSUL, UL Listed