



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1011 First Place Blvd  
73099-0000, OK Yukon  
Phone: 405-265-8424  
Fax: 405-494-4041



## 89TZ 3-1/2", 90D Emt Elb *Topaz - Southwire LLC*

Catalog Number	89TZ
Manufacturer	Topaz - Southwire LLC
Description	Emt Conduit Elbow, Steel Material; Galvanized Finish; UI 797, Csa Approval; Ansi C80.3, WW-C-563 Applicable Standard; 1 Per Case Standard Package; 3-1/2 Inch Trade Size; Plain End Type; 90 Degree Bend Angle; 15 Inch Bend Radius
Weight per unit	10.8 (lbs/each)
Product Category	Steel

### Features

Applicable Standard	ANSI C80.3, WW-C-563
Bend Angle	90 Degree
Bend Radius	15 INCH
End Type	Plain
Material	Steel

### Material, Color, and Finish

Finish	Galvanized
--------	------------

### Descriptions

Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	3-1/2", 90D EMT ELB
extra long description	STEEL MATERIAL; GALVANIZED FINISH; UL (CANADA AND US), UL 797 APPROVAL; ANSI C80.3, FEDERAL SPECIFICATION WW-C-563 APPLICABLE STANDARD; 35 PER CASE STANDARD PACKAGE; 3-1/2 INCH TRADE SIZE; PLAIN END TYPE; 90 DEGREE BEND ANGLE; 15 INCH BEND RADIUS; STRAIGHT LEG EACH END SIZE 6.75 INCH
Long Description	EMT CONDUIT ELBOW, STEEL MATERIAL; GALVANIZED FINISH; UL 797, CSA APPROVAL; ANSI C80.3, WW-C-563 APPLICABLE STANDARD; 1 PER CASE STANDARD PACKAGE; 3-1/2 INCH TRADE SIZE; PLAIN END TYPE; 90 DEGREE BEND ANGLE; 15 INCH BEND RADIUS
Product Type	Emt Conduit Elbow

### Manufacturer Information

Brand	TOPAZ ELECTRIC CORP
GTIN	00751338305007
Manufacturers Part Number	89TZ
UPC	751338305007



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1011 First Place Blvd  
73099-0000, OK Yukon  
Phone: 405-265-8424  
Fax: 405-494-4041

## Taxonomies, Classifications, and Categories

Category Description ..... EMT ELBOWS

## Trade Size

Trade Size ..... 3-1/2 INCH

## Packaging

Carton ..... 1

Standard Package ..... 1 PER CASE

Weight Per each ..... 10.8

## Uses, Certifications, and Standards

Approval ..... UL 797, CSA