ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3705 Lee Street
Alexandria, LA 71302-0
Phone: 3184451336
Fax: 3184458356

64566 2X6 RGD NIP

TOPAZ - SOUTHWIRE LLC

Catalog Number	64566
Manufacturer	TOPAZ - SOUTHWIRE LLC
Description	2IN X6IN CONDUIT NIPPLE
Weight per unit	1.6 (lbs/each)
Product Category	Steel

Features

End Type	THREADED
Material	Steel

Material, Color, and Finish

Finish	Galvanized

Dimensions and Weight

Length	6 INCH

Descriptions

Commodity Description	ELBOWS-COUPLINGS-NIPPLES - STEEL
Description	2X6 RGD NIP
Features	Topaz□s closed Conduit Nipples are used to extend a length of threaded rigid or IMC conduit. Fabricated from rugged galvanized steel for low conductivity and high corrosion resistance and to ensure secure connections and preserve integrity and longevity. A comprehensive inventory of trade sizes are always in stock and ready for fast delivery to your facility or a job site. UL listed.
Long Description	2IN X6IN CONDUIT NIPPLE RIGID CONDUIT NIPPLE, STRAIGHT TYPE; STEEL MATERIAL; GALVANIZED FINISH; 6 INCH; UL, CSA APPROVAL; 25 PER CASE STANDARD PACKAGE; 2 INCH TRADE SIZE; THREADED END TYPE
Product Type	Rigid Conduit Nipple
Extra Long Description	STEEL MATERIAL; GALVANIZED FINISH; 6 INCH; UL (CANADA AND US) APPROVAL; FEDERAL SPECIFICATION WW-C-563, ANSI C80.1 APPLICABLE STANDARD; 1 PER CASE STANDARD PACKAGE; 2 INCH TRADE SIZE; MALE THREADED END TYPE; USED ON IMC/RIGID CONDUIT

Manufacturer Information

Brand	Southwire Rough Electrical Com SOUTHWIRE ROUGH ELECTRICAL COMPONENTS
GTIN	00751338317505
Manufacturers Part Number	64566
UPC	751338

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3705 Lee Street
Alexandria, LA 71302-0
Phone: 3184451336
Fax: 3184458356

Taxonomies, Classifications, and Categories

Category Description	RIGID NIPPLES
Type	STRAIGHT

Trade Size

Trade Size	2 INCH

Packaging

Carton	1
Package	30
Standard Package	25 PER CASE
Weight Per Each	1.6 (lbs/each)

Uses, Certifications, and Standards

Approval	UL, CSA