



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A1614CHNFSS 16X14X6 N4X SS CLMP CH Encl

Hoffman Enclosures, Inc.

Catalog Number	A1614CHNFSS
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge With Clamps Junction Box Type 4X, 16X14X6, Brushed, Stainless 304
Weight per unit	18.8 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Size	16.00x14.00x6.00 in
Width	14

Descriptions

Description	16X14X6 N4X SS CLMP CH ENCL
extra long description	NVENT HOF A1614CHNFSS Stainless CHN
Features	Used in either indoor or outdoor applications, these enclosures combine a rugged continuous hinge, seamless foam-in-place gasket and stainless steel screw-down clamps for a reliable seal that protects components from corrosive environments.
Long Description	Continuous Hinge with Clamps Junction Box Type 4X, 16x14x6, Brushed, Stainless 304
Product Type	Stainless CHNFSS Box 16.00
Short Description	Stainless CHNFSS Box 16.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510563103
Manufacturers Part Number	A1614CHNFSS
UPC	783510563103

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Terminal and Junction Boxes

Packaging

Carton	1
Weight Per each	18.84



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X