



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 693IG Combo 2 Switches 3W 15A 120/277V Iv

*Pass & Seymour/Legrand*

Catalog Number	693IG
Manufacturer	Pass & Seymour/Legrand
Description	Combination Switch, 1 Pole, 15 A, 120/277 V Ac, Ivory, 1.32 (L) X 0.94 (W) X 3.28 (H) In, Toggle Actuator, Wall Mount, 0.27 LB
Weight per unit	0.2675 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) 3W
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
Load Rating	15 A @ 120/277 VAC
Load Type	Universal, CFL, Fluorescent, Incandescent, Halogen, LED, Xenon
Material	Thermoplastic
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	3-way
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 277 VAC
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2 SWITCHES 3W 15A 120/277V IV
extra long description	P&S 693IG COMBO 2 SWITCHES 3W 15A 1
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006131
Manufacturers Part Number	693IG
UPC	785007006131

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Combination, Switch

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	20
Weight Per each	0.2675

## Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20