



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ACP3034BC 30A 3W4P P&S Plug (600VAC/250VDC)

Appleton/Oz Gedney

Catalog Number	ACP3034BC
Manufacturer	Appleton/Oz Gedney
Description	Pin and Sleeve Plug, 30 A, 600 V Ac 3 Phase @ 50 to 400 HZ 250 V DC, 4 Poles, 3 Wires, Epoxy Powder Coated Copper Free Aluminum, -40 °C Operating Temperature, +107 °C Operating Temperature, Pressure Wire Terminal, #10 to #6 Awg (Building);#10 to #8 Awg (Extra Flex) Wire Size, 1.8 LB
Weight per unit	1.8 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	30
connection	Pressure Wire Terminal
Number of Wires	3
Phase	3
Poles	4

Descriptions

Description	30A 3W4P P&S PLUG (600VAC/250VDC)
extra long description	APP ACP3034BC 30AMP PLUG 3W-4P STYL
Special Features	Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell and extra pole;Ideal for use on shipping docks, ports and other ship to shore applications;Locking screw and slot prevents plug cable collar from backing off;Natural finish glass filled polyester insulating blocks;Plug and receptacle combination is NEMA 4X rated when clamping ring is fully tightened on receptacle;

Manufacturer Information

Brand	Appleton
GTIN	00781381440424
UPC	781381440424

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 2 Metallic Clamping Ring Plug

Packaging

Carton	6
Weight Per each	1.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For ADR3034 Receptacle And ARC3034BC Connector Body
environmental conditions	Temperature Rating: -40 To 107 DEG C
standard	CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917