



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AE50 50 CFM 0.5 Sones Fan Energy Star

Broan/Nutone LLC

|                  |   |
|------------------|---|
| Catalog Number   | AE50  |
| Manufacturer     | Broan/Nutone LLC  |
| Description      | Ventilation Fan, 26 Gauge Rugged Galvanized Steel, Ceiling Mount, 120 V Ac @ 60 HZ, 20 W, 0.2 A, 50 CFM Air Flow, 60 HZ, Round Duct Shape, 4 In Duct Size, White, Polymeric Grill Material, Square Grill Shape, 11-1/2 In (L) X 12 In (W) Grill Size, Rugged 26 Gauge Galvanized Steel Housing Material, Square Housing Shape, 10 In Overall Length, 9-1/4 In Overall Width, 5-3/4 In Overall Height, 4 In Duct Diameter, Exhaust, 8.6 LB |
| Weight per unit  | 8.6 (lbs/each)  |
| Product Category | Exhaust Fans  |

### Features

|               |           |
|---------------|-----------|
| Air Flow Rate | 50 CFM    |
| Sound Level   | 0.5 Sones |

### Dimensions and Weight

|      |   |
|------|---|
| Size | 10 Inch Length x 9-1/4 Inch Width x 5-3/4 Inch Height |
|------|---|

### Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Power Rating 20 Watt; Includes Non-Metallic Damper/Duct Connector |
| Commodity Description  | Exhaust Fans  |
| Description            | 50 CFM 0.5 SONES FAN ENERGY STAR                                  |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00026715236466 |
| UPC  | 026715236466   |

### Taxonomies, Classifications, and Categories

|                      |                  |
|----------------------|------------------|
| Category Description | FANS & HEATERS   |
| Type                 | 1-Speed, Ceiling |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 8.6 |

### Uses, Certifications, and Standards

|          |       |
|----------|-------|
| Approval | UL mA |
|----------|-------|