

# Specifications

## Eaton AH430C7W

Eaton Arrow Hart pin and sleeve connector, IP69K Rated, #10 -#2 AWG, 30A, 3Ø 480V, Back wire, Red, Nickel plated brass, IP67, Nylon, Three-pole, Four-wire, grounding, 0.433-0.985in (1.10-2.5cm), Female, 10 HP, Nylon, Three-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart pin and sleeve connector
<b>CATALOG NUMBER</b>	AH430C7W
<b>UPC</b>	032664732720
<b>PRODUCT LENGTH/DEPTH</b>	10.375 in
<b>PRODUCT HEIGHT</b>	4.813 in
<b>PRODUCT WIDTH</b>	4.75 in
<b>PRODUCT WEIGHT</b>	1.207 lb
<b>CERTIFICATIONS</b>	cRUus
<b>PRODUCT TYPE</b>	Pin and Sleeve connector



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Connector
<b>AMPERAGE RATING</b>	30A
<b>VOLTAGE RATING</b>	480 V
<b>CONTACT MATERIAL</b>	Nickel plated brass
<b>APPLICATION</b>	Industrial, food and beverage, wastewater treatment
<b>NUMBER OF WIRES</b>	Grounding 4
<b>NUMBER OF POLES</b>	Three-pole
<b>CORD DIAMETER</b>	0.433-0.985in (1.10-2.5cm)
<b>PHASE</b>	Three-phase
<b>ENVIRONMENTAL RESISTANCE</b>	IP69K IP67
<b>COLOR</b>	Red
<b>GENDER</b>	Female
<b>HORSEPOWER</b>	10 hp
<b>ALLOWABLE WIRE SIZE</b>	#10-2 AWG
<b>TORQUE RATING</b>	10 lbf-inch
<b>DESIGN TYPE</b>	Pin and sleeve connector
<b>FACE/BODY MATERIAL</b>	Nylon
<b>MATERIAL</b>	Nylon

## Resources

<b>BROCHURES</b>	<a href="#">Eaton IEC 60309 Arrow Hart pin and sleeve devices brochure</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - AH430C7W</a> <a href="#">20A and 30A IEC 309 Watertight pin and sleeve devices spec sheet</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton AH430C7W

Eaton Arrow Hart pin and sleeve connector, IP69K Rated, #10 -#2 AWG, 30A, 3Ø 480V, Back wire, Red, Nickel plated brass, IP67, Nylon, Three-pole, Four-wire, grounding, 0.433-0.985in (1.10-2.5cm), Female, 10 HP, Nylon, Three-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton Arrow Hart pin and sleeve connector
<b>CATALOG NUMBER</b>	AH430C7W
<b>UPC</b>	032664732720
<b>PRODUCT LENGTH/DEPTH</b>	10.375 in
<b>PRODUCT HEIGHT</b>	4.813 in
<b>PRODUCT WIDTH</b>	4.75 in
<b>PRODUCT WEIGHT</b>	1.207 lb
<b>CERTIFICATIONS</b>	cRUus
<b>PRODUCT TYPE</b>	Pin and Sleeve connector



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	Connector
<b>AMPERAGE RATING</b>	30A
<b>VOLTAGE RATING</b>	480 V
<b>CONTACT MATERIAL</b>	Nickel plated brass
<b>APPLICATION</b>	Industrial, food and beverage, wastewater treatment
<b>NUMBER OF WIRES</b>	Grounding 4
<b>NUMBER OF POLES</b>	Three-pole
<b>CORD DIAMETER</b>	0.433-0.985in (1.10-2.5cm)
<b>PHASE</b>	Three-phase
<b>ENVIRONMENTAL RESISTANCE</b>	IP69K IP67
<b>COLOR</b>	Red
<b>GENDER</b>	Female
<b>HORSEPOWER</b>	10 hp
<b>ALLOWABLE WIRE SIZE</b>	#10-2 AWG
<b>TORQUE RATING</b>	10 lbf-inch
<b>DESIGN TYPE</b>	Pin and sleeve connector
<b>FACE/BODY MATERIAL</b>	Nylon
<b>MATERIAL</b>	Nylon

## Resources

<b>BROCHURES</b>	<a href="#">Eaton IEC 60309 Arrow Hart pin and sleeve devices brochure</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - AH430C7W</a> <a href="#">20A and 30A IEC 309 Watertight pin and sleeve devices spec sheet</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

