



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



71A8172001D 150W HPS Quad Ballast

Advance By Signify

Catalog Number	71A8172001D
Manufacturer	Advance By Signify
Description	Magnetic Hid Kit, Magnetic Hid Ballast, Pulse, 150 W, 120/208/240/277 V Ac, 2.8 A;1.6 A;1.4 A;1.25 A, Non Dimmable, 1 Lamps, 3.9 In Length, 4.2 In Width, 2.8 In Height, 1 Ballast Factor, 0.90 Power Factor, 60 HZ, -40 °F (Starting Temperature) Operating Temperature, +105 °C (Ignitor) Operating Temperature, 3.688 KG
Weight per unit	8.2 (lbs/each)
Product Category	Hid Ballast Kits

Features

ANSI Code	S55
dimnable	No
Lamp Type	HPS
Power Rating	150 W

Descriptions

Description	150W HPS QUAD BALLAST
-------------	-----------------------

Manufacturer Information


Brand	Signify Electronics
GTIN	00781087817216
UPC	781087817216

Taxonomies, Classifications, and Categories

Category Description	HID BALLASTS
Type	Magnetic HID

Packaging

Carton	1
Weight Per each	8.16



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID 71A8172001D

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S55
Lamp Type	150W HPS
Number of Lamps	1 piece/unit
Circuit Type	HX-HPF
Ballast Type	Magnetic HID
Base Model	71A8172
Core Size	3 X 4 (2 LW)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI551-H4
Ignitor Temperature Rating	105°C
Capacitor Value	14 MFD
Capacitor Catalog Number	7C140M30RA
Capacitor Requirements	280V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.65 in
Capacitor Height	2.75 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/208/240/277 V

Input Frequency	60 Hz
Input Current (Open Circuit)	2.8/1.6/1.4/1.25 A
Input Current (Starting)	2/1.15/1/0.85 A
Input Current (Short Circuit)	1.15-1.75/0.65-1/0.55-0.85/0.5-0.75 A
Secondary Short Circuit Current	3.95-4.85 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	120 V
Input Current (Nom)	1.65/0.95/0.83/0.72 A A
Input Power (Nom)	190 W
Rated Lamp Power	150 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	2'
Recommended Fuse Value	10/5/5/4 A

Core & Coil (71A) HPS ~LT~ 200W


Approval and Application

Open Circuit Voltage Test (Volts)	110-130 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	E/E/E/E
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029E

Product Data

Order product name	CORE & COIL HID 71A8172001D
EAN/UPC - Product	781087817216
Order code	913700556509
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700556509
Net Weight (Piece)	3.688 kg

Dimensional drawing



HPS BAL 150W S55 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A8172001D	4.2 in	2.5 in	3.9 in	3.5 in	2.8 in	2.4 in

