



F-can (72C)

F-CAN HID MH BAL 70W M98/143 120/277V FCAN

The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans.

Product data

General Information	
ANSI Code	M98(PULSESTART)
Lamp Type	70W MH
Number of Lamps	1 piece/unit
Circuit Type	HX-HPF
Ballast Type	Magnetic HID
Base Model	72C5282
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	Inside Can
Capacitor Catalog Number	Inside Can
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/277 V
Input Frequency	60 Hz
Input Current (Open Circuit)	1.6/0.75 A
Input Current (Starting)	1.25/0.55 A
Input Current (Short Circuit)	0.55-0.85/0.25-0.4 A
Secondary Short Circuit Current	0.95-1.2 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	255 V
Input Current (Nom)	0.85/0.37 A A

Input Power (Nom)	94 W	
Rated Lamp Power	70 W	
Wiring		
Wire Striplength	0.5 mm	
Wire Length by Color	12"	
Wire Type	Stranded	
Remote Wiring Configuration Allowed	Yes	
Max Ballast-Lamp Distance Remote Wiring 10'		
Recommended Fuse Value	4/2 A	
Mechanical and Housing		
Housing Material	Metal	
Housing Material Housing	Metal F-Can	
Housing	F-Can	
Housing	F-Can	
Housing Housing Dimensions	F-Can	
Housing Housing Dimensions Approval and Application	F-Can 11.75 x 2.63 x 3.19	
Housing Dimensions Approval and Application Open Circuit Voltage Test (Volts)	F-Can 11.75 x 2.63 x 3.19 230-280 V	
Housing Dimensions Approval and Application Open Circuit Voltage Test (Volts)	F-Can 11.75 x 2.63 x 3.19 230-280 V CSA certificate UL certificate RoHS	
Housing Housing Dimensions Approval and Application Open Circuit Voltage Test (Volts) Approval Marks	F-Can 11.75 x 2.63 x 3.19 230-280 V CSA certificate UL certificate RoHS Compliant	
Housing Housing Dimensions Approval and Application Open Circuit Voltage Test (Volts) Approval Marks Temperature Marking	F-Can 11.75 x 2.63 x 3.19 230-280 V CSA certificate UL certificate RoHS Compliant 90°C max. case	
Housing Housing Dimensions Approval and Application Open Circuit Voltage Test (Volts) Approval Marks Temperature Marking UL Recognized	F-Can 11.75 x 2.63 x 3.19 230-280 V CSA certificate UL certificate RoHS Compliant 90°C max. case No	


Datasheet, 2019, March 22 data subject to change

F-can (72C)

UL Insulation Class	A(105°C)
UL Temperature Code	NA
Product Data	
Order product name	F-CAN HID MH BAL 70W M98/143 120/277V
	FCAN
EAN/UPC - Product	781087025253

Order code	913710407801
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710407801
Net Weight (Piece)	4.086 kg

Dimensional drawing



MH BAL 70W M98/143 120/277V FCAN

 Product
 A1
 A2
 A3
 B1
 B2
 C1
 D1

 F-CAN HID MH BAL 70W M98/143
 12 in
 11.13 in
 10.5 in
 3.9 in
 2.0 in
 2.6 in
 0.3 in

 120/277V FCAN

