# Arrow Hart color coded industrial grade L16-30 locking devices

| Project Name:   | Prepared By: |  |
|-----------------|--------------|--|
| Project Number: | Date:        |  |
| Catalog Number: | Type:        |  |



Photography is for reference only.

# **Description**

30A, 3Ø 480V/AC, 3-Pole, 4-Wire NEMA L16-30







#### Design features for plug & connector

- · All nylon construction
- · EPDM gasket seals cord hole from dust and debris
- · Back wire terminal clamps for easy secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires
- Clear cover over wiring compartments allows easy inspection of wiring terminations
- · Rating printed on side of device
- Double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters

#### Design features for receptacle

- · Rugged glass filled nylon body
- Clearly marked rating, NEMA configuration and approval listings on receptacle face
- One piece brass contacts offer superior performance and minimum heat rise
- · Back and side wiring terminal clamps for easy, secure wiring

## Design features for flanged inlet & outlet

- All nylon construction
- Mounting holes interchangeable with competitive units
- · Back wire terminal clamps for easy, secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires

Table 1. NEMA L16-30 Color Coded Industrial Grade Locking Devices

| Catalog No.  | Description                                  | Amps | Volts | Color       |
|--------------|--|------|-------|-------------|
| ☐ AHCL1630P  | Color coded ultra grip plug, 3-phase         | 30   | 480   | Red & Black |
| ☐ AHCL1630C  | Color coded ultra grip connector,<br>3-phase | 30   | 480   | Red & Black |
| □ AHCL1630R  | Color coded single receptacle,<br>3-phase    | 30   | 480   | Red & Black |
| ☐ AHCL1630F0 | Color coded flanged outlet, 3-phase          | 30   | 480   | Red & Black |
| ☐ AHCL1630FI | Color coded flanged inlet, 3-phase           | 30   | 480   | Red & Black |

Compliances, specifications and availability are subject to change without notice.



| Project Name:   | Prepared By: |
|-----------------|--------------|
| Project Number: | Date:        |
| Catalog Number: | Type:        |

# **Applications**

The new Eaton Arrow Hart color coded locking devices are designed specifically to improve safety and increase labor savings on the job site. Eaton's color coded locking devices are an industry-first solution that uses the six voltage rating color codes consistent with IEC 60309 standards for plugs, connectors, inlets/outlets and receptacles. Color coded locking devices are available in standard NEMA configurations for 20A and 30A applications. Plugs and connectors are built with a durable nylon shell and body to provide long lasting, dependable service in commercial and industrial environments—their ergonomic design has a comfortable feel, and the double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters.

Table 2. Specifications


| Catalog No.                  | AHCL1630 Series   |  |   |
|------------------------------|---|--|---|
| Device Type                  | Plug & Connector  | Single Receptacle  | Flanged Inlet & Outlet  |
| NEMA Config                  | NEMA L16-30   | NEMA L16-30  | NEMA L16-30   |
| Wiring Type                  | Back wire   | Back & side wire   | Back wire   |
| Environmental Specifications | Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F)   | Flammability: Meets UL94 requirements;<br>V0 rated<br>Temperature Rating: -40°C to 70°C<br>(-40°F to 158°F)  | Flammability: Meets UL94 requirements;<br>V2 rated<br>Temperature Rating: -40°C (w/o impact)<br>to 60°C (-40°F to 140°F)<br>-25°C (w/impact) to 60°C (-13°F to 140°F)   |
| Electrical Specifications    | Dielectric Voltage: Twice the device rating + 1000V per UL498<br>Current Interrupting: Yes, at full-rated current<br>Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC) | Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC) | Dielectric Voltage: ≤300V: 2000V, 301-<br>600V: 3000V per UL498<br>Current Interrupting: Yes, at full-rated<br>current<br>Temperature Rise: Max. 30°C (86°F) after<br>50 cycles of overload @ 150% of rated<br>current (DC) |
| Mechanical Specifications    | Terminal Accommodation: #14 - #8 AWG<br>Voltage Ratings: Permanently marked on device   | Terminal Accommodation: #14 - #8 AWG<br>Voltage Ratings: Permanently marked on<br>device   | Terminal Accommodation: #14 - #8 AWG<br>Voltage Ratings: Permanently marked on<br>device  |

#### Table 3. Materials

| Catalog No.            | AHCL1630 Series                           |   |   |
|------------------------|---|---|---|
| Device Type            | Plug & Connector                          | Single Receptacles                          | Flanged Inlet & Outlet                      |
| NEMA Config            | NEMA L16-30                               | NEMA L16-30                                 | NEMA L16-30                                 |
| Outer Shell            | Nylon                                     | N/A   | Nylon                                       |
| Face                   | N/A                                       | Glass-filled nylon                          | N/A   |
| Base                   | N/A                                       | Glass-filled nylon                          | N/A   |
| Mounting Strap         | N/A                                       | 0.050" thick steel, zinc plated             | N/A   |
| Interior Body          | Nylon                                     | N/A   | Nylon                                       |
| Terminal Retainer      | Polycarbonate                             | N/A   | Polycarbonate                               |
| Blades                 | Brass                                     | N/A   | 0.062" thick brass (inlet only)             |
| Line Contacts          | Bronze, tin plated                        | 0.041" thick brass                          | 0.031" thick brass (outlet only)            |
| Terminal Clamps/Plates | Steel, tin plated                         | 0.041" thick brass                          | Steel                                       |
| Terminal Screws        | #10-32 brass, zinc plated (neutral screw) | #10-32 brass, nickel plated (neutral screw) | #10-32 brass, nickel plated (neutral screw) |
| Ground Screw           | #10-32 brass (green)                      | #10-32 brass (green)                        | #10-32 brass (green)                        |
| Assembly Screws        | Steel, nickel plated                      | N/A   | Steel, zinc plated                          |
| Gasket/Dust Shield     | EPDM                                      | N/A   | N/A   |
| Cord Clamp Screws      | Steel, nickel plated                      | N/A   | N/A   |
| Cord Clamp             | Nylon                                     | N/A   | N/A   |
| Ground Contacts        | N/A                                       | 0.041" thick brass                          | N/A   |
| Back Plate             | N/A                                       | 0.041" thick brass, nickel plated           | N/A   |
| Mounting Screws        | N/A                                       | Steel, zinc plated                          | Steel, zinc plated                          |

| Project Name:   | Prepared By: |  |  |
|-----------------|--------------|--|--|
| Project Number: | Date:        |  |  |
| Catalog Number: | Type:        |  |  |

## **Product Dimensions**



1.97" - (50.0mm) → (100.08mm)  $^{\circ}$ 




Figure 1. AHCL1630P

Figure 2. AHCL1630C

Figure 3. Bottom View





Figure 4. AHCL1630R



3.06" (77.7mm)-2.03" (51.6mm)-2.24" (56.9mm) (55.6mm)

Figure 5. AHCL1630FO

Figure 6. AHCL1630FI

0.22" (5.6mm) 120° 120° -1.34"-(34.0mm)

Figure 7. Top View

# Arrow Hart color coded industrial grade L16-30 locking devices

| Project Name:   | Prepared By: |  |  |
|-----------------|--------------|--|--|
| Project Number: | Date:        |  |  |
| Catalog Number: | Type:        |  |  |

# **Certifications & Compliances**

| Catalog No. | ¢ՄL)us | <b>(h)</b> | ⊕- | _ | <b>£</b> | <u>HOM</u><br>426 |
|-------------|--------|------------|----|---|----------|-------------------|
| AHCL1630P   | •      |            |    | • | •        | •                 |
| AHCL1630C   | •      |            |    | • | •        | •                 |
| AHCL1630R   |        | •          | •  | • | •        | •                 |
| AHCL1630F0  | •      |            |    | • | •        | •                 |
| AHCL1630FI  | •      |            |    | • | •        | •                 |
|             |        |            |    |   |          |                   |

ւ**Մ∟**տ cULus

KEY:

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

CSA

AFTA

₩ ROHS

Compliances, specifications and availability are subject to change without notice.

(N) UL

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com/wiringdevices Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Eaton.com/wiringdevices

© 2018 Eaton All Rights Reserved Printed in USA Publication No. TD630037EN (rev 1) December 2018 Mexico Operations Carr. TlaInepantla -Cuautilan Km 17.8 s/n Col. Villa Jardin esq. Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800 Mexico Eaton.mx Eaton.com/wiringdevices

Electrical Sector

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com