

Eaton 7503V-BOX

Catalog Number: 7503V-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 752421



General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7503V-BOX
UPC	Product Length/Depth
032664752421	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.15 lb	NAFTA
	RoHS Compliant
Certifications	
cULus Listed	

Product specifications

Special features

Box

Switch type

Three-way

Phase

Single-phase

Load type

Fan

LED

Motor Control

CFL

FLR

HAL

ELV

INC

MLV

Closure type

Maintained

Color

Ivory

Wiring method

Back and push

Material

Thermoplastic

Mounting method

Flush

Allowable wire size

#14-12 AWG

Amperage Rating

15A

Number Of Poles

Three-way

Type

Switch decorator

Voltage rating

120/277 V

Resources

Brochures

Decorator standard grade switches spec sheet

Specifications and datasheets

Eaton Specification Sheet - 7503V-BOX

Actuator
Decorator



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)