


# Specifications



Photo is representative



## Eaton 7621V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 647291

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade decorator switch
<b>CATALOG NUMBER</b>	7621V-BOX
<b>UPC</b>	032664647291
<b>PRODUCT LENGTH/DEPTH</b>	1.29 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	1.18 in
<b>PRODUCT WEIGHT</b>	0.2 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cULus Listed
<b>PRODUCT TYPE</b>	Commercial grade decorator switch



Powering Business Worldwide

## Product specifications

<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>SPECIAL FEATURES</b>	Box
<b>TYPE</b>	Switch decorator
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	120/277 V
<b>NUMBER OF POLES</b>	Single-pole
<b>PHASE</b>	Single-phase
<b>WIRING METHOD</b>	Back and push
<b>SWITCH TYPE</b>	Single-pole
<b>MOUNTING METHOD</b>	Flush
<b>CLOSURE TYPE</b>	Maintained
<b>LOAD TYPE</b>	LED Motor Control ELV INC Fan CFL HAL MLV FLR
<b>MATERIAL</b>	Thermoplastic
<b>ACTUATOR</b>	Antimicrobial paddle
<b>COLOR</b>	Ivory

## Resources

	<a href="#">Eaton Specification Sheet - 7621V-BOX</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Arrow Hart commercial specification grade AC decorator switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton 7621V-BOX

Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, Ivory, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Single-pole, Thermoplastic 647291

### General specifications

<b>PRODUCT NAME</b>	Eaton commercial grade decorator switch
<b>CATALOG NUMBER</b>	7621V-BOX
<b>UPC</b>	032664647291
<b>PRODUCT LENGTH/DEPTH</b>	1.29 in
<b>PRODUCT HEIGHT</b>	4.19 in
<b>PRODUCT WIDTH</b>	1.18 in
<b>PRODUCT WEIGHT</b>	0.2 lb
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed cULus Listed
<b>PRODUCT TYPE</b>	Commercial grade decorator switch



Powering Business Worldwide

## Product specifications

<b>ALLOWABLE WIRE SIZE</b>	#14-10 AWG
<b>SPECIAL FEATURES</b>	Box
<b>TYPE</b>	Switch decorator
<b>AMPERAGE RATING</b>	20A
<b>VOLTAGE RATING</b>	120/277 V
<b>NUMBER OF POLES</b>	Single-pole
<b>PHASE</b>	Single-phase
<b>WIRING METHOD</b>	Back and push
<b>SWITCH TYPE</b>	Single-pole
<b>MOUNTING METHOD</b>	Flush
<b>CLOSURE TYPE</b>	Maintained
<b>LOAD TYPE</b>	LED Motor Control ELV INC Fan CFL HAL MLV FLR
<b>MATERIAL</b>	Thermoplastic
<b>ACTUATOR</b>	Antimicrobial paddle
<b>COLOR</b>	Ivory

## Resources

	<a href="#">Eaton Specification Sheet - 7621V-BOX</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Arrow Hart commercial specification grade AC decorator switches spec sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

