Arrow Hart color coded industrial grade L21-20 locking devices

Project Name:	Prepared By:	
Project Number:	Date:	
Catalog Number:	Type:	



Photography is for reference only.

Description

20A, 3ØY 120/208V/AC, 4-Pole, 5-Wire NEMA L21-20 20A





= Blue indicates 120/208 V/AC

Design features for plugs & connectors

- All nylon construction
- · EPDM gasket seals cord hole from dust and debris
- · Back wire terminal clamps for easy secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires
- Clear cover over wiring compartments allows easy inspection of wiring terminations
- · Rating printed on side of device
- Double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters

Design features for receptacles

- · Rugged glass filled nylon body
- Clearly marked rating, NEMA configuration and approval listings on receptacle face
- One piece brass contacts offer superior performance and minimum heat rise
- Back and side wiring terminal clamps for easy, secure wiring

Design features for flanged inlet & outlet

- All nylon construction
- · Mounting holes interchangeable with competitive units
- Back wire terminal clamps for easy, secure wiring
- Individual wiring compartments with tapered channel for easy insertion of wires

Table 1. NEMA L21-20 Color Coded Industrial Grade Locking Devices

Catalog No. Description		Amps	Volts	Color
☐ AHCL2120P	Color Coded ultra grip plug, 3-phase	20	120/208	Blue & Black
□ AHCL2120C	Color Coded ultra grip connector, 3-phase	20	120/208	Blue & Black
□ AHCL2120R	Color Coded single receptacle, 3-phase	20	120/208	Blue & Black
☐ AHCL2120FO	Color Coded flanged outlet, 3-phase	20	120/208	Blue & Black
☐ AHCL2120FI	Color Coded flanged inlet, 3-phase	20	120/208	Blue & Black

Table 2. NEMA L21-20 Industrial Grade Flat Locking Devices

Catalog No.	Description	Amps	Volts	Color
☐ AHL2120PF	Ultra grip plug, flat cable, 3-phase	20	120/208	Black
☐ AHL2120FF Ultra grip plug, flat cable, 3-phase ☐ AHL2120CF Ultra grip connector, flat cable, 3-phase		20	120/208	Black



Project Name:	Prepared By:		
Project Number:	Date:		
Catalog Number:	Туре:		

Applications

The new Eaton Arrow Hart color coded locking devices are designed specifically to improve safety and increase labor savings on the job site. Eaton's color coded locking devices are an industry-first solution that uses the six voltage rating color codes consistent with IEC 60309 standards for plugs, connectors, inlets/outlets and receptacles. Color coded locking devices are available in standard NEMA configurations for 20A and 30A applications. Plugs and connectors are built with a durable nylon shell and body to provide long lasting, dependable service in commercial and industrial environments—their ergonomic design has a comfortable feel, and the double dovetail cord clamps with reversible inserts provide secure cord retention over a full range of cord diameters.

Table 3. Specifications


Catalog No.	AHCL2120 Series		
Device Type	Plugs & Connectors	Single Receptacles	Flanged Inlet & Outlet
NEMA Config	NEMA L21-20	NEMA L21-20	NEMA L21-20
Wiring Type	Back wire	Back & side wire	Back wire
Environmental Specifications	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F) except flat cable: -40°C (w/o impact) to 75°C (-40°F to 167°F)	Flammability: Meets UL94 requirements; V0 rated Temperature Rating: -40°C to 70°C (-40°F to 158°F)	Flammability: Meets UL94 requirements; V2 rated Temperature Rating: -40°C (w/o impact) to 60°C (-40°F to 140°F) -25°C (w/impact) to 60°C (-13°F to 140°F)
Electrical Specifications	Dielectric Voltage: Twice the device rating + 1000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric Voltage: ≤300V: 2000V, 301-600V: 3000V per UL498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
Mechanical Specifications	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device	Terminal Accommodation: #14 - #8 AWG Voltage Ratings: Permanently marked on device


Table 4. Materials

Catalog No.	AHCL2120 Series		
Device Type	Plug & Connector	Single Receptacles	Flanged Inlet & Outlet
NEMA Config	NEMA L21-20	NEMA L21-20	NEMA L21-20
Face	N/A	Glass-filled nylon	N/A
Base	N/A	Glass-filled nylon	N/A
Mounting Strap	N/A	0.050" thick steel, zinc plated	N/A
Outer Shell	Nylon	N/A	Nylon
Interior Body	Nylon	N/A	Nylon
Terminal Retainer	Polycarbonate	N/A	Polycarbonate
Blades	Brass	N/A	0.062" thick brass (inlet only)
Line Contacts	Bronze, tin plated	0.041" thick brass	0.031" thick bronze (outlet only)
Terminal Clamps/Plates	Steel, tin plated	0.041" thick brass	Steel
Terminal Screws	#10-32 brass, zinc plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)
Ground Screw	#10-32 brass (green)	#10-32 brass (green)	#10-32 brass (green)
Assembly Screws	Steel, nickel plated	N/A	Steel, nickel plated
Gasket/Dust Shield	EPDM	N/A	N/A
Cord Clamp Screws	Steel, nickel plated	N/A	N/A
Cord Clamp	Nylon	N/A	N/A
Ground Contacts	N/A	0.041" thick brass	N/A
Back Plate	N/A	0.041" thick brass, nickel plated	N/A
Mounting Screws	N/A	Steel, zinc plated	Steel, zinc plated

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Product Dimensions








Figure 1. AHCL2120P

Figure 2. AHCL2120C

Figure 3. Bottom View





Figure 4. AHCL2120R





0.22" (5.6mm) 120° 120°

Figure 5. AHCL2120FO

Figure 6. AHCL2120FI

Figure 7. Top View

Arrow Hart color coded industrial grade L21-20 locking devices

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Certifications & Compliances

c(UL)us	(l)	(∰-	F (l) S	NOM 426	<u></u>	 €
•				•	•	•
				•	•	•
•				•	•	•
				•	•	•
	•	•	•	•	•	•
•				•	•	•
•				•	•	•
	•	c(h) vs (h)	• • •	• • • • • •	•	c(N)n (N) (N) F(O)S (N)

 ROHS KEY: շ**Մ**Lus cULus ● UL ◆ CSA F®s Fed Spec NOM NOM NAFTA Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

Compliances, specifications and availability are subject to change without notice.

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Eaton.com/wiringdevices

Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 EatonCanada.ca Eaton.com/wiringdevices

© 2018 Eaton All Rights Reserved

Printed in USA
Publication No. TD630039EN (rev 1)
December 2018

Eaton is a registered trademark.

Electrical Sector

Mexico Operations

Col. Villa Jardin esq.

Eaton.mx

Carr. Tlalnepantla -Cuautitlan Km 17.8 s/n

Cerrada 8 de Mayo Cuautitlan, Mexico CP 54800

Eaton.com/wiringdevices

All other trademarks are property of their respective owners.

