



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7813PMD 30A 3P 3 PH Ac MD Nema 1 Enc

*Pass & Seymour/Legrand*

Catalog Number	7813PMD
Manufacturer	Pass & Seymour/Legrand
Description	Ac Manual Motor Controller, Suitable As Motor Disconnect - 10KA @ 600VAC, 30A Max. Class J Fuse.
Weight per unit	0.7180 (lbs/each)
Product Category	Misc Wiring Devices

### Features

actuator	Toggle
amperage rating	30
connection	Side & Back Wired
Enclosure Type	Nema 1
indoor/outdoor	Both
load	30A
Load Rating	30 A @ 600 VAC
Load Type	CFL, Xenon, Universal, Incandescent, LED, Halogen, Fluorescent
Material	Aluminum
Mounting Type	On-Wall
Number of Gangs	1
Number of Phases	3.0
Number of Switches	1.0
operating cycles	50000
Poles	3-way
Switch Type	Toggle
throw type	Triple Throw
Voltage	600.0 V
Voltage Rating	600
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	2.8" Depth x 2.825" Width x 3.91" Height
------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	30A 3P 3 PH AC MD NEMA 1 ENC
extra long description	P&S 7813PMD 30A 3P 3 PH AC MD, NEMA
Features	Enclosed
Long Description	AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.
Product Type	30A 3P 3 PH Ac MD, Nema 1 Enc
Special Features	Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007267693
Manufacturers Part Number	7813-PMD
UPC	785007267693

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller

## Trade Size

Amperage	30.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.718

## Uses, Certifications, and Standards

Application	Commercial/Industrial
Enclosure	NEMA 1
environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	FLUSH
Operating Temperature standard	Maximum continuous +75°C, minimum -40°C CULUS, CSA Listed, UL Listed