

Specifications

Eaton AHCL720C

Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 20A, Industrial, 277V, Back, Gray, Black, Ultra grip, Nylon, L7-20, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

General specifications

PRODUCT NAME	Eaton Arrow Hart Color Coded Locking Connector
CATALOG NUMBER	AHCL720C
UPC	032664755668
PRODUCT LENGTH/DEPTH	2.23 in
PRODUCT HEIGHT	3.71 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.49 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Color Coded Locking



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Voltage Color Coding
TYPE	Locking Connector
AMPERAGE RATING	20A
VOLTAGE RATING	277 V
APPLICATION	Industrial
WIRING METHOD	Back
NUMBER OF WIRES	3
NUMBER OF POLES	Two-pole
COLOR	Gray Black
CORD DIAMETER	0.38-1 in (9.5-25.4 mm)
MATERIAL	Nylon
OPERATING TEMPERATURE	-40 to 60 °C (-40 to 140 °F)
ALLOWABLE WIRE SIZE	#14-8 AWG Copper, or Copper-Clad Aluminum
NEMA CONFIGURATION	L7-20
TORQUE RATING	For #10-14 AWG: 14-16 lbf- inch. For #8 AWG: 20 lbf- inch
DESIGN TYPE	Ultra grip
FACE/BODY MATERIAL	Nylon

Resources

MULTIMEDIA	Eaton Arrow Hart color coded locking devices
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - AHCL720C Arrow Hart color coded industrial grade L7-20 locking devices spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

