



# AMS4/0

by Burndy Catalog ID: AMS4/0

Prop65

Aluminum Mechanical Splice, 4/0-6 AWG, 9/16" Screw Dia, 2 Screws, 5/16" Hex Size, Al/Cu Rated, Tin Plated.

Features: All Splicer/Reducers Are Dual Rated For Use With Aluminum And Copper Conductors And Are Constructed From High Strength, Tin Plated Aluminum, PENTROX Oxide Inhibiting Joint Compounds Are Recommended For All Aluminum Applications, All Connectors Are Tin-Plated: Provide Low Contact Resistance And Prevents Galvanic Corrosion, Connectors Feature Rounded Bottoms: Facilitates Taping, Solid Center Barrier: Prevents Contact Of Dissimilar Metals, Large Screw Diameters: Ensures Greater Surface Contact With Wires For Maximum Pullout Force, Large Cable Ranges: Each Splice Is Also An Effective Reducing Connector, Conductor Type: Copper, Aluminium, Number Of Screws: 2, Hex Size: 5/16 IN, Screw Diameter: 9/16 IN

## **Product Details**

### General

| Application                           | For Use With Copper And Aluminum Conductors |
|---------------------------------------|---|
| Connector Type                        | Splice;Reducer                              |
| Hex Size                              | 5/16  |
| Installation Torque Recommended in-Ib | 275 LBS/in                                  |
| Material                              | Aluminum                                    |
| Material - Hardware                   | Aluminum                                    |
| Physical Attribute - Number of Screws | 2   |
| Physical Attribute - Screw Type       | Slot  |
| Plated                                | Y   |
| Plating Type                          | Tin   |
| Sub Brand                             | SPLICER/REDUCER                             |
| Temperature Rating                    | 194° F                                      |
| Туре                                  | AMS, Dual Rated                             |
| UPC                                   | 781810241028                                |
| UPC 12 Digit                          | 7818102410288                               |

### Dimensions

| Dimension - H1 Height inch      | 1.09 in |
|---------------------------------|---------|
| Dimension - Height fraction     | 1-3/32  |
| Dimension - L Length Overall mm | 59 mm   |
| Dimension - Length Overall inch | 2.31 in |
| Dimension - Width fraction      | 1 in    |
| Dimension - Width inch          | 1.00 in |
| Dimension - Width mm            | 25 mm   |

### **Electrical Ratings**

| Rating - Minimum Voltage | 600 |
|--------------------------|-----|
|                          |     |

### Conductor Related

| Conductor - AL Str Run              | 6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG       |
|-------------------------------------|---|
| Conductor - AL Str Run Range        | 6 AWG-4/0 AWG   |
| Conductor - AL Str Size             | 6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG       |
| Conductor - AL Str Size Range       | 6 AWG-4/0 AWG   |
| Conductor - AL Str Tap              | 6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG       |
| Conductor - AL Str Tap Range        | 6 AWG-4/0 AWG   |
| Conductor - Copper Solid Run        | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Run Range  | 6 AWG-4/0 AWG   |
| Conductor - Copper Solid Size       | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Size Range | 6 AWG-4/0 AWG   |
| Conductor - Copper Solid Tap        | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG |
| Conductor - Copper Solid Tap Range  | 6 AWG-4/0 AWG   |
| Conductor - Copper Str Run          | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG    |
| Conductor - Copper Str Run Range    | 6 AWG-4/0 AWG   |
| Conductor - Copper Str Size         | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG    |
| Conductor - Copper Str Size Range   | 6 AWG-4/0 AWG   |
| Conductor - Copper Str Tap          | 6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG    |
| Conductor - Copper Str Tap Range    | 6 AWG-4/0 AWG   |
|                                     |   |

### Certifications and Compliance

| Certification - CSA Approved            | No    |
|---|-------|
| Certification - UL Listed Direct Burial | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | Yes   |

### Logistics

| Carton Quantity       | 240 EA |
|-----------------------|--------|
| Minimum Pack Quantity | 1      |

#### For further technical assistance, please contact us

### **BURNDY Headquarters**

47 East Industrial Park Drive Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)