

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street 71302-0000, LA Alexandria Phone: 318-445-1336

Fax: 318-445-8356



Width

8200HI Compact Hosp GRD Duplex Recp 15A 125V lv *Pass & Seymour/Legrand*

.780

Pass & Seymour/Legra	and	
Catalog Number	8200HI	
Manufacturer	Pass & Seymour/Legrand	
Description	Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 15A 125V	
Weight per unit	0.2067 (lbs/each)	
Product Category	Gen Purpose Recept & Surge Pro	
Features		
amperage rating	15	
connection	Back and side wire	
Dielectric Strength	Withstands 2000V minimum	
indoor/outdoor	Indoor	
Material	Nylon	
Number of Wires	3	
Outlet Type	Indoor, Commercial	
Poles	2	
Voltage	125.0 V	
Voltage Rating	125	
Wall Plate Included	NO	
Wattage	Electrical power is expressed in Amps and Volts.	
Wire Size	14 - 10	
Material, Color, and Finish		
Finish	Matte	
Dimensions and Weight		
Height	3.281	
=		



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street 71302-0000, LA Alexandria Phone: 318-445-1336 Fax: 318-445-8356

Descriptions

COMPACT HOSP GRD DUPLEX RECP 15A 125V IV	
P&S 8200HI COMPACT HG DUP REC 15A 1	
Brass Mounting Strap	
Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 15A 125V	
Compact HG Dup Rec 15A 125V I	
Impact-resistant nylon face. One-piece heat-treated triple-wipe brass power contacts. Easily accessible break-off line contact connecting tab for split circuit wiring. Corrosion-resistant, zinc-plated steel strap is locked in. Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors. High strength thermoplastic back body. Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment. Auto-ground clip	

Manufacturer Information

Brand	Pass and Seymour	
GTIN	00785007820034	
Manufacturers Part Number	8200-HI	
UPC	785007820034	

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Туре	Outlet

Trade Size

Amperage	15.0
7 ii ii poi ugo	10.0

Packaging

Carton	1	
Package	100	
Weight Per each	0.2067	

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-15R
Operating Temperature	-40°-60°C
standard	CULUS, UL498, CSA C22.2 No. 42, FEDSPEC